


**ONE HOLE HYLUG™ CODE
CONDUCTOR STANDARD
BARREL NARROW TONGUE**

C-16

**TYPE YA-L-NT UNINSULATED
COPPER COMPRESSION
NARROW TONGUE TERMINAL**

UL Listed 90° C, Up to 35 kV ♦

45° and 90° angles available. Please contact
Customer Service to order: 1-800-346-4175




NOTE: Field bending straight lugs to achieve an angular connection will void UL Listing / CSA Certifications and BURNDY will not be liable for the connection.


Features & Benefits

- Inspection window allows for visual verification that the wire has been fully inserted prior to crimping the lug; not recommended in highly corrosive environments as the wire in the barrel is exposed to corrosive elements installed
- Narrow tongue/tang is designed for limited space applications
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the wire strands during insertion
- Short/Standard length barrel is recommended for installations with limited space requirements and meet the exact UL testing requirements as long barrel connectors so performance of the connection is not compromised
- 45° and 90° angular lugs are available; please contact Customer Service
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding


Straight






45°



90°



**ONE HOLE HYLUG™ CODE
CONDUCTOR STANDARD
BARREL NARROW TONGUE
(Continued)**



45° and 90° angles available. Please contact Customer Service to order: 1-800-346-4175



NOTE: Field bending straight lugs to achieve an angular connection will void UL Listing / CSA Certifications and BURNDY will not be liable for the connection.

Catalog Number	Conductor		Stud Hole Size	Tongue Width	Figure Dimensions			Dieless	Installation Tooling (# of crimps)					Wire Strip Length
	AWG	MM ² ***			(B)	(T)	(L)		Mech.	Hydraulic		Color Code	Die Index	
										MD6, OUR840, MD7-34R	BCT500HS, Y500CTHS			
YA8CLNT6	#8 AWG #8 Flex G,H,I,K,M DLO 37/24	10	#6	0.29	0.44	0.09	1.08	Y1MRTC (1) Y122CMR (1) MY29-3 (1) MY29-11 (1) Y81KFT (1)	W8CVT (1)	X8CRT (1)	U8CRT (1)	Red	49	1/2
YA8CLNT8			#8	0.33	0.44	0.09	1.18							
YA6CLNT6	#6 AWG Sol./Str.□	—	#6	0.29	0.54	0.09	1.17	Y1MRTC (1) MY29-3 (1) MY29-11 (1) MRC840 (1) Y81KFT (1) PAT81KFT (1) Y122CMR (1)	W5CVT (1)	X5CRT (1)	U5CRT (1)	Blue	7	7/8
YA4CLNT10	#4 AWG	—	#10	0.40	0.81	0.09	1.73		W4CVT (1)	X4CRT (1)	U4CRT (1)	Gray	8	7/8
YA3CLNT14	#3 AWG #2 Sol.	25	1/4	0.41	0.88	0.08	1.82		W3CVT (1)	W3CVT (1)	U3CRT (1)	White	9	15/16
YA3CLNT516			5/16	0.49	0.88	0.08	1.80							
YA2CLNT10	#2 AWG	35	#10	0.48	0.88	0.11	1.80		W2CVT (1)	X2CRT (1)	U2CRT (1)	Brown	10	15/16
YA2CLNT14			1/4	0.48	0.88	0.11	1.80							
YA2CLNT516			5/16	0.49	0.88	0.11	1.82							
YA1CLNT10	#1 AWG	50	#10	0.50	0.88	0.10	2.23	MY29-3 (1) MY29-11 (1) Y81KFT (1)	W1CVT (1)	X1CRT1 (1)	U1CRT1 (1)	Green	11	15/16
YA1CLNT14			1/4	0.50	0.88	0.10	2.23							
YA25LNT10	1/0 AWG	—	#10	0.62	0.88	0.12	2.28	MY29-3 (1) MY29-11 (1) MRC840	W25VT (2)	X25RT (2)	U25RT (1)	Pink	12	15/16
YA25LNT14			1/4	0.48	0.88	0.12	1.93							
YA25LNT516			5/16	0.62	0.88	0.12	2.28							
YA25LNT38			3/8	0.62	0.88	0.12	2.18							
YA26LNT10	2/0 AWG	70	#10	0.62	0.94	0.13	2.62	Y644HSXT (1) Y81KFT (1) PAT81KFT (1)	W26VT (2)	X26RT (1)	U26RT (1)	Black	13	1
YA26LNT14			1/4	0.48	0.94	0.12	2.02							
YA26LNT516			5/16	0.62	0.94	0.13	2.62							
YA26LNT38			3/8	0.72	0.94	0.12	2.48							
YA27LNT14	3/0 AWG	—	1/4	0.76	1.00	0.13	2.10	MY29-3 (1) MY29-11 (1) MRC840 (2) Y644 (1) Y81KFT (2) PAT81KFT (2)	W27VT (2)	X27RT (3)	U27RT (1)	Orange	14	1-1/16
YA27LNT516			5/16	0.60	1.00	0.12	2.17							
YA27LNT38			3/8	0.76	1.00	0.12	2.73							
YA28LNT14	4/0 AWG	—	1/4	0.76	0.88	0.14	2.60	W28VT (2)	X28RT (3)	U28RT (1)	Purple	15	1-1/8	
YA28LNT516			5/16	0.70	0.88	0.14	2.09							
YA28LNT38			3/8	0.76	0.88	0.14	2.67							

* Use PUADP-1 adapter with U dies in Y46 HYPRESS™ □ Y644 / PAT644 tooling not for use on 6 AWG Sol.
 ** The MM² conductor size listed is for Class 2 and Class 5 conductor ▲ See tooling section of this catalog for complete tool and die listings. Use ONLY color-coded die recommendations for FX connectors. For nest/indenter system contact factory
 *** The MM² conductor sizes listed are the recommendations for Class 2 conductor ♦ For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions
Note: All dimensions shown are for reference only.