Wire Termination Tools and Installation Kits

13600 Electric Hydraulic Pump

- Designed for use with singleacting cylinders and tools rated for 10,000-psi operation
- Supplied with metal carrying case
- 13620 hand switch and 13619 hydraulic hose, both sold separately, required for operation

.....Specifications

- Motor: ½ hp, 115V 50–60 Hz, 10 amps
- Pumping Capacity:
 170 cu. in./min. at 100 psi
 32 cu. in./min. at 1,000 psi
 25 cu. in./min. at 5,000 psi
 18 cu. in./min. at 10,000 psi
- Reservoir Volume: 104 cu. in. (.45 gal.)
- Basic Pump Dimension: 6" x 8" x 16"
- · Weight: 25 lbs.



CAT. NO.	DESCRIPTION	PKG. QTY.
13600	Electric Hydraulic Pump — hand or foot switch and non-	1
	metallic hose (sold separately) required for operation	

13610A Electric Hydraulic Pump with Shure-Stake® Control

- Shure-Stake® control mechanism requires 9,800-psi pump pressure before recyling to prevent under-crimping
- Designed for use with single-acting cylinders and tools rated for 10,000-psi operation
- Supplied with metal carrying case



..... Specifications

- Motor Rating: ½ hp, 115V, 50–60 Hz, 12.5 amps
- Pumping Capacity:
 170 cu. in./min. at 100 psi
 32 cu. in./min. at 1,000 psi
 25 cu. in./min. at 5,000 psi
 18 cu. in./min. at 10,000 psi
- Reservoir Volume: 104 cu. in. (.45 gal.)
- Basic Pump Dimension: 8½" x 10½" x 16"
- · Weight: 35 lbs.

CAT. NO.	DESCRIPTION	PKG. QTY.
13610A	Electric Hydraulic Pump with Shure-Stake® control —	1
	hand or foot switch and non-metallic hose	
	(sold separately) required for operation	

13810 Heavy-Duty Electric Hydraulic Pump with Shure-Stake® Control



- Designed for perfect crimps every time in heavy-duty OEM applications
- · Heavy-duty OEM two-stage pump with high flow rate
- Shure-Stake® control mechanism requires 9,800-psi pump pressure before recyling to prevent under-crimping
- Requires hand or foot control (sold separately)

...... Specifications

- Motor Rating: 1½ hp, 115V, 60 Hz, 23 amps
- Pumping Capacity:
 235 cu.in./min. at 200 psi
 6 cu.in./min. at 8,000 psi
- Reservoir Volume: 462 cu.in./2 gal.
- Dimensions (L x W x H): 10³/₄" x 15" x 20³/₄"
- · Weight: 60 lbs.

CAT. NO.	DESCRIPTION	PKG. QTY.
13810	Heavy-duty electric hydraulic pump with Shure-Stake® control — hand or foot switch and non-metallic hose (sold separately) required for operation	1

Accessories for the pumps on this page

Accessories for the pumps on this page				
CAT. NO.	DESCRIPTION	PKG. QTY.		
You may als	so needfor 13600			
13620	Hand Switch	1		
13589A	Foot Switch	1		
13619	10-ft. Non-Metallic Hose	1		
13618	20-ft. Non-Metallic Hose	1		
13600S	"Sled" type stand for 13600 pump	1		
You may als	so needfor 13610A & 13810			
13611	Hand Switch	1		
13612	Foot Switch	1		
13619	10-ft. Non-Metallic Hose	1		
13618	20-ft. Non-Metallic Hose	1		

Tel: 888.862.3289

