# **Carlon**<sup>®</sup>

### Conduit and Fittings

#### Split Duct Product Overview

Split Duct is the fast and easy way to repair broken ductwork without the costly cutting and resplicing of your conductors.

Our unique tongue-and-groove design leads the industry in providing a strong, rigid solution for duct repair situations.

The interlocking design allows the split duct sections to be staggerend and butted together. Joints may be sealed with tape and reinforced with plastic or metallic straps to produce a rigid, stable unit.

Manufactured from a compound designed specifically for power and telecommunications applications, Split Duct exhibits superior impact strength.

Available in 2 in. through 6 in. diameters, this product line also contains couplings and sweeps necessary to complete the system.


Verify with local inspection authorities before using.



The fast and easy method of installing duct around existing cable for repair and temporary installations.

#### **Recommended Installation Procedure**

- 1. Place one 10-foot Split Duct section under cable.
- Order to stagger joints, saw another section in half (about 5 feet long).
- 3. Place 5-foot section over cable and snap the two sections together.
- Place strap about one foot from the end and another strap about a foot from the joint where the ends of the top sections will butt.
- Place another 10-foot Split Duct section over the open half of the bottom section, butt the ends tightly together and snap the sections together.
- 6. Place a length of tape around both sections of the Split Duct to cover the butted joint.
- 7. Place a strap about one foot beyond the taped joint.
- Lay another length of Split Duct underneath cable, butt together, tape the butted joint and strap one foot on each side of the joint.
- 9. Repeat procedure.





### Conduit and Fittings



# **Split Duct**



Cat. No.	Description	Std. Ctn. Qty.	Std. Ctn. Wt. (lb.)	O.D. (in.)
Schedule 40			1	
49011SD-010	2 in. Schedule 40 Split Duct	700	523	2.375
49012SD-010	2-1/2 in. Schedule 40 Split Duct	460	562	2.875
49013SD-010	3 in. Schedule 40 Split Duct	500	802	3.500
49014SD-010	3-1/2 in. Schedule 40 Split Duct	290	560	4.000
49015SD-010	4 in. Schedule 40 Split Duct	290	662	4.500
49016SD-010	5 in. Schedule 40 Split Duct	130	718	5.563
49017SD-010	6 in. Schedule 40 Split Duct	130	523	6.625
Schedule 80			1	
49411SD-010	2 in. Schedule 80 Split Duct	700	702	2.375
49415SD-010	4 in. Schedule 80 Split Duct	290	890	4.500
C Duct				
68515SD-010	4 in. C Duct Split Duct	320	614	4.350

#### **Split Sleeve Coupling**



Cat. No.	Size (in.)	Description	Lenth (in.)	Split	Std. Ctn. Qty.	Std. Ctn. Wt. (lb.)
Schedule 40 and 80						
E200JS6	2	Split Coupling	6	1	25	6.1
E200KS7	2-1/2		7		25	21
E200LS7	3		7		25	15.5
E200LSS	3		6-1/2		25	10
E200MS8	3-1/2		8		25	41.2
E200NS8	4		8		15	16
E200NSS	4		6		25	17
E200PS8	5		8		15	25
E200PS9	5		9		8	16.4
E200RS1	6		10		6	24.2
C Duct						
E900NS8 (white)	4	C Duct Split Coupling	8	1	15	19
E900NSW (white)	4		6		25	22

#### **Split Sleeve Sweeps**



Item	Cat. No.	Nom. Size (in.)	Radius (in.)	Std. Ctn. Qty.	Std. Ctn. Wt. (lb.)
45° Sweep	UA7DJSD	2	24	1	1.4
	UA7FJSD	2	36		2.1
	UA7FLSD	3	36		4.7
	UA7HJSD	2	48		2.7
	UA7HLSD	3	48		6.1
	UA7IJSD	2	60		3.2
	UA7ILSD	3	60		7.2
	UA7INSD	4	60		10.2
22-1/2° Sweep	UA5INSD	4	60		6.1
11-1/4º Sweep	UA3IJSD	2	60		1.0
	UA3ILSD	3	60		3.6
	UA3INSD	4	60		5.1

Two 45° Elbows may be segmented for 90°.



