


Cable Tie Mounting Bases



Accepts cable ties up to 50-lb. (222N) tensile strength (miniature through standard)!

- Supplied on closed cell foam with synthetic rubber-based adhesive
- Use #6 self-tapping screw for added strength if desired




Std. Pkg. Cat. No.	Bulk Pkg. Cat. No.	Material	Mounting Method	Height		Length		Width		Slot Height		Slot Width		Std. Pkg.	Bulk Pkg.
				(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)		
Adhesive Mounting Cradle															
MCNY-1250-9-C	MCNY-1250-9-D	Natural Nylon 6.6	SRA* Adhesive	0.285	7.24	1.250	31.75	1.000	25.4	0.090	2.29	0.300	7.62	100	50

*Synthetic Rubber Adhesive



Fluoropolymer available for harsh environments!

- SMNY-001 accepts cable ties to 50 lbs. (222N) tensile (miniature through standard)
- SMNY-002 accepts cable ties to 120 lbs. (533N) tensile (miniature through heavy-duty)
- Use #4, #6, #8, or #10 machine screw (as referenced)



Std. Pkg. Cat. No.	Material	Mounting Method	Height		Length		Width		Slot Height		Slot Width		Bulk Pkg.
			(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	
Screw Mount													
SMNY-000-9-D	Natural Nylon 6.6	#4 Screw	0.27	6.86	0.57	14.48	0.34	8.64	0.07	1.78	0.12	3.10	500
SMTZ-001-9-D	Radiation-Resistant Fluoropolymer (green)	#6, #8 Screw	0.28	7.11	0.60	15.24	0.39	9.77	0.06	1.52	0.20	5.08	
SMNY-002-9-D	Natural Nylon 6.6	#8, #10 Screw	0.39	9.90	0.88	22.22	0.63	15.87	0.09	2.29	0.33	8.26	
SMTZ-002-9-D	Radiation-Resistant Fluoropolymer (green)		0.39	9.90	0.88	22.22	0.63	15.87	0.09	2.29	0.33	8.26	
SMNY-001-0-D	Heat-Stabilized Black Nylon	#6, #8 Screw	0.28	7.11	0.60	15.24	0.39	9.77	0.06	1.52	0.20	5.08	
SMNY-002-0-D		#8, #10 Screw	0.39	9.90	0.88	22.22	0.63	15.87	0.09	2.29	0.33	8.26	

SMNY series for use in temperatures ranging from -40°F to 221°F (-40°C to 105°C).

SMTZ series for use in temperatures ranging from -50°F to 302°F (-45°C to 150°C).



This mounting base provides a saddle for the wire run. Ty-Rap® tie is threaded under bundle and tied in usual manner. **NOTE:** For additional materials, see Technical Services.

Std. Pkg. Cat. No.	Bulk Pkg. Cat. No.	Mounting Method	Maximum Tie Width Accom. (in.)	Width		Length		Std. Pkg.	Bulk Pkg.
				(in.)	(mm)	(in.)	(mm)		
Saddle Support Base									
-	TC140	#4 Pan Head	0.091	0.344	8.74	0.563	14.30	-	500
TC5141	TC141*	#6 Pan Head	0.190	0.439	11.15	0.672	17.07	100	
TC5142	TC142	#10 Pan Head	0.301	0.563	14.30	0.922	23.42		

* Add suffix FR for flame-retardant material (TC141 only).

Natural nylon colour.

For use in temperatures ranging from -40°F to 185°F (-40°C to 85°C).