



Shown actual size: Maestro Wireless dimmer and 1-gang Claro wallplate in White (WH).

Shown actual size: Pico wireless remote in White (WH), W: 1.25 in (31.75 mm) x H: 2.63 in (66.68 mm) x D: .33 in (8 mm). For details, see p. 178)

Product family features

- Uses Lutron Clear Connect® radio frequency (RF) technology, which provides reliable RF communication with Pico® wireless remotes (see p. 178) and Radio Powr Savr™ wireless sensors (see pp. 198 and 202)
- Combine up to 10 wireless devices (dimmers, switches, sensors and/or wireless remotes)
- True multi-location dimming from every location
- Tap on to favorite level; tap off; tap twice for full on
- Touch rocker to adjust light level
- Delayed off provides light as you exit the room
- **C•L® model available**
- Communicates at 434 MHz frequency
- Coordinating Claro®, Satin Colors®, and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates, see p.237

Control types

- Single-pole (one location)
- Multi-location (up to 10 locations)
- Wireless multi-location (up to 10 locations)

Direct load type compatibility

- Incandescent/halogen lighting
- Dimmable CFL/LED lighting (screw-base)
- Magnetic low-voltage lighting
- Electronic low-voltage lighting
- Fluorescent lighting
- LED lighting
- Switched lighting/fan/motor

Load type requiring load interface

- Neon/cold cathode lighting

Lighting load interfaces may be applicable for some load type, voltage, and capacity combinations. For additional information, see pp.255–259.

Available finishes

Use **BOLD** color code in model number (Example: MRF2-600M-**PD**)

Gloss finishes*



WH
White



LA
Light Almond



AL
Almond



IV
Ivory



GR
Gray



BR
Brown



BL
Black

Satin Colors® finishes*



SW
Snow



LS
Limestone



BI
Biscuit



ES
Eggshell



PD
Palladium



TP
Taupe



ST
Stone



BG
Bluestone



PL
Plum



SG
Sea Glass



TQ
Turquoise



GS
Goldstone



DS
Desert Stone



GB
Greenbriar



MS
Mocha Stone



TC
Terracotta



SI
Sienna



HT
Hot



MR
Merlot



MN
Midnight



SS
Stainless Steel

Metal finish wallplate**

* Coordinating wallplates only available separately. For wallplate information, see p. 236.

** Stainless Steel wallplate only available separately and includes black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls. For wallplate information, see p. 236.

**Incandescent/halogen dimmer****Magnetic low-voltage dimmer****Hi-lume® 1% 2-wire LED driver dimmer****Tu-Wire® fluorescent ballast dimmer**

Digital fade wireless dimmer—
specification grade^{*,**}

Multi-location/single-pole MRF2-6ND-120-**XX**¹
120V 600W (Inc)
600VA/450W (MLV)
350W (Hi-lume 1% LED driver, max. 8)
5A (Tu-Wire fluorescent ballast)

The stated W (Watt) rating is the maximum incandescent lamp load. Ratings for MLV loads represent the maximum of the total lamp wattage plus MLV transformer loss (typically 20%).

Compatible with Advance Mark X and Sylvania POWERSENSE fluorescent ballasts, in addition to Lutron Tu-Wire®

Setting the low-end trim is necessary to ensure optimal dimming performance when using with LED drivers and fluorescent ballasts. For more information consult Lutron Application Note #370, Maestro Wireless Advanced Programming Mode, at www.lutron.com/applicationnotes

**Electronic low-voltage dimmer**

Digital fade wireless dimmer*

Multi-location/single-pole* MRF2-6ELV-120-**XX**¹
120V 600W

**3-wire fluorescent ballast/LED driver dimmer**

Digital fade wireless dimmer*

Multi-location/single-pole MRF2-F6AN-DV-**XX**¹
120/277V 6A

For use with Hi-lume 1% and EcoSystem® ballasts, and Hi-lume 1% and Hi-lume Premier 0.1% LED drivers.

For more information on Hi-lume 1% LED drivers, visit www.lutron.com/HilumeLED.

Adjustable low-end trim.

XX¹: Gloss color codes, see p. 153

Wallplates not included. Order separately, see p. 236

All models must be derated if ganged unless otherwise noted, see pp. 250–252.

***Requires neutral wire connection**

**Minimum load required, see specification submittal