

Lug Information

Aluminum Body Lugs for Copper or Aluminum Wire

Selection

For Use With Type(s)	Circuit Breaker Ampere Rating	Cables Per Lug	Lug Wire Range	Catalog Number	List Price \$
QJ2, QJH2 QJ2H, HQJ2H	60–225	1	#6 AWG–300 kcmil (Cu) #4 AWG–300 kcmil (Al)	TA1Q300	12.00 (pkg. of 3)
All 2, 3 pole ED2, ED4, ED6, ED6 ETI, HED4, HHED6	15–25	1	#14–#10 AWG (Cu) #12–#10 AWG (Al)	SA1E025	3.50
	30–100	1	#10–#1/0 (Cu or Al)	LN1E100	3.50
	110–125	1	#3-3/0 (Cu) #1-2/0 (Al)	TA1E6125	11.40
CED6 All 1 pole ED, HED	30–60	1	#10–4 (Cu or Al)	LD1E060 (Load Side)	11.40
	70–100	1	#4–#1/0 (Cu or Al)	LD1E100 (Load Side)	3.50
FXD6-A, FD6-A, HFD6, CFD6 HHFD6	70–250	1	#6 AWG–350 kcmil (Cu) #4 AWG–350 kcmil (Al)	TA1FD350A	19.80
SJD6(A), SHJD6(A) SCJD6	65-200	1–2	#4 AWG–3/0 (Cu or Al)	TA2J630	29.00
JXD2(A), JXD6(A), JD6(A), SJD6(A), HJD6(A), HJXD6(A) HHJXD6, HHJD6, SHJD6(A), CJD6, SCJD6	200–400	1–2	3/0–500 kcmil (Cu) 4/0–500 kcmil (Al)	TA2J6500	28.00
LXD6(A), LD6(A), SLD6(A), HLD6(A), HLXD6(A), HHLXD6, HHLD6, SHLD6(A), CLD6, SCLD6	250–600	1–2	3/0–500 kcmil (Cu) 4/0–500 kcmil (Al)	TA2J6500	28.00
LMD6 ^① , LMXD6 ^① , HLMd6 ^① , HLMXD6 ^① , MD6, MXD6, SMD6, HMD6, HMXD6, SHMD6, CMD6, SCMD6	500–600	1–2	#1–500 kcmil (Cu or Al)	TA2K500	64.00
		1–3	1/0–500 kcmil (Cu or Al)	TA3K500	87.00
	500–800	1–2	500–750 kcmil (Cu or Al)	TA2N750 ^②	90.00
ND6, NXD6, SND6, HND6, HNXD6, SHND6, CND6, SCND6	800–1200	1–4	250–500 kcmil (Cu or Al)	2TA4P8500 ^{③④} 3TA4P8500 ^④	522.00 754.00
			250–500 kcmil (Cu or Al)	2TA4N8500 ^③ 3TA4N8500 ^④	526.00 762.00
PD6, HPD6, CPD6 PXD6, HPXD6, SPD6, SHPD6	1200–1600	1–5	300–600 kcmil (Cu or Al)	TA5P600	286.00
PD6, PXD6, HPD6, HPXD6, SPD6, SHPD6, RD6, RXD6, HRD6, HRXD6, STD	1200–2000	1–6	300–600 kcmil (Cu or Al)	TA6R600	302.00

① Use TA2K500 or TA3K500 only.

② Used for 100% rated MD/ND frame breakers.

③ Contains 2 connectors plus 1 NDTS end barrier.

④ Contains 3 connectors plus 1 NDTS end barrier.