


Electrical Metallic Tubing (EMT) Fittings



Insulated for safe, simple installation in cramped locations or tight corners!

Short Elbows — Insulated*

- Ideal for applications where large radius conduit elbows won't fit or would appear unworkmanlike
- Shoulders on body of 1/2" size are hex-shaped to provide positive holding for standard installation tools
- Malleable iron construction
- UL rated 105°C



CAT. NO.	HUB SIZE	DIMENSION (IN.)		
		A	B	C
4240	1/2"	1 1/16	1s	7/16
4241-TB	3/4"	1 11/16	1 1/32	1/2
4242	1"	1 1/8	1 23/32	5/8
4243-TB	1 1/4"	2 1/4	2 1/32	1 1/16
4244	1 1/2"	3 3/16	2 3/4	1 1/16
4245	2"	3 3/8	3 3/16	1 1/8


UL File No. E-09043

CSA File No. 2884

Ideal for cramped locations or tight corners!

Short Elbows — Malleable Iron*

- Shoulders on body of 1/2" size are hex-shaped to provide positive holding for standard installation tools
- Malleable iron construction




CAT. NO.	HUB SIZE	DIMENSION (IN.)		
		A	B	C
4230	1/2"	1 1/16	1s	7/16
4231	3/4"	1 11/16	1 1/32	1/2
4232	1"	1 1/8	1 23/32	5/8
4233	1 1/4"	2 1/4	2 1/32	1 1/16
4234	1 1/2"	3 3/16	2 3/4	1 1/16
4235	2"	3 3/8	3 3/16	1 1/8

UL File No. E-09043

CSA File No. 2884

For connecting EMT to threaded rigid and intermediate metal conduit.

Combination Coupling — Steel*



CAT. NO.	HUB SIZE	DIMENSIONS (IN.)	
		A	B
530-TB	1/2"	1 1/8	1 1/16
531	3/4"	1 1/2	1 11/32
532	1"	1 13/32	1 21/32

UL File No. E-09043

CSA File No. 2884

For XJG Conduit Expansion Couplings for EMT see page A-25.

T&B® Fittings