

Nonmetallic Liquidtight Conduit

Fittings

CILTCC-03 /
CILTCC-08



Supplied with locknut

CILTCC-903 /
CILTCC-908



Supplied with locknut



Cat. No.	Trade Size (in.)	KO Size (in.)	Throat (in.)
Nonmetallic Liquidtight Fittings (Straight)			
CILTCC-03	3/8	1/2	0.54
CILTCC-04	1/2	1/2	0.54
CILTCC-06	3/4	3/4	0.74
CILTCC-08	1	1	0.98
Nonmetallic Liquidtight Fittings (90°)			
CILTCC-903	3/8	1/2	0.54
CILTCC-904	1/2	1/2	0.54
CILTCC-906	3/4	3/4	0.74
CILTCC-908	1	1	0.98

Features

- Chemical resistant
- Corrosion-free
- No metal fatigue or jacket separation
- Crush and abrasive resistant
- Insulated for safety
- Extra rugged and flexible
- Temperature range: -18°C to 75°C (0°F to 167°F)
- Cold impact resistant
- Lightweight
- Cuts easily
- Prevents hand injuries
- Marked at 1 foot intervals for easy measurement and cutting

Time saving... Cost effective

Applications

- Electrical motors and controls
- Plating applications
- Water treatment
- Marine equipment
- Heating and refrigeration
- Computer equipment
- Robotics
- Machine tools
- Chemical processing
- Printing equipment
- Fiber optics
- Pumps and related equipment
- Air conditioning
- Etc...

Nonmetallic liquidtight conduit may be used with **nonmetallic, malleable iron or zinc liquidtight fittings**, offering a combination of benefits not available from traditional metal liquidtight conduit.