

Cable Ties for Special Environments

Material Selection Ordering Guide

Thomas & Betts offers Ty-Rap® cable ties and accessories in a wide variety of materials, each suited for specific environments. The purpose of this document is to assist you in choosing the best material for your particular application. The effects of weathering, flame, chemicals, extreme temperatures, and radiation on the different materials are clearly presented in the following tables to simplify this process. Once you have determined the most suitable material, you can choose from the wide variety of Ty-Rap® cable ties, identification ties, mounting bases, lashing ties, etc., offered by Thomas & Betts.

Locat Cuitable

How to use Table 1:

Table 1 simplifies the material selection process by giving the relative performance ratings of the materials offered by Thomas & Betts. For example, if your application is in an extremely cold environment, four materials will answer your need: Fluoropolymer, nylon 12, Halar® (*), and stainless steel. Then, cost may be your next most important criteria, so out of those four options, nylon 12 would be the most cost effective. However, if tensile strength is important, then stainless steel would be the better choice.

Refer to tables 2 (page C33) and 3 (pages C34-C36) for more detailed information regarding physical properties of the materials and chemical resistance of the materials respectively.

It is extremely difficult to provide data on all the possible combinations or conditions that can occur. This information is based on data provided by the manufacturers of the specific materials listed and is provided only as a general guide. No specific recommendation is intended. As each application may differ, cable tie samples should be tested in the intended application by the user to determine suitability.

Arrailable Materiale

TABLE 1

Available Mat	5 = Most Suitable 1 = Least Suitable									
	Natural 66 Nylon	Weather Resistant 66 Nylon	Heat Stabilized Natural 66 Nylon	Flame Retardant 66 Nylon	Weather Resistant Nylon 12	Weather Resistant Polypropylene	Fluoro- polymer	Halar®	Stainless Steel	Weatherable Acetal
Ultraviolet Resistance	1	4	1	1	4	4	5	5	5	4
Radiation Resistance	1	1	1	1	1	1	4	4	5	1
Low Temperature	3	3	3	2	4	3	4	4	5	4
High Temperature	3	3	4	3	2	2	4	4	5	2
Flammability	3	3	3	4	1	1	4	4	5	1
Tensile Strength	3	3	3	3	2	1	3	3	5	2
Relative Cost	Low	Low	Low	Med	Med	Low	High	High	High	High
Chemical Resistance					See Table 3					

Mant Cuitable

^{*} Halar® is the trademark of Solvay Solexis, Inc.





Detectable using metal detection and X-ray detection systems and visions systems.

Polypropylene parts are also bouyant in liquid application. **Material** — Polyamide (Nylon 6.6) or Polypropylene **Colour** — Blue

For use in temperatures ranging from -40°F to 185°F (-40°C to 85°C).

Cat. No.	Length (in./mm)	Body Max. Wii Width Bundle D (in./mm) (in./mm		Tensile Strength (lb./N)	Base Material	Std. Pkg.		
Ty-Rap® Detectable Cable Ties								
TY523M-NDT	3.62/91.95	0.09/2.29	0.63/16.00	18/80		100		
TY525M-NDT	7.31/186.00	0.19/4.70	1.75/44.40	50/220	Nylon	100		
TY527M-NDT	13.40/340.00	0.27/6.86	3.50/89.00	120/540	NYIOH	50		
TY528M-NDT	14.20/36.00	0.19/4.70	4.00/102.00	50/220				
TY523M-PDT	3.62/91.90	0.09/2.29	0.63/16.00	18/80		100		
TY525M-PDT	7.31/186.00	0.19/4.70	1.75/44.40	30/135	Polypropylene			
TY527M-PDT	13.40/340.00	0.27/6.86	3.50/89.00	60/267	Folypropylerie	50		
TY528M-PDT	14.20/36.00	0.19/4.70	4.00/102.00	30/135		100		







Make safety a priority!

This material meets UL 94V-0 flammability rating. **Colour** — White

For use in temperatures ranging from -40°F to 185°F (-40°C to 85°C).

† Not (Recognized Models.

Cat. No.	Length (in./mm)	Body Width (in./mm)	Max. Wire Bundle Dia. (in./mm)	Marking Pad Size (in./mm) W x H	Tensile Strength (lb./N)	Std. Pkg.
Ty-Rap® Cabl	le Ties – Flan	ne Retarda	nt Nylon 6.6			
TY23MFR	3.62/91.95	0.09/2.29	0.63/16.00		18/80.07	1,000
TY232MFR	8.00/203.20	0.09/2.29	2.00/50.80		10/00.07	
TY24MFR	5.50/139.70	0.14/3.56	1.13/28.70		40/177.90	
TY25MFR	7.31/185.67	0.18/4.57	1.75/44.45	N/A	50/222.40	
TY28MFR	14.20/360.68	0.18/4.57	4.00/101.60		30/222.40	
TY272MFR†	8.00/203.20	0.27/6.86	2.00/50.80		120/533.80	500
TY27MFR	13.20/335.28	0.27/6.86	3.50/88.90			
TY53MFR	4.00/101.60	0.09/2.29	0.63/16.00	0.81 x 0.36/20.57 x 9.1		500
TY153MFR	4.35/110.49	0.10/2.54	0.63/16.00	0.78 x 1/19.81 x 14.00	10/00.07	







This material provides very good resistance to ultraviolet light and chemical exposure. Nylon 12 is a lower, moisture-absorbing material than 6.6 nylon and the effect of water on properties is much less.

Colour — Black

For use in temperatures ranging from -40°F to 185°F (-40°C to 85°C).

Std. Cat. No.	Bulk Cat. No.	Length (in./mm)	Body Width (in./mm)	Max. Wire Bundle Dia. (in./mm)	Tensile Strength (lb./N)	Std. Pkg.	Bulk Pkg.		
Ty-Rap® Nylon 12 Cable Ties – Ultraviolet and weather-resistant!									
TYC525MX	TYC25MX	7.31/185.67	0.18/4.57	1.75/44.45	35/155.70	100	1,000		
_	TYC28MX	14.20/360.68	0.10/4.37	4.00/101.60	33/133.70				
_	TYC272MX	8.00/203.20	0.27/6.86	2.00/50.80		_	500		
TYC527MX	TYC27MX	13.20/335.28	0.27/0.00	3.50/88.90	85/378.10	50			
-	TYC29MX	30.00/762.00	0.30/7.62	9.00/228.60		_			







Engineered to withstand high temperatures!

Material meets ASTM D4066 PA121.

Colour — Green Tint

For use in temperatures ranging from -40°F to 221°F (-40°C to 105°C).

Cat. No.	Length (in./mm)		Max. Wire Bundle Dia. (in./mm)	Tensile Strength (lb./N)	Std. Pkg.
Ty-Rap® Heat Sta	bilized Ties				
TYH23M	3.62/91.95	0.00/0.00	0.63/16.00	10/00 07	1,000
TYH232M	8.00/203.20	0.09/2.29	2.00/50.80	18/80.07	
TYH24M	5.50/139.70		1.13/28.70	40/177.90 30/135	
TYH242M	8.19/208.03	0.14/3.56	2.00/50.80		
TYH26M	11.10/281.94		3.00/76.20		
TYH25M	7.31/185.67		1.75/44.45		
TYH253M	11.40/289.56	0.18/4.57	3.00/76.20	50/222.40	
TYH28M	14.20/360.68		4.00/101.60		
TYH27M	13.20/335.28	0.27/6.86	3.50/88.90		
TYH272M	8.75/222.25	0.27/0.00	2.00/50.80	120/533.80	500
TYH29M	30.00/762.00	0.30/7.62	9.00/228.60	1	



