

Cutting & Notching Tools

Aviation Snips – Regular/Offset/Bulldog

- Forged and heat-treated steel blades for strength and durability.
- Regular and offset blades have the capacity of cutting 18 gauge cold-rolled sheet metal and 22 gauge stainless steel sheet metal.
- Offset blades provide ease of cutting tight curves and keep user's hand away from metal.
- Bulldog snips (Cat. No. 2103) for notching or trimming 16 gauge cold-rolled sheet metal and 18 gauge stainless steel sheet metal.
- Spring-loaded for self-opening action.
- Latch keeps jaws closed when not in use.
- Hardened handles for extra strength.
- Contoured plastic handles are comfortable and color-coded by cutting pattern.

Cat. No.	Cutting Pattern	Length of Cut	Color Code	Overall Length	Weight (oz.)
1100L	regular left	1-3/8" (35 mm)	red	9-3/4" (248 mm)	14.4
1101R	regular right	1-3/8" (35 mm)	green	9-3/4" (248 mm)	14.7
1102S	regular straight	1-1/2" (38 mm)	yellow	10-1/8" (257 mm)	14.4
2100L	offset left	1-1/4" (32 mm)	red	9-1/2" (241 mm)	15.5
2101R	offset right	1-1/4" (32 mm)	green	9-1/2" (241 mm)	15.7
2102S	offset straight	1-1/2" (38 mm)	yellow	9-1/2" (241 mm)	15.5
2103	notch	7/8" (22 mm)	yellow	9-1/4" (235 mm)	13.9




Replacement springs for aviation snips

P406	replacement spring for Cat. Nos. 1100L and 1102S
P407	replacement spring for Cat. No. 1101R

Crimping Tools

5-Blade Crimper

- Produces factory-precision indentations in stove pipe and round duct with just a squeeze.
- Compound-leverage mechanism, heavy-duty jaw/handle linkage, and closing stop provide easy operation and consistent crimps for virtually leak-proof connections.
- Hardened steel handles include hand guards and are covered with vinyl grips for added comfort and easy operation.
- All steel construction and nickel-plating provide long life and consistent crimp profile.



86550

Cat. No.	Overall Length	Crimps	Handle Color	Weight (lbs.)
86550	9" (229 mm)	24 ga. CRSM and 28 ga. SSSM	blue	1.00

Sheet Metal Fasteners

Self-Piercing Sheet Metal Screws

NEW!



8910-3/4

- Zinc plated.
- Sheet metal screws with self piercing tips.
- Slotted 1/4" hex head washer.

Cat. No.	Length	Driver Type	Size	Head Type
8910-3/4	3/4" (19 mm)	1/4" slotted	#8	hex washer
8910-1/2	1/2" (13 mm)	1/4" slotted	#8	hex washer

NEW!

Duct Stretching & Slitting Tools

Duct Stretcher



89565

- Aligns and pulls ductwork together, easing installation of drive cleats.
- Offset handle protects hand.

Cat. No.	Overall Length	Weight (oz.)
89565	16" (406 mm)	12

Duct Slitting Tool



DS7

- Blade used to scribe a line or pierce and enlarge holes in sheet metal.
- Cushion-Grip handle for greater comfort and control.
- Patented Tip-Ident® quickly identifies the type of tool and tip orientation.

Cat. No.	Overall Length	Weight (oz.)
DS7	13" (330 mm)	5.6

All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: Never use on or near live electrical circuits.

