
The Eaton difference



- Mid-size screwless wallplates deliver the ultimate in designer looks with a screwless finish; they are fast and easy to install, virtually unbreakable and easy to clean
- Mid-size & oversize wallplates are designed for use in applications where additional wall coverage is needed
- Extra depth wallplates are available for use with old work outlet boxes for a flush fit to the wall
- Available wallplate materials include virtually unbreakable nylon & polycarbonate thermoplastics, 302/304 corrosion resistant stainless steel, brass, and thermoset
- Nylon & polycarbonate wallplates feature screw-catch, a timesaving feature that holds mounting screws captive to simplify installation
- Our wallplates are manufactured according to the performance & dimensional requirements of Federal Specification WP-455, NEMA Standard WD-1, UL Standard 514 and the NEC®



Specific wallplate solutions for today's needs



Aesthetic upgrade

Our screwless wallplates come in 3 different openings for upgrading the look of toggle switches, GFCIs, rotary dimmers and duplex receptacles without having to change out devices!

See pages C-17 to C-19

Shown: PJS1





Corrosion resistance

Brass and stainless steel wallplates offer durable, elegant corrosion resistance making them ideal for high-moisture locations like kitchens, baths, garages and basements.

See pages C-10 to C-25







Impact resistance

Thermoplastic polycarbonate and nylon wallplates are virtually unbreakable, warp resistant, abrasion resistant and soil resistant, making them ideal for high-traffic areas.

See pages C-10 to C-26




Shown: PJ26



Wallplate material information





Design features

- Rugged construction reduces installation cost due to less plate breakage and resists bowing to provide a smooth, flat installation
- Exclusive timesaving Screw-catch feature holds mounting screws captive and simplifies installation
- · High gloss finish is soil resistant
- Polycarbonate wallplates are virtually unbreakable with high structural rigidity, long-term form retention, plus superior impact and abrasion resistance
- Nylon wallplates have a flush-fitting, warp resistant design
- Matching mounting screws provide

Testing & code compliance

 cULus listed to UL514C, file no. E33216, certified to CSA C22.2, no. 42.1

Material characteristics

- Flammability: meets UL94 requirements; 5V rated
- Temperature rating: -40°C to 70°C (-40°F to 158°F)

Thermoset wallplates

Design features

 Extensive line of non-flammable thermoset plates provides flush-fitting, warp resistant performance

Material characteristics

- Flammability: Meets UL94 requirements; 5V rated
- Temperature rating: -40°C to 65°C (-40°F to 149°F)

Testing & code compliance

 cULus listed to UL514C, file no. E33216, certified to CSA C22.2, no. 42.1

302/304 Stainless steel wallplates

Design features

- Superior non-corrosive and non-magnetic properties for applications needing protection from those elements
- Stainless steel alloy contains 18% chromium and 8% nickel for corrosion resistance
- Stamped from 0.032" (0.81mm) thick material
- Horizontally satin-brushed surface finish resists finger prints
- All plates are coated with clear, removable PVC to safeguard the surface during handling and installation

Matching stainless steel mounting screws provided

Testing & code compliance

 Listed to UL514D, file no. E92122, certified to CSA C22.2, no.42.1

Material characteristics

• Temperature rating: -40°C to 70°C (-40°F to 158°F)



Brass wallplates

Design features

- Line of handsomely crafted, elegant solid brass designs in 11 popular NEMA standard size configurations
- Strong, corrosion resistant and coated with transparent lacquer to resist premature oxidation
- Horizontally satin-brushed surface finish resists fingerprints
- Matching brass-plated steel screws resist damage during installation

- All plates are coated with clear, removable PVC to safeguard the surface during handling and installation
- Solid brass material is a 70/30 alloy (#26C), .040" (1.02mm) thick

Testing & code compliance

• Listed to UL514D, file no. E92003

Material characteristics

• Temperature rating: -40°C to 70°C (-40°F to 158°F)

Wallplate quick reference guide



Toggle









|--|

	Standard size				Mid-size				Oversize	
Gang	Thermoset	Nylon	Stainless steel	Brass	Thermoset	Polycarbonate	Screwless	Stainless steel	Thermoset	Stainless steel
1-Gang	2134	5134	93071	94071	2034	PJ1	PJS1	93971	2144	93871
2-Gang	2139	5139	93072	94072	2039	PJ2	PJS2	93972	2149	93872
3-Gang	2141	5141	93073	94073	2041	PJ3	PJS3	93973	2741	93873
4-Gang	2154	5154	93074	_	2054	PJ4	PJS4	_	_	93874
5-Gang	2155	_	93075	_	_	PJ5	_	_	_	_
6-Gang	2156	_	93076	_	_	PJ6	_	_	_	_


Decorator/GFCI














	Standard size	е			Mid-size				Oversize	
Gang	Thermoset	Nylon	Stainless steel	Brass	Thermoset	Polycarbonate	Screwless	Stainless steel	Thermoset	Stainless steel
1-Gang	2151	5151	93401	94401	2051	PJ26	PJS26	93934	2751	93834
2-Gang	2152	5152	93402	94402	2052	PJ262	PJS262	93935	_	_
3-Gang	2163	_	93403	_	2063	PJ263	PJS263	93936	_	_
4-Gang	2164	_	93404	_	2064	PJ264	PJS264	_	_	_
5-Gang	2165	_	93405	_	_	PJ265	PJS265	_	_	_
6-Gang	2166	_	93406	_	_	PJ266	PJS266	_	_	_

Duplex receptacle







	Standard size	Standard size			Mid-size				Oversize	
Gang	Thermoset	Nylon	Stainless steel	Brass	Thermoset	Polycarbonate	Screwless	Stainless steel	Thermoset	Stainless steel
1-Gang	2132	5132	93101	94101	2032	PJ8	PJS8	93901	2142	93801
2-Gang	2150	5150	93102	94102	2050	PJ82	_	93902	2750	93802
3-Gang	_	_	93103	_	_	_	_	_	_	_

Blank









Standard size					Mid-size				Oversize	
Gang	Thermoset	Nylon	Stainless steel	Brass	Thermoset	Polycarbonate	Screwless	Stainless steel	Thermoset	Stainless steel
1-Gang	2129	5129	93151	94151	2029	PJ13	_	93951	2729	93851
2-Gang	2137	5137	93152	_	2037	PJ23	_	_	_	93852
3-Gang	_	_	93153	_	_	_	_	_	_	_
4-Gang	_	_	93154	_	_	_	_	_	_	_
1-strap mt.	_	_	_	_	_	PJ14	_	_	_	_

Compliances, specifications and availability are subject to change without notice.



Wallplate quick reference guide

Power outlet







	Standard size	Standard size				Mid-size				Oversize	
Gang	Thermoset	Nylon	Stainless steel	Chrome	Thermoset	Polycarbonate	Screwless	Stainless steel	Thermoset	Stainless steel	
1-1.40" Hole	2131	5131	93091	_	_	PJ7	_	_	2731	93891	
1-1.59" Hole	_	_	93111	_	_	PJ720	_	_	_	_	
1-2.15" Hole	_	_	93221	39CH	2068	PJ724	_	_	_	_	
2-2.15" Hole	2168	_	93227	68	_	PJ703	_	_	_	_	

Combination












	Standard size	Standard size				Mid-size			
Gang	Thermoset	Nylon	Stainless steel	Brass	Thermoset	Polycarbonate	Stainless steel	Thermoset	
Toggle & duplex receptacle	2138	5138	93532	94532	2038	PJ18	93932	2148	
Toggle & decorator	2153	5153	93432	94432	2053	PJ126	93937	_	
Toggle & blank	_	5171	_	_		PJ113	_	<u> </u>	
Duplex receptacle & blank		5170	_	_	<u> </u>	PJ138	_	<u> </u>	
Duplex receptacle & decorator	2157	_	_	_	_	PJ826	_	_	





	Standard size			Mid-size
Gang	Thermoset	Nylon	Stainless steel	Polycarbonate
2 Toggles & duplex receptacle	2158	5158	93543	PJ28
2 Toggles & decorator	2173	_	93443	PJ226

Size options



Color ordering information:

A (Almond), B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White), Brass, Stainless Steel, BB (Brushed Bronze)



^{*}Note: See pages C-9 – C-24 for full specifications and available color options.

Compliances, specifications and availability are subject to change without notice.



Mid-size wallplates

Mid-size toggle switch wallplates

Product description

1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang











5-Gang



6-Gang





3-Gang



4-Gang

Togale switch

loggie switch				*
Description	Material	Color suffix	Catalog no.	♣ 🕙
1-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ1	•
	Thermoset	A, B, LA, V, W	□ 2034	• •
	302/304 Stainless steel	_	□ 93971	• •
2-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□PJ2	•
	Thermoset	A, B, LA, V, W	□ 2039	• •
	302/304 Stainless steel	_	□ 93972	• •
3-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ3	•
	Thermoset	A, B, LA, V, W	□ 2041	• •
	302/304 Stainless steel	_	□ 93973	• •
4-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ4	•
	Thermoset	A, LA, V, W	□ 2054	• •
5-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ5	•
6-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ6	•

Mid-size toggle switch screwless wallplates

Product description

1-Gang, 2-Gang, 3-Gang, 4-Gang

Screwless toggle switch

Description	Material	Color suffix	Catalog no.	V
1-Gang	Polycarbonate	A, B, BB, BK, LA, V, W	□ PJS1	•
2-Gang	Polycarbonate	A, B, BB, BK, LA, V, W	□PJS2	•
3-Gang	Polycarbonate	A, LA, V, W	□PJS3	•
4-Gang	Polycarbonate	A, LA, V, W	□PJS4	•

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White), BB (Brushed Bronze), Stainless Steel



Certification information: 2000, 5000 and PJ series wallplates are cULus certified; 93000 series wallplates are UL and CSA certified; 94000 are UL certified Dimensional information: C-5, C-6 Specification information: Please visit www.eaton.com/wiringdevices Compliances, specifications and availability are subject to change without notice.



Indicates NAFTA compliant - Page G-21



C-16