



Shown actual size: Nova T[☆] dimmer in Black (BL) with 1-gang Architectural wallplate in Clear Anodized Aluminum (CLA).









Product family features

- Full family of controls plus matching fan controls, switches, and wiring devices
- Exclusive dimmer/switch size opening
- Slide adjusts light to suit any activity
- Classic slider, thin profile design
- Voltage compensation maintains stable light levels, despite line voltage variations
- **C•L[®] model available**
- Coordinating wallplate included with Architectural matte finish controls; metal wallplates only available separately
- Custom engraving and custom coloring available for wallplates, see p. 229


Control types

-  Single-pole (one location)
-  3-way or 4-way (two or more locations)

Direct load type compatibility

-  Incandescent/halogen lighting
-  Dimmable CFL/LED lighting (screw-base)
-  Magnetic low-voltage lighting
-  Electronic low-voltage lighting
-  Fluorescent lighting
-  LED lighting
-  Switched lighting/fan/motor
-  Ceiling fans

Load types requiring load interface

-  Neon/cold cathode lighting

Lighting load interfaces may be applicable for some additional load type, voltage, and capacity combinations.

For additional information, see pp. 255–259.

Available finishes

Use **BOLD** color code in model number (Example: NT-600-**SI**)

Architectural matte finishes*



WH
White



LA
Light Almond



AL
Almond



BE
Beige



IV
Ivory



TP
Taupe



GR
Gray



SI
Sienna



BR
Brown



BL
Black

Architectural metal finish wallplates**



BN
Bright Nickel



BC
Bright Chrome



CLA
Clear Anodized
Aluminum



SC
Satin Chrome



SN
Satin Nickel



QZ
Antique Bronze



AU
Gold Plated



BB
Bright Brass



BRA
Brass Anodized
Aluminum



SB
Satin Brass



QB
Antique Brass



BLA
Black Anodized
Aluminum

*Coordinating wallplate included with Architectural matte controls.

**Metal finish wallplates only available separately and include black plastic trim/adaptor, visible from side. Match with separate Black (BL) controls. For wallplate information, see p. 226.

 **3-wire fluorescent ballast/LED driver dimmers**
(small controls)

Slide-to-off dimmers*


| | |
|-------------------------|------------------------------------|
| Single-pole 120V 16A | NTF-10- XX ¹ |
| Single-pole 277V 8A | NTF-10-277- XX ¹ |

For use with EcoSystem[®] and Hi-lume[®] 3D ballasts, and Hi-lume 1% and Hi-lume Premier 0.1% LED drivers.

Adjustable low-end trim.

For more information on Hi-lume 1% LED drivers, visit www.lutron.com/HilumeLED.

No derating required if ganged.

 **0-10V fluorescent/LED fixture dimmer**
(current sink control)
(small control)

Slide-to-off dimmer

| | |
|--------------------------------------------------|-------------------------------|
| Single-pole 120/277V 30mA max control current | NTSTV- XX ¹ |
|--------------------------------------------------|-------------------------------|

No power pack required.

Dimmer has maximum capacity of 8A load or 30mA 0–10V sink, limited by whichever rating is achieved first. Power pack (PP-DV) may be used for loads over 8A.

Compatible with any IEC 60929 Annex E compliant ballast or driver, available from many manufacturers (check for IEC 60929 compliance on the specification of the designed ballast or driver, or confirm compatibility with the manufacturer).

Consult ballast/driver manufacturer for specific ballast/driver current draw to determine maximum number of ballasts/drivers per control.

No derating required if ganged.

XX¹: Architectural matte color codes, see p. 31 (1-gang wallplate included)

 **Tu-Wire[®] fluorescent ballast dimmers**
(small controls)

Slide-to-off dimmers

| | |
|-------------------------|--------------------------------------|
| Single-pole 120V 5A | NTFTU-5A- XX ¹ |
| Single-pole* 277V 5A | NTFTU-5A-277- XX ¹ |

Also compatible with Advance Mark X ballasts, for further information visit www.lutron.com/advance.

For information on use with Sylvania POWERSENSE ballasts, contact Technical Support at 1.800.523.9466.

All models must be derated if ganged, unless otherwise noted, see pp. 248–249.

* **Requires neutral wire connection**