Cushion-Grip Screwdrivers

Cabinet-Tip Screwdrivers – Round-Shanks

Additional Feature:

 Narrow cabinet-tip permits blade access where space is limited.



Cat. No.	Shank Tip Width	Shank Length	Overall Length	Weight (lbs.)
601-3	3/16" (5 mm)	3" (76 mm)	6-3/4" (171 mm)	.10
601-4	3/16" (5 mm)	4" (102 mm)	7-3/4" (197 mm)	.15
601-6	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.15
601-8	3/16" (5 mm)	8" (203 mm)	11-3/4" (298 mm)	.20
601-10	3/16" (5 mm)	10" (254 mm)	13-3/4" (349 mm)	.20

Cat. No.	Shank Tip Width	Shank Length	Overall Length	Weight (lbs.)			
Heavy-Du	Heavy-Duty Shanks						
605-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.25			
605-6	1/4" (6 mm)	6" (152 mm)	10-11/32" (263 mm)	.30			
605-8	1/4" (6 mm)	8" (203 mm)	12-11/32" (314 mm)	.30			
605-10	1/4" (6 mm)	10" (254 mm)	14-11/32" (365 mm)	.35			

Refer to the insulated section for insulated screwdrivers.

Profilated Phillips-Tip Screwdrivers – Round-Shanks

Additional Features:

- Tips are precision-machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Provides accurate fit and torque without slippage.



603-7

Cat. No.	Point Size	Shank Length	Overall Length	Weight (lbs.)
603-1	No. 2	1-1/2" (38 mm)	3-7/16" (87 mm)	.10
603-3	No. 1	3" (76 mm)	6-3/4" (171 mm)	.15
603-4	No. 2	4" (102 mm)	8-5/16" (211 mm)	.25
603-6	No. 3	6" (152 mm)	11" (279 mm)	.35
603-7	No. 2	7" (178 mm)	11-5/16" (287 mm)	.30
603-10	No. 2	10" (254 mm)	14-5/16" (364 mm)	.35

Refer to the insulated section for insulated screwdrivers.

Miniature Cushion-Grip Screwdrivers



Additional Feature:

• Precision tip for exact fit and rigorous applications.

Cat. No.	Tip Type	Shank Tip Size	Shank Length	Overall Length	Weight (lbs.)
604-3	Phillips	No. 0	3" (76 mm)	5-3/4" (146 mm)	.04
606-2	keystone	1/16" (1.6 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
607-2	cabinet	3/32" (2.4 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
607-3	cabinet	3/32" (2.4 mm)	3" (76 mm)	5-3/4" (146 mm)	.04
607-4	cabinet	3/32" (2.4 mm)	4" (102 mm)	6-3/4" (171 mm)	.04
608-2	cabinet	1/8" (3.2 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
608-3	cabinet	1/8" (3.2 mm)	3" (76 mm)	5-3/4" (146 mm)	.04
608-4	cabinet	1/8" (3.2 mm)	4" (102 mm)	6-3/4" (171 mm)	.05
608-6	cabinet	1/8" (3.2 mm)	6" (152 mm)	8-3/4" (222 mm)	.05
608-8	cabinet	1/8" (3.2 mm)	8" (203 mm)	10-3/4" (273 mm)	.05
608-10	cabinet	1/8" (3.2 mm)	10" (254 mm)	12-3/4" (324 mm)	.05

Coated Cabinet-Tip Screwdrivers – Round-Shanks



620-4

Additional Features:

- Plastic coated for circuit protection only. NOT INSULATED.
- Special plastic coating resists cutting, cracking, and chipping.
- Thin coating permits use in confined areas.

Cat. No.	Shank Tip Width	Shank Length	Overall Length	Weight (lbs.)		
620-3	3/16" (5 mm)	3" (76 mm)	6-3/4" (171 mm)	.15		
621-6	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.20		
621-8	3/16" (5 mm)	8" (203 mm)	11-3/4" (298 mm)	.20		
621-10	3/16" (5 mm)	10" (254 mm)	13-3/4" (349 mm)	.25		
Heavy-Duty Shanks						
620-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.20		
620-6	5/16" (8 mm)	6" (152 mm)	10-15/16" (278 mm)	.40		
620-8	3/8" (10 mm)	8" (203 mm)	13-7/16" (341 mm)	.60		

All dimensions are in inches and (millimeters).

AWARNING: NOT insulated. Will NOT protect against electrical shock.

AWARNING: Do NOT use to pry or chisel.



AWARNING: Always wear approved eye protection.