
SWITCHES

Hard Use & Commercial Specification Grade Switches 15 & 20A, 120/277VAC



15 & 20 Amp

Features

- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrsion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 – #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

CATALOG NUMBER				RATING			3rd PARTY COMPLIANCE					
						(L)	FSUL	€.				
SINGLE POLE	DOUBLE POLE	THREE-WAY	FOUR-WAY	A.	VAC	COLOR	UL20	WS896	C22.2 111			
HARD USE SPECIFICATION GRADE BACK & SIDE WIRE												
CSB15AC1I	CSB15AC2I	CSB15AC3I	CSB15AC4I	15	120/277	lvory	•	•	•			
CSB15AC1W	CSB15AC2W	CSB15AC3W	CSB15AC4W	15	120/277	White	•	•	•			
CSB15AC1	CSB15AC2	CSB15AC3	CSB15AC4	15	120/277	Brown	•	•	•			
CSB15AC1GRY	CSB15AC2GRY	CSB15AC3GRY	CSB15AC4GRY	15	120/277	Gray	•	•	•			
CSB15AC1LA	CSB15AC2LA	CSB15AC3LA	CSB15AC4LA	15	120/277	Light Almond	•	•	•			
CSB20AC1I	CSB20AC2I	CSB20AC3I	CSB20AC4I	20	120/277	Ivory	•	•	•			
CSB20AC1W	CSB20AC2W	CSB20AC3W	CSB20AC4W	20	120/277	White	•	•	•			
CSB20AC1	CSB20AC2	CSB20AC3	CSB20AC4	20	120/277	Brown	•	•	•			
CSB20AC1BK		CSB20AC3BK		20	120/277	Black	•	•	•			
CSB20AC1GRY	CSB20AC2GRY	CSB20AC3GRY	CSB20AC4GRY	20	120/277	Gray	•	•	•			
CSB20AC1LA	CSB20AC2LA	CSB20AC3LA	CSB20AC4LA	20	120/277	Light Almond	•	•	•			

CATALOG NUMBER		DATING			3rd PARTY COMPLIANCE							
CATALOG NUMBER		RATING			(A)	FSUL	€.					
SINGLE POLE	THREE-WAY	A.	VAC	COLOR	UL20	WS896	C22.2 111					
COMMERCIAL SPECIFICATION GRADE SIDE WIRE												
CS15AC1I	CS15AC3I	15	120/277	lvory	•	•	•					
CS15AC1W	CS15AC3W	15	120/277	White	•	•	•					
CS15AC1	CS15AC3	15	120/277	Brown	•	•	•					
CS15AC1GRY	CS15AC3GRY	15	120/277	Gray	•	•	•					
CS15AC1BK	CS15AC3BK	15	120/277	Black	•	•	•					
CS15AC1LA	CS15AC3LA	15	120/277	Light Almond	•	•	•					
CS20AC1I	CS20AC3I	20	120/277	lvory	•	•	•					
CS20AC1W	CS20AC3W	20	120/277	White	•	•	•					
CS20AC1	CS20AC3	20	120/277	Brown	•	•	•					
CS20AC1GRY	CS20AC3GRY	20	120/277	Gray	•	•	•					
CS20AC1LA	CS20AC3LA	20	120/277	Light Almond	•	•	•					

For Bulk Packaging Solutions consult factory.



DEVICES & WALL PLATES

Color Selection Chart

Devices & Plastic Wall Plate Colors



See specific device and wall plate catalog charts for particular color availabilities.


Metal Wall Plates

Metal Finish



Custom Metal Wall Plates Paint Finish Colors

Paint Color



To order custom metal wall plates, see Pages P-41 - P-45.

 $\label{prop:consult} \textbf{For additional colors consult factory.}$