


## STRAIGHT BLADE RECEPTACLES

## PlugTail™ Specification Grade Receptacles


PTTR5362W and PT5362SCI  
PlugTail™ Spec Grade Receptacles

- A. Auto-ground clip** assures positive ground.
  - B. .036 inch thick, brass, triple-wipe power contacts** for lasting retention.
  - C. Dual mechanical shutter system** to help prevent insertion of foreign objects.
  - D. Plated steel wrap strap design** for maximum durability and corrosion resistance.
  - E. Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.
  - F. Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.
  - G. Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.
  - H. Pre-stripped connector leads** fasten to conductors, easier than standard pigtails.
  - I. No exposed terminals** create a finger safe application before, during, and after installation.
  - J. Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.
  - K. Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.
  - L. Exclusive patented feature, circuit label on back** allows permanent circuit identification.
  - M. Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.
  - N. Pre-stripped connector leads** fasten to conductors, easier than standard pigtails.
  - O. Auto-ground clip** assures positive ground.
  - P. .036 inch thick, brass, triple-wipe power contacts** for lasting retention.
  - Q. Plated steel wrap strap design** for maximum durability and corrosion resistance.
  - R. Pre-wired with one welded pre-stripped wire lead** to facilitate switched receptacle circuit applications.
- Three drive screws anchor strap** to back body and face.




# STRAIGHT BLADE RECEPTACLES

## PlugTail™ Hospital Grade Receptacles 15 & 20A, 125V



PT8200HW




PT8300HW

### Features

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap-around strap design for maximum durability and corrosion resistance.
- No exposed terminals create a fingersafe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing.
- Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE		
	A.	V.			cUL <sup>us</sup> UL498	FSUL WC596	CSF C22.2 No. 42
<b>HEAVY-DUTY COMPACT DESIGN DUPLEX RECEPTACLES</b>							
PT8200HI	15	125	Ivory	5-15R	•	•	•
PT8200HGRY	15	125	Gray	5-15R	•	•	•
PT8200HRED	15	125	Red	5-15R	•	•	•
PT8200HW	15	125	White	5-15R	•	•	•
PT8200HBK	15	125	Black	5-15R	•	•	•
PT8200HLA	15	125	Light Almond	5-15R	•	•	•
PT8200H	15	125	Brown	5-15R	•	•	•
PT8300HI	20	125	Ivory	5-20R	•	•	•
PT8300HGRY	20	125	Gray	5-20R	•	•	•
PT8300HRED	20	125	Red	5-20R	•	•	•
PT8300HW	20	125	White	5-20R	•	•	•
PT8300HBK	20	125	Black	5-20R	•	•	•
PT8300HLA	20	125	Light Almond	5-20R	•	•	•
PT8300H	20	125	Brown	5-20R	•	•	•




For Bulk Packaging Solutions consult factory.


# DEVICES & WALL PLATES

## Color Selection Chart

### Devices & Plastic Wall Plate Colors



Ivory    Light Almond    White    Green    Antique Brass    Dark Bronze    Nickel




Black    Blue    Brown    Gray    Orange    Red

See specific device and wall plate catalog charts for particular color availabilities.

### Metal Wall Plates


Metal Finish



Aluminum    Brass (Brushed)    Polished Brass    Stainless Steel    Brushed Bronze    Chrome

### Custom Metal Wall Plates Paint Finish Colors

Paint Color



Orange    Green    Gray    Yellow    Glossy Black    Brown    White



Primer    Red    Pink    Flat Black    Ivory    Light Almond    Blue

To order custom metal wall plates, see Pages P-40 - P-44.

**For additional colors consult factory.**