

VISTA POINT5™ ARCHITECTURAL COLUMNS


Vista Point5 Architectural Columns Add-On Plates for Small Frame Vista Series Ordering Information

VS1A Device Cover




Has one cutout for duplex receptacle and two adapters for Wiremold CM Series Open Systems communication modules, and Ortronics® Series II or TracJack devices.

VB880 Adapter Plate




Adapts Vista Point5 to 880 Series Floor Boxes.

VSEAP5 AV Device Cover




Has one (1) duplex receptacle cutout and openings for two (2) Extron® Electronics AAP modules. Standard color/ material is anodized aluminum or black.

VSEA** **AV Device Cover**




Has openings for four (4) Extron® Electronics AAP modules. Standard color/ material is anodized aluminum or black.

VSEMP5 AV Device Cover




Has one (1) duplex receptacle cutout and openings for four (4) Legrand AVIP or Extron® Electronics MAAP modules. Standard color/material is anodized aluminum or black.

VSCR** **AV Device Cover**



Has openings for one (1) two-gang or two (2) singlegang Crestron® Quick Media wall plate(s). Standard color/ material is anodized aluminum or black.

VSEM** **AV Device Cover**



Has openings for four (4) Legrand AVIP or Extron® Electronics MAAP modules. Standard color/material is anodized aluminum or black.

- *Refer to the list of colors in th chart on the previous page for the four-digit code number.
- **Products are ETL Listed.

NOTE: If selecting VSEA, VSCR or VSEM Device Covers, such covers will allow for only A/V connectivity. No power outlets are accessible or available with these covers.



TELE-POWER® POLES



Tele-Power® Poles provides a cost-effective, configurable solution for distributing power and communication services to open spaces.




CODE REFERENCE

cULus Listed Multioutlet Assemblies: File E15191, E178348 Guide PVGT

Raceway Fittings: File E41751 Guide RJPR Accessories: File E53857 Guide RVUR Meets Article 380 & 386 of NEC.

Steel Tele-Power Poles Ordering Information





NOTE: Custom colors, other lengths
[20' [6.1m] max.) or additional
circuits are available on custom
order. Consult factory for more
information. Can be factory or field
wired with many commercially
available devices.



Tele-Power Poles provide a wide range of options for distributing services from overhead systems to open space office, commercial, and retail areas.

COLOR OPTIONS



25DTP/DTC Series Tele-Power Poles are now available in two colors: ivory and designer gray.

Custom color options are also available. Consult the factory for more information.



TELE-POWER® POLES

Steel Tele-Power Poles

25DTP Series Tele-Power Poles Wire Fill Capacities

	NO. & TYPE	NO. & TYPE POLE H			WIRE SIZE THHN/THWN		CAT 5		CAT 6		RG58/U		RG62A/U		RG62/U	
CATALOG NUMBER	OF POWER OUTLETS	Inches	mm	FINISH	#10	#12	0.22" 20%*	[5.6mm]	0.25" 20%*	[6.3mm] 40%**	0.195" 20%*	[5.0mm] 40%**	0.242" 20%*	[6.1mm] 40%**	0.270 20%*	[6.9mm] 40%**
25DTP-4	Two Duplex	10' 5"	[3.175m]	Ivory/Gray	10	15	10	19	9	17	13	25	8	16	7	13
25DTP-412		12' 5"	[3.780m]	Ivory/Gray	10	15	10	19	9	17	13	25	8	16	7	13
25DTP-415	Receptacles (20A, 125V)	15' 5"	[4.700m]	Ivory/Gray	10	15	10	19	9	17	13	25	8	16	7	13
25DTP-E10	(204, 1201)	10' 5"	[3.175m]	Ivory/Gray	10	15	10	19	9	17	13	25	8	16	7	13
25DTP-4 D		10' 5"	[3.175m]	Ivory/Gray	10	15	10	19	9	17	13	25	8	16	7	13
	Two Duplex Receptacles (20A, 125V), One Dedicated/ Isolated & One Standard Branch Circuit															
25DTP-4ACT		10' 5"	[3.175m]	Ivory/Gray	10	15	10	19	9	17	13	25	8	16	7	13
	Two Duplex Receptacles (20A, 125V), One Communications Insert Mounting Adapter, One Dual Cat 5e Insert, Two Blank Inserts & Labeling Supplies															

^{*20%} cable fill is calculated to approximate reduction in cable capacity due to connectors mounted within pole section that may restrict cross-sectional areas.

25DTP Series Tele-Power Poles Ordering Information

25DTP-4, 25DTP-4-DG Tele-Power Pole

25DTP-412, 25DTP-412-DG, 25DTP-415, 25DTP 415-DG

Two-compartment pole (power and communications). Nominal material thickness .030" [.8mm]. Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8" [203mm] cover at top front of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished. Available in standard lengths of 10' 5" [3.2m] [25DTP-41, 12' 5" [3.8m] (25DTP-412), and 15' 5" [4.7m] [25DTP-415]. Also increase the length of any 25 Series pole with the 25DTC-E5 Tele-Power Pole Extender.

25DTP-4ACT, 25DTP-4ACT-DG

Tele-Power Pole

Identical to 25DTP-4 except with one communications insert mounting adapter, one dual Cat 5e insert, two blank inserts and labels.

25DTP-4D, 25DTP-4D-DG Tele-Power Pole

Identical to 25DTP-4 except has one 20A 125V dedicated/isolated ground duplex receptacle and one 20A 125V standard duplex receptacle.

25DTP-E10, 25DTP-E10-DG

Tele-Power Pole

Two sections of a two-compartment (power and communication) pole [5' 4" [1.626m] base + 5' [1.524m] extender] assembles to form a 10' 4" [3.148m] pole. Nominal material thickness .040" [1.0mm]. Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8" [203mm] cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished.

25DTP-4-C, 25DTP-4-DG-C



Tele-Power Pole (Canada Only)

25DTP-412-C, 25DTP-412-DG-C, 25DTP-415-C. 25DTP-415-DG-C

Two-compartment pole (power and communications). Nominal material thickness .030" [.8mm]. Ivory or gray boot base. Factory wired with fed-spec general grade 15A 125V duplex style receptacles. An 8" [203mm] cover at top front of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors Mounting hardware, entrance end plate and two ceiling trim plates furnished. Available in standard lengths of 10' 5" [3.2m] (25DTP-41, 12' 5" [3.8m] (25DTP-412), and 15' 5" [4.7m] (25DTP-415). Comes with a 10' [3.0m] cord. Also increase the length of any 25 Series pole with the 25DTC-E5 Tele-Power Pole Extender.

^{**40%} cable fill is the maximum designed cable fill based on a proposed revision to TIA/EIA 569-A.

Steel Tele-Power Poles

- Standard of the industry; combines good looks, economy, and easy installation with sufficient capacity for expansion.
- Ivory enamel finish with matching 20A, 120V NEMA heavy duty duplex receptacles.
- Dedicated circuit pole features separate isolated ground circuit protection.
- Dual channel poles for communication cabling and power wiring accessibility.
- Modular jack knockouts and modular furniture outlets permit direct connections or use "mouse hole" grommet for direct cable feed.

T pole eserts.

25DTP-4ACT pole with additional inserts.

Receptacle Heig	hts
15.875" [403mm] 1" [25mm] 25DTP-4	
Power Commun	

Ordering Guide												
				FINISH	CAPACITY							
CATALOG NO.	OUTLETS	HE	IGHT				UTP					
25DTP-4 25DTP-412 25DTP-415	Two Duplex Receptacles (20A, 125V)	10'5" 12'5" 15'5"	[3.175m] [3.780m] [4.700m]		#10	#12	4-PR	25-PR				
25DTP-4ACT	Two Duplex Receptacles (20A, 125V) One Communications Insert Mounting Bezel, One Dual Cat 5e Insert, Two Blank Inserts and Labeling Supplies	10'5"	[3.175m]	lvory	10	15	15	6				
25DTP-4D	Two Duplex Receptacles (20A, 125V) One Dedicated/ Isolated and One Standard Branch Circuit	10'5"	[3.175m]	Ivory	10	15	15	6				
30TP-2V 30TP-212V	Two Duplex Receptacles	10'5" 12'5"	[3.175m] [3.780m]	Ivory	9	14	22	8				
30TP-4V 30TP-412V	(20A, 125V)	10'5" 12'5"	[3.175m] [3.780m]	lvory	18	18	30	11				
25AM10FO	5AM10FO 2" [51mm] radius control entrance fitting for 25DT and AMDT Series											

