GFCIs

Weather-Resistant Self-Test GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC





1597TRWRW

2097TRWRW

Features

- Weather-Resistant: Meets National Electrical Code® Weather-Resistant requirements.
- Tamper-Resistant: Meets National Electrical Code® Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Listed to the Weather-Resistant supplement of UL498 meeting demanding UL requirements including:
 - Ultraviolet light exposure test
 - Cold impact test
 - Accelerated aging test
 - Stringent material requirements for current carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the

indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box.
- Auto-Ground clip assures a positive ground to metal box.
- Meets 2015 UL requirements.
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).

- Trip indicator light (red LED)
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 10kA short circuit rating.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long nickel post-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trio Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

	RATING				3rd PARTY COMPLIANCE		
					£∰.us	£.₩Lus	
CATALOG NUMBER	Α.	VAC	COLOR	NEMA CONFIG. NO.	UL943 C22.2 No. 144	UL498 C22,2 No. 42	FSUL WC596
					C22.2 NO. 144	C22.2 No. 42	WC376
TRADEMASTER®/SPEC GRADE WEATHER-RESISTANT 15 AMP DUPLEX GFCI							
1597TRWRI	15	125	lvory	5-15R	•	•	•
1597TRWRW	15	125	White	5-15R	•	•	•
1597TRWR	15	125	Brown	5-15R	•	•	•
1597TRWRGRY	15	125	Gray	5-15R	•	•	•
1597TRWRBK	15	125	Black	5-15R	•	•	•
1597TRWRLA	15	125	Light Almond	5-15R	•	•	•
SPECIFICATION GRADE WEATHER-RESISTANT 20 AMP DUPLEX GFCI							
2097TRWRI	20	125	lvory	5-20R	•	•	•
2097TRWRW	20	125	White	5-20R	•	•	•
2097TRWR	20	125	Brown	5-20R	•	•	•
2097TRWRGRY	20	125	Gray	5-20R	•	•	•
2097TRWRBK	20	125	Black	5-20R	•	•	•
2097TRWRLA	20	125	Light Almond	5-20R	•	•	•





National Electrical Code® Section 406.8 Receptacles in Wet or Damp Locations.


Requires that all 15- and 20-amp, 125- and 250-volt non-locking receptacles installed in wet or damp locations shall be weather-resistant receptacles.



DEVICES & WALL PLATES

Color Selection Chart

Devices & Plastic Wall Plate Colors



See specific device and wall plate catalog charts for particular color availabilities.


Metal Wall Plates

Metal Finish



Custom Metal Wall Plates Paint Finish Colors

Paint Color



To order custom metal wall plates, see Pages P-40 - P-42.

For additional colors consult factory.