






GROUNDING & BONDING



Galvanized Ground Rod, Pointed



Featured Highlights

- Meets ANSI®/NEMA® GR1
- Zinc-coated exteriors are hot-dip galvanized for solid protection against corrosion, in accordance with ASTM® specification A153-78
- Surfaces are rigidly inspected to eliminate seams, slivers and other defects

Material: Steel
Finish: Hot-Dip Galvanized
Tensile Strength: 80,000 psi Min



Part Number	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual	Length	Unit Weight	UPC Label	Certifications
811260UPC	1/2"	0.507"	6'	4.1 lb	Yes	
811280UPC	1/2"	0.507"	8'	5.4 lb	Yes	
811350	1/2"	0.507"	5'	3.4 lb	No	
811360	1/2"	0.507"	6'	4.1 lb	No	
811380	1/2"	0.507"	8'	5.4 lb	No	
813400	3/4"	0.732"	10'	14.0 lb	No	CSA
813400UPC	3/4"	0.732"	10'	14.3 lb	Yes	
813480	3/4"	0.732"	8'	11.2 lb	No	
814400	1"	1.011"	10'	27.2 lb	No	CSA
815800	5/8"	0.631"	10'	10.6 lb	No	CSA
815800UPC	5/8"	0.631"	10'	10.6 lb	Yes	
815840	5/8"	0.631"	4'	4.2 lb	No	
815850	5/8"	0.631"	5'	5.3 lb	No	
815860	5/8"	0.631"	6'	6.4 lb	No	
815860UPC	5/8"	0.631"	6'	6.4 lb	Yes	
815880	5/8"	0.631"	8'	8.5 lb	No	
815880UPC	5/8"	0.631"	8'	8.4 lb	Yes	