



GFCIs


PlugTail™ Specification & Hospital Grade Tamper-Resistant Self-Test GFCI Receptacles with SafeLock™ Protection 2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



PT2097TRW



PT2097HGTRW



PTR65TR

Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3-wire PlugTail Connectors creating a non-feed-thru application for facility owners.
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.
- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box.
- Auto-Ground clip assures a positive ground to metal box.
- Meets 2015 UL requirements.
- 10kA short circuit rating.
- FSUL Listed (Federal Specification WC596).
- Exceed UL 943 voltage surge requirements survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE		
	A.	VAC			UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
SPECIFICATION GRADE TAMPER-RESISTANT 15 AMP DUPLEX GFCI							
PT1597TRI	15	125	Ivory	5-15R	•	•	•
PT1597TRW	15	125	White	5-15R	•	•	•
PT1597TR	15	125	Brown	5-15R	•	•	•
PT1597TRGRY	15	125	Gray	5-15R	•	•	•
PT1597TRBK	15	125	Black	5-15R	•	•	•
PT1597TRRED	15	125	Red	5-15R	•	•	•
PT1597TRLA	15	125	Light Almond	5-15R	•	•	•
SPECIFICATION GRADE TAMPER-RESISTANT 20 AMP DUPLEX GFCI							
PT2097TRI	20	125	Ivory	5-20R	•	•	•
PT2097TRW	20	125	White	5-20R	•	•	•
PT2097TR	20	125	Brown	5-20R	•	•	•
PT2097TRGRY	20	125	Gray	5-20R	•	•	•
PT2097TRRED	20	125	Red	5-20R	•	•	•
PT2097TRLA	20	125	Light Almond	5-20R	•	•	•
HOSPITAL GRADE TAMPER-RESISTANT 15 AMP DUPLEX GFCI							
PT1597HGTRI	15	125	Ivory	5-15R	•	•	•
PT1597HGTRW	15	125	White	5-15R	•	•	•
PT1597HGTRBK	15	125	Black	5-15R	•	•	•
PT1597HGTRRED	15	125	Red	5-15R	•	•	•
PT1597HGTRLA	15	125	Light Almond	5-15R	•	•	•
HOSPITAL GRADE TAMPER-RESISTANT 20 AMP DUPLEX GFCI							
PT2097HGTRI	20	125	Ivory	5-20R	•	•	•
PT2097HGTRW	20	125	White	5-20R	•	•	•
PT2097HGTRGRY	20	125	Gray	5-20R	•	•	•
PT2097HGTRGBK	20	125	Black	5-20R	•	•	•
PT2097HGTRRED	20	125	Red	5-20R	•	•	•
PT2097HGTRLA	20	125	Light Almond	5-20R	•	•	•



For PlugTail Connector catalog numbers, see Page C-13 or C-14.

ALL devices listed on this page conform to NEMA WD-1 and WD-6.