

## **Digital Light Meter**



- Measures incandescent, fluorescent, metal halide, high-pressure sodium and halogen lamp output.
- Color and cosine-corrected for enhanced accuracy.
- Measures up to 50,000 lux.
- · Peak and data hold means no lost measurements.
- Accessories included: (1) 9V battery and carrying case.
- Lifetime Limited Warranty

## SPECIFICATIONS

Ranges		
Foot Candles		0.01-5,000Fc (20/200/2,000/5,000)
Lux		0.1-50,000 lux (200/2,000/20,000/50,000)
Accuracy		
Incandescent Light Source		± 4%
Other Light Sources		±7%
Temperature Range		0° to 40° C (32° to 104° F)
Sampling Rate		2.5 times per second
CAT. NO.	UPC NO.	DESCRIPTION
93-172	06060	Digital Light Meter

93-172	06060	Digital Light Meter		
93-172-C*	07084*	Digital Light Meter		
06200	06200	Carrying Case		
06061	06061	Sensor		
06083	06083	Sensor Case		

\* includes Certificate of Calibration

R R R

## **Gas Lamp Tester**



- Test most fluorescent lamps, low pressure sodium vapor, high pressure sodium discharge lamps, neon tubes, mercury vapor and metal halide lamps.
- · Checks starters, resistors, ignitors, capacitors and photo cells.
- Indicates AC/DC voltage and continuity.
- Includes detachable antenna, batteries, leads, probes, clamps and holster.
- Lifetime Limited Warranty

## SPECIFICATIONS

Capacity	Voltage – up to 500 VAC & VDC; Continuity – to 300 kΩ
Size	6" x 2-3/4" x 1-3/4" (152 x 70 x 45 mm); Antenna – 27" (686 mm)
Weight	2.4 lbs. (1.1 kg)
Batteries	2-9V, included

	CAT. NO.	UPC NO.	DESCRIPTION
	5715	34529	Gas Lamp Tester
R	5713	34528	Holster
R	35450	35450	Battery Door
R	5710	34525	Antenna
R R R	5786	34574	Small Alligator Clamps (2)
R	5783	34556	Push-on Probes (2)