


Accessories for plastic enclosures




Contact block



Double contact block



Lamp blocks



Protective sleeve



Cable gland



Sealing ring



Blanking plugs

Description	Catalog number	Weight oz.
Contact block for rear mounting		
1NO	MCB-10B	0.46
1NC	MCB-01B	0.46
Double contact block		
2NO	MCB-20B	0.92
2NC	MCB-02B	0.92
1NO+1NC	MCB-11B	0.92
Contact block with gold plated contacts		
1NO	MCB-10BG	0.46
1NC	MCB-01BG	0.46
Lamp block for rear mounting		
For max. 2 W, 230 V AC and DC Filament Bulb or LED	MLB-1B	0.53
115 V AC supply voltage. For 60 V Filament Bulb 1.2 W	MLB-2B	0.60
230 V AC supply voltage. For 130 V Filament Bulb 2 W	MLB-3B	0.71
Protective sleeve		
Protective sleeve	5396 0543-1	0.071
Note: To make a rear mounted lamp block screen protected. IP20 (Not together with illuminated selector switch)		
Cable gland		
Grey plastic. Threaded outer sleeve sealing ring included.		
M25	MA5-3001	0.53
M20	MA5-3002	0.53
PG 13.5	MA5-3006	0.35
PG 16	MA5-3007	0.53
Nut		
Grey plastic. For cable gland above.		
M25	MA5-3003	0.18
M20	MA5-3004	0.18
PG 13.5	MA5-3008	0.035
PG 16	MA5-3009	0.035
Earthing Terminal		
For Plastic Enclosure.	MA5-3005	0.18
Sealing ring		
For plastic enclosure.	MA1-8150	0.035
Spacer		
1 mm thick. Needed when legend plates are not used in plastic enclosures.		
Spacer	SK 615 516-1	0.071
Spacer for modular emergency stop pushbutton	KA1-8045	0.14
Blanking plug		
Grey, 22mm	MA1-8129	0.18
Black, 22mm	MA1-8130	0.18
Black, 30mm	MA1-8133	0.18
Light grey, 22mm	MA1-8136	0.18
Adaptor		
PG 16/M20	MA5-3010	0.35