

Beacons

Flashing Xenon

92 Series

Edwards 92-N5 Series Xenon strobe beacons are light duty visual signals suitable for use in industrial, commercial and institutional applications where short term intermittent visual signaling is required. They feature brilliant light output and a cast base that can be utilized as a junction box. Optically designed fresnel lenses improve viewer perception for indoor and outdoor applications. Trigger and timing circuits are included as integral parts of the power supply. Replacement costs are reduced, as it is necessary to replace only the strobe tube.

Features and Specifications

- Xenon strobe light source
- Flash rate 65 fpm
- Cast base can function as a junction box
- Optically designed fresnel lenses
- Suitable for indoor and outdoor applications
- For outdoor use, lens should face up
- Option for panel, conduit or box mounting
- Designed for 4" octagonal box mounting
- Operating temperature range: -31°F to 150°F (-35°C to 65.6°C)



Ordering Information

Description	Cat. No.	Operating Voltage ¹	Current	Lens Colors	Peak Candela	Replacement	
						Lens	Strobe Tube
Xenon Strobe	92A-N5	120V AC	0.1 A	Amber	1,400,000	92-LA	
	92B-N5	120V AC	0.1 A	Blue	1,400,000	92-LB	
	92C-N5	120V AC	0.1 A	Clear	1,400,000	92-LC	
	92G-N5	120V AC	0.1 A	Green	1,400,000	92-LG	92-LST
	92M-N5	120V AC	0.1 A	Magenta	1,400,000	92-LM	5,000 hour ²
	92R-N5	120V AC	0.1 A	Red	1,400,000	92-LR	

¹AC voltage frequency is 50/60 Hz

²Calculated at operating power to 75% efficiency.

Accessories

Description	Cat. No.
Corner Mount Bracket	CBR
Wall Mount Bracket	WBR
Lens Guard	92-GRD



CBR
Corner Mount Bracket



WBR
Wall Mount Bracket



92-GRD
Lens Guard



Beacons

Flashing Xenon

92 Series

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
92*-N5	1.60	1.93
CBR	4.00	4.20
WBR	2.30	2.50
92-GRD	0.31	0.47

*Letter in this position designates lens color: A - amber, B - blue, C - clear, G - green, M - magenta or R - red

