# SCEPTER JBOX

Scepter JBox

Scepter<sup>®</sup> JBox<sup>™</sup>, the Next Generation Junction Box. The original junction box is completely redesigned and new features have been added to make this the easiest box to use. The patent pending integral gasket, nonmetallic fasteners, molded mounting feet, embossed grid-lines and flat cover features have been engineered to provide a contractor-friendly junction box.

# **ADVANTAGES**

2

3)

(4)

(5)

# **Zero Footprint**

Design allows for installation in corners and immediately adjacent to other products. There is easy access to all mounting feet and fasteners.

# Installing Overhead

Integral fasteners allow for easy overhead positioning and securing.

# Mounting in a Cover

Pilot lights, control switches and other devices are easily mounted. The Cover is free and clear of supporting ribs, and has a uniform thickness.

# **Added Security**

Sizes 6" and larger feature a lock-out option. Tie-wrap, tamper resistant bolt or padlock will restrict access to the box.

# More Interior Volume

Increased space from wire pulling and for ease of bend radius. The increased cubic inch volume allows for more flexibility

# APPLICATIONS

- Corrosive environments
- Waste-water treatment facilities
- Marine & car washes
- Agricultural Wash down

# **STANDARDS**

### **NEMA Rated**

1, 2, 3R, 4, 4X, 6\*, 6P\*, 12, 13 \*Applies only to 4" to 12" non-hinged covers

**CSA** Listed CSA C22.2 No. 40 CSA C22.2 No. 85 UL 50 / CSA C22.2 No. 94.1 UL 50E / CSA C22.2 No. 94.2



JBOX CEPTER

30

# SHORT FORM SPECIFICATIONS

Junction boxes shall be acceptable for indoor and outdoor use and manufactured of PVC in a gray color analogous to Rigid PVC conduit and fittings. The junction box and its fasteners, hinges or components shall be entirely non-metallic. Boxes shall be NEMA rated and certified to bi-national standard UL50/50E - CSA No.94.1/94.2 by a Nationally Recognized Testing Laboratory (i.e. UL or CSA).

The cover/box gasket shall be dual-molded or permanently fixed so as to be an integrated part of the cover. The cover should be secured to the box using non-metallic quarter-turn "close by hand,

tool assist to open" fasteners. To aid in the alignment and proper positioning of conduit connections the box/enclosure shall have embossed gridlines on the sidewalls. The mounting feet shall be a permanent molded feature of the box and not extend beyond the periphery of the box/enclosure. On boxes/enclosures of nominal size 6" x 6" and larger, back-panel / DIN rail mounting and pad-lock provisions shall be incorporated into the product.

Acceptable manufacturer: IPEX (Scepter JBox Series)

# SMOOTH FLAT COVER

• No engravings

- No ribs offers a flat, smooth surface for mounting of devices or labels
- HAND-CLOSE FASTENERS
- Close by hand tool assist to open
- 100% non-metallic corrosion resistant material
- No loose hardware for easy installation

# 

- Available on sizes 6" to 16"
- Use a tie-wrap, bolt or padlock for added security

# LEAK-FREE INTEGRATED GASKET


- Injection molded and extruded gaskets permanently fixed to the cover – no installation required
- Proprietary gasket material creates a 6P rated enclosure (4" – 12")
- Neoprene gasket material creates a 4X rated enclosure (14" 16")

# **GRIDLINES FOR DRILLING**

- Easy reference for drilling knockouts
- Makes conduit alignment a snap
- Indicates a "drill zone"

# MOLDED MOUNTING FEET

- Molded no loose parts to assemble
- Located on corners out of the way of conduit connections
- Flush with the back of the box for close surface mounting
- Integrated design of mounting feet offers improved strength



# POLE MOUNTING KIT

- One kit fits 4" to 12" new Scepter JBoxes (PMK4-12)
- Supplied as a complete kit

ZG.

- Works with wood, concrete, steel and composite poles
- Installs on round, square & octagonal poles up to 15" diameter

### **BACK PANEL**


- Designed to fit sizes 6" and 16"
- Made of 14 gauge carbon steel
- White epoxy powder-coated finish
- Easy to cut and drill to mount devices



# **JUNCTION BOXES**

Scepter's **FLANGED 'H' SERIES JUNCTION BOXES** provide H10 Highway Loading equivalent to handling a 50 psi load. The fiber-reinforced safety tread cover secures using recessed Hex Key fastening hardware offering a simple installation while reducing the opportunity for tampering. These boxes are not UL Certified and are not returnable.

| Part   | Product | Box | (ID (inch |       |      | iensions (i |      | Volume |
|--|---------|-----|-----------|-------|------|-------------|------|--------|
| Number   | Code    | L   | W         | D     | A    | В           | C    | (in³)  |
| Flanged Box w Fire-reinforced Safety Tread Cover |         |     |           |       |      |             |      |        |
| H664   | 077685  | 6   | 6         | 4-1/4 | 9.0  | 9.0         | 0.60 | 138.0  |
| H666   | 077686  | 6   | 6         | 6-1/4 | 9.0  | 9.0         | 0.60 | 211.0  |
| H884   | 077687  | 8   | 8         | 4-1/4 | 11.5 | 11.5        | 0.75 | 248.0  |
| H886   | 077688  | 8   | 8         | 6-1/4 | 11.5 | 11.5        | 0.75 | 434.0  |
| H887   | 077689  | 8   | 8         | 7-1/4 | 11.5 | 11.5        | 0.75 | 434.0  |
| H887-A   | 077692  | 8   | 8         | 7-1/4 | 11.5 | 11.5        | 0.75 | 434.0  |



| Size<br>(inches)      | Part<br>Number | Product<br>Code |  |  |  |  |  |
|-----------------------|----------------|-----------------|--|--|--|--|--|
| Junction Box Adapters |                |                 |  |  |  |  |  |
| 1/2                   | JBA10          | 077721          |  |  |  |  |  |
| 3/4                   | JBA15          | 077722          |  |  |  |  |  |
| 1                     | JBA20          | 077723          |  |  |  |  |  |
| 1-1/4                 | JBA25          | 077724          |  |  |  |  |  |
| 1-1/2                 | JBA30          | 077725          |  |  |  |  |  |
| 2                     | JBA35          | 077726          |  |  |  |  |  |
| 2-1/2                 | JBA40          | 077727          |  |  |  |  |  |
| 3                     | JBA45          | 077728          |  |  |  |  |  |
| 3-1/2                 | JBA50          | 077729          |  |  |  |  |  |
| 4                     | JBA55          | 077730          |  |  |  |  |  |



37