


Industrial grade 50A locking devices

Product description


3-pole, 4-wire grounding
50A, 125/250V/AC
Non-NEMA, California standard



CS6365EX



CS6364EX



CS6376

California standard plugs & connectors

Rating	A	V/AC	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
50	125/250		Pro grip nylon	0.44-1.06" (11.1-26.0mm)	RD & BK	<input type="checkbox"/> CS6365EX	<input type="checkbox"/> CS6364EX	•	•
			Armored	0.68-1.13" (17.3-28.6mm)	Steel	<input type="checkbox"/> CS6365		•	•
			Armored	0.68-1.13" (17.3-28.6mm)	Steel		<input type="checkbox"/> CS6364	•	•

California standard grade receptacles

Rating	A	V/AC	Description	Color	Single receptacle		
50	125/250		California standard receptacles	BK	<input type="checkbox"/> CS6369	•	•

California standard flanged inlets

Rating	A	V/AC	Description	Color	Flanged inlet	Flanged inlet w/ lid		
50	125/250		California standard flanged inlets	Steel	<input type="checkbox"/> CS6375	<input type="checkbox"/> CS6376	•	•

Accessories for 50A California standard locking devices

Description	Color suffix	Catalog no.		
Weather protective glass-filled nylon, w/ lift lid cover	BK, CR, GY	<input type="checkbox"/> 7788__	•	•
Weather protective diecast aluminum, w/ lift lid cover		<input type="checkbox"/> 7770	•	
Weather protective boot for 50A armored plug		<input type="checkbox"/> 7716	•	
Weather protective boot for 50A armored connector		<input type="checkbox"/> 7717	•	
Weather protective boot for 50A pro grip plug		<input type="checkbox"/> 7716EX	•	
Weather protective boot for 50A pro grip connector		<input type="checkbox"/> 7717EX	•	



7788CR
Corrosion resistant



7770



7716



7717



7716EX



7717EX

Dimensional information:
C-80, C-81

Plug & connector specification information:
50A: C-92

Receptacle specification information:
50A: C-92

Flanged inlet & flanged outlet specification information:
50A: C-92

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: BK (Black), GY (Gray), RD (Red), Y or CR (Yellow)



Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32

Poles, wires	Rating	10A - 30A Non-NEMA locking	
		Receptacle, connector, & flanged outlet	Plug & flanged inlet
3-pole, 3-wire	10/15A 125/250V/AC	4755 ◊L 7565N ◊N 7580 □ 7582 Δ	4767 ◆L 4767AN ◆AL 7567N ◆N
	20A 125/250V/AC	7310B Δ 7314C ◊L 7314CW ◊W 7314CY ◊Y 7314RW ΔW 7328N ○	7327N ● 9965C ◆L 9965PW ◆W 9965PY ◆Y
	30A 125/250V/AC	3330-2 Δ 3333CW ◊W 3333CY ◊Y 3333RW ΔW AH3333N ◊U 3336N ○	AH3331N ◆U 3331PW ◆W 3331PY ◆Y 3337N ●
4-pole, 4-wire	20A 3Ø 120/208V/AC	7409N ○ 7410B Δ 7413C ◊L 7413CW ◊W 7413CY ◊Y 7413RW ΔW	7408N ● 7411C ◆L 7411PW ◆W 7411PY ◆Y
	30A 3Ø 120/208V/AC	3430 Δ 3433CW ◊W 3433CY ◊Y AH3433N ◊U 3433RW ΔW 3436N ○	AH3431N ◆U 3431PW ◆W 3431PY ◆Y 3434N ●
4-P, 5-W grounding	20/10A 250/600V/AC	AH3523BK ◊U 3525BK ○	AH3521BK ◆U 3524BK ●

Poles, wires	Rating	50A Non-NEMA locking	
		Receptacle & connector	Plug, flanged inlets & hull inlet
2-pole, 3-wire grounding	125V/AC Marine corrosion resistant	63CR60EX ◊P 63CR60 ◊T 63CR70 Δ	63CR61EX ◆P 63CR61 ◆T
	125V/AC California standard	CS6360EX ◊P CS6360 ◊T CS6370 Δ	CS6361EX ◆P CS6361 ◆T CS6377 ● CS6378 ●Z
	250V/AC California standard	CS8264EX ◊P CS8264 ◊T CS8269 Δ	CS8265EX ◆P CS8265 ◆T CS8275 ● CS8277 ●Z
	250V/DC 600V/AC	3762EX ◊P 3762 ◊T 3771 Δ	3763EX ◆P 3763 ◆T 3777 ● 3767 ●Z
	480V/AC California standard	CS8464EX ◊P CS8464 ◊T CS8469 Δ	CS8465EX ◆P CS8465 ◆T CS8475 ● CS8477 ●Z
3-pole, 4-wire grounding	125/250V/AC Marine corrosion resistant	63CR64EX ◊P 63CR64 ◊T 63CR69 Δ	63CR65EX ◆P 63CR65 ◆T
	125/250V/AC California standard	CS6364EX ◊P CS6364 ◊T CS6369 Δ	CS6365EX ◆P CS6365 ◆T CS6375 ● CS6376 ●Z
	3Ø 250V/AC California standard	CS8364EX ◊P CS8364 ◊T CS8369 Δ	CS8365EX ◆P CS8365 ◆T CS8375 ● CS8377 ●Z
	250V/DC 600V/AC	3764EX ◊P 3764 ◊T 3769 Δ	3765EX ◆P 3765 ◆T 3775 ● 3768 ●Z
	250V/DC 600V/AC	7764EX ◊P 7764 ◊T 7379 Δ	7765EX ◆P 7765 ◆T 7958 ● 7968 ●Z
	3Ø 480V/AC California standard	CS8164EX ◊P CS8164 ◊T CS8169 Δ	CS8165EX ◆P CS8165 ◆T CS8175 ● CS8177 ●Z

Locking device legend: How to use the chart

Core catalog number color indicates a device's grade:

BLACK = Industrial specification grade

A suffix combining a **RED** shape and alpha letter indicate a device's body, type and available options.

Device body:

- Duplex receptacle
 - △ Single receptacle
 - ◆ Plug
 - ◊ Connector
 - Flanged inlet
 - Flanged outlet
 - Hull inlet
 - Mechanical interlock
- Open shape** has holes (receptacles, connectors, outlets)
Closed shape has blades (plugs, inlets)

Device type:

- A** Angled
- C** Corrosion resistant
- L** Safety grip
- N** Auto grip
- P** Pro grip
- T** Armored body
- U** Ultra grip
- W** Watertight
- Y** Severe duty insulated
- Z** With lid or cover