

### Controlled Cycle Crimping Tools – Ferrule End Sleeve

- Specifically designed for the installation of Pan-Term® Ferrules
- Controlled cycle mechanism assures high quality, consistent terminations
- Ergonomic tool design assures operator comfort, safety, and performance
- Multi-position locator facilitates a high quality repeatable crimp



CT-1002



CT-1003



CT-1004



CT-1005



CT-1006



CT-1104



CT-1123



CT-1090



CT-1160



CT-1170



Part Number	Part Description	Std. Pkg. Qty.
CT-1002	Controlled cycle crimp tool with trapezoid profile for #26 – 10 AWG (0.14 – 6.0mm <sup>2</sup> ) insulated and non-insulated single wire ferrules and #22 – 12 AWG (0.50 – 4.0mm <sup>2</sup> ) insulated twin wire ferrules.	1
CT-1003	Controlled cycle crimp tool with trapezoid profile for #22 – 8 AWG (0.50 – 10.0mm <sup>2</sup> ) insulated and non-insulated ferrules and #22 – 10 AWG (0.50 – 6.0mm <sup>2</sup> ) insulated twin wire ferrules.	1
CT-1004	Controlled cycle crimp tool with trapezoid profile for #8 – 6 AWG (10.0 – 16.0mm <sup>2</sup> ) insulated and non-insulated ferrules and #10 AWG (6.0mm <sup>2</sup> ) insulated twin wire ferrules.	1
CT-1005	Controlled cycle crimp tool with trapezoid profile for #4 – 2 AWG (26.0 – 35.0mm <sup>2</sup> ) insulated and non-insulated ferrules.	1
CT-1006	Controlled cycle crimp tool with trapezoid profile for #1 AWG (50.0mm <sup>2</sup> ) insulated and non-insulated ferrules.	1
CT-1104	Controlled cycle crimp tool with square profile for #8 – 6 AWG (10.0 – 16.0mm <sup>2</sup> ) insulated and non-insulated ferrules and #10 AWG (6.0mm <sup>2</sup> ) insulated twin wire ferrules.	1
CT-1123	Controlled cycle crimp tool with square profile for #26 – 8 AWG (0.14 – 10.0mm <sup>2</sup> ) insulated and non-insulated ferrules and #22 – 12 AWG (0.50 – 4.0mm <sup>2</sup> ) insulated twin wire ferrules.	1
CT-1160	Controlled Cycle Ferrule Crimp Tool with Hexagon profile for 28-5 AWG (0.08 - 16 mm <sup>2</sup> ) insulated and non-insulated single wire ferrules and 23-10 AWG (2 x 0.25mm <sup>2</sup> - 2x 6mm <sup>2</sup> ) insulated twin ferrules.	1
CT-1170	Controlled Cycle Ferrule Crimp Tool with Square profile for 28-5 AWG (0.08 - 16 mm <sup>2</sup> ) insulated and non-insulated single wire ferrules and 23-10 AWG (2 x 0.25mm <sup>2</sup> - 2x 6mm <sup>2</sup> ) insulated twin ferrules.	1
CT-1090	Controlled Cycle Ferrule Crimp tool with square profile for #26 - 10 AWG (0.14-6.0mm <sup>2</sup> ) insulated and non-insulated single wire ferrules and #22 - 12 AWG (0.05 - 4.0mm <sup>2</sup> ) insulated twin ferrules.	1

A.  
Cable  
Ties

B.  
Stainless  
Steel

C.  
Wiring  
Duct

D.  
Terminals  
and  
Reel  
Smart™  
System

E.  
Power  
Connectors  
and  
Grounding

F.  
Part  
Number  
Index