


STRAIGHT BLADE RECEPTACLES

Tamper-Resistant Nightlight/GFCI Receptacles 2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1595NLTTRWCC4 2095HGNTLTRW


Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- LED rated at 186 milliwatts at 120V.
- Two receptacles.
- Photocell turns nightlight ON in dark, OFF in daylight.
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 - #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 10 kA short circuit rating.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate (except NI, AB, and DB models).
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

CATALOG NUMBER	RATING		LIGHT OUTPUT IN 1' FCD*	COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE		
	A.	VAC				UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
COMBINATION TAMPER-RESISTANT 15 AMP NIGHTLIGHT/GFCI								
1595NLTTRICC4	15	125	0.180	Ivory	5-15R	•	•	•
1595NLTTRWCC4	15	125	0.180	White	5-15R	•	•	•
1595NLTTRBKCC4	15	125	0.180	Black	5-15R	•	•	•
1595NLTTRLACC4	15	125	0.180	Light Almond	5-15R	•	•	•
1595NLTTRNICC4	15	125	0.180	Nickel	5-15R	•	•	•
1595NLTTRABCC4	15	125	0.180	Antique Brass	5-15R	•	•	•
1595NLTTRDBCC4	15	125	0.180	Dark Bronze	5-15R	•	•	•
COMBINATION TAMPER-RESISTANT 20 AMP NIGHTLIGHT/GFCI								
2095NLTTRI	20	125	0.180	Ivory	5-20R	•	•	•
2095NLTTRW	20	125	0.180	White	5-20R	•	•	•
2095NLTTRGRY	20	125	0.180	Gray	5-20R	•	•	•
2095NLTTRLA	20	125	0.180	Light Almond	5-20R	•	•	•
HOSPITAL GRADE COMBINATION TAMPER-RESISTANT 15 AMP NIGHTLIGHT/GFCI								
1595HGNTLTRI	15	125	0.180	Ivory	5-15R	•	•	•
1595HGNTLTRW	15	125	0.180	White	5-15R	•	•	•
1595HGNTLTR	15	125	0.180	Brown	5-15R	•	•	•
1595HGNTLTRRED	15	125	0.180	Red	5-15R	•	•	•
HOSPITAL GRADE COMBINATION TAMPER-RESISTANT 20 AMP NIGHTLIGHT/GFCI								
2095HGNTLTRI	20	125	0.180	Ivory	5-20R	•	•	•
2095HGNTLTRW	20	125	0.180	White	5-20R	•	•	•
2095HGNTLTRGRY	20	125	0.180	Gray	5-20R	•	•	•
2095HGNTLTRRED	20	125	0.180	Red	5-20R	•	•	•
2095HGNTLTRLA	20	125	0.180	Light Almond	5-20R	•	•	•



*FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See Page R-68 for more information.

All devices listed on this page conform to NEMA WD-1 and WD-6.

DEVICES & WALL PLATES

Color Selection Chart

Devices & Plastic Wall Plate Colors



Ivory Light Almond White Green Antique Brass Dark Bronze Nickel



Black Blue Brown Gray Orange Red

See specific device and wall plate catalog charts for particular color availabilities.

Metal Wall Plates

Metal Finish



Aluminum Brass (Brushed) Polished Brass Stainless Steel Brushed Bronze Chrome

Custom Metal Wall Plates Paint Finish Colors

Paint Color



Orange Green Gray Yellow Glossy Black Brown White



Primer Red Pink Flat Black Ivory Light Almond Blue

To order custom metal wall plates, see Pages P-40 - P-44.

For additional colors consult factory.