

Switches

Heavy Duty Safety Switches

Type 4/4X & 12 with Viewing Window

Description





30–600A, 3-pole 600V max. in fusible and non-fusible versions in Type 4/4X stainless steel and Type 12 enclosures.

All allow viewing of visible blade position. 30–200A also allow viewing of indicating type fuses.

Features

- Rugged installer-friendly enclosure design features a gasket flange with continuously welded seams
- Tool-free cover latches
- Two, three and four point mounting
- Metal handle with large insulating grip features a positive stop in both ON and OFF position
- Ground lugs provided as standard
- Type 12 enclosures are fabricated from galvanized steel and are also rated for 3R/3S outdoor applications
- Type 4X stainless steel switches (30–200A) are provided with stainless steel interior parts
- The widest range of accessories available including 200% neutrals, gold plated PLC auxiliary contacts and isolated ground kits



System	Ampere Rating	Catalog Number	List Price \$	Ship. Weight ^①	Maximum Horsepower Ratings ^③					
					240V AC		480V AC	600V AC	250V	600V
					1 Phase, 2 Wire	3 Phase, 3 Wire	3 Phase, 3 Wire	3-Phase, 3 Wire	DC	DC
3-Pole, 3 Wire Fusible, Type 12 ^{④⑤}					600 Volt AC / 250 Volt DC ^②					
	30	HFC361JW		17	3	7 1/2	15	20	5	—
	60	HFC362JW		22	10	15	30	50	10	30 ^⑥
	100	HFC363JW		26	15	30	60	75	20	50 ^⑥
	200	HFC364JW		53	—	60	125	150	40	50
	400	HFC365JW		166	—	125	250	350	50	—
	600	HFC366JW		168	—	200	400	500	50	—
3-Pole, 3 Wire Non-Fusible, Type 12 ^{④⑤}					600 Volt AC / 250 Volt DC ^②					
	30	HNFC361JW		14	3	10	20	30	5	—
	60	HNFC362JW		21	10	20	50	60	10	30 ^⑥
	100	HNFC363JW		25	15	40	75	100	20	50 ^⑥
	200	HNFC364JW		51	15	60	125	150	40	50
	400	HNFC365JW		133	15	125	250	350	50	—
	3-Pole, 3 Wire Fusible, Type 4X Stainless Steel ^⑤					600 Volt AC / 250 Volt DC ^②				
	30	HFC361SW		17	3	7 1/2	15	20	5	—
	60	HFC362SW		23	10	15	30	50	10	30 ^⑥
	100	HFC363SW		28	15	30	60	75	20	50 ^⑥
	200	HFC364SW		55	—	60	125	150	40	50
	400	HFC365SW		168	15	125	250	350	50	—
	3-Pole, 3 Wire Non-Fusible, Type 4X Stainless Steel ^⑤					600 Volt AC / 250 Volt DC ^②				
	30	HNFC361SW		15	3	10	20	30	5	—
	60	HNFC362SW		23	10	20	50	60	10	30 ^⑥
	100	HNFC363SW		27	15	40	75	100	20	50 ^⑥
	200	HNFC364SW		54	15	60	125	150	40	50
	400	HNFC365SW		134	15	125	250	350	50	—

① In pounds (lbs).

② 200A switches are also rated 600V DC.

③ Maximum HP ratings listed apply only when time delay fuses are used.

④ Also rated 3S/3R for outdoor use.

⑤ All switches are suitable for use as service entrance equipment. Use outside poles of 3-pole switch for 2-pole application.

⑥ 600V DC and 600V DC horsepower rating shown requires (2) poles to be connected in series.