# A100P Amp-Trap<sup>®</sup> Form 101

A100P Amp-Trap<sup>®</sup> Form 101 Semiconductor Protection fuses are rated 1000V, extending the range of protection for UPS systems, AC and DC drives, reduced voltage motor starters and similar applications where lower l<sup>2</sup>t and superior reliability are needed. With ratings from 15 through 1000 amperes, a wide range of high voltage applications can be served.

### Features/Benefits:

- Low I<sup>2</sup>t minimizes damage to protected components on short circuit
- · Controlled arc voltage reduces stress to circuit components during fuse clearing
- Wide range of ampere ratings

### **Highlights**:

- Fast acting
- Current limiting
- Low I<sup>2</sup>t
- Optional trigger indicator

### **Applications:**


 Protection of UPS systems AC/ DC drives, reduced voltage motor starters and other 1000V or less semiconductor devices



#### Ratings:

| Volts | : 1000VAC     |
|-------|---------------|
|       | : 750VDC      |
| Amps  | : 15 to 1000A |
| I.R.  | : 100kA I.R.  |
| L/R   | : 25ms        |

### **Catalog Numbering System**



\* For ampere ratings and styles not listed, call Technical Services at 978-465-4853.

## Single Pole Fuse Blocks for A100P Fuses

| Fuse Ampere<br>Rating | Fuse Block<br>Catalog No. |
|-----------------------|---------------------------|
| 35-100                | P266G                     |
| 125-400               | P266L                     |



### Approvals:

- UL recognized component File E60314
- AC: UL guide no. JFHR2 (35-600A)
- DC: self-certified





## A100P Amp-Trap<sup>®</sup> Form 101


### Catalog Numbers (amps)

| Catalog No. | Dimen. Fig. | Catalog No.  | Dimen. Fig. | Catalog No.  | Dimen. Fig. |
|-------------|-------------|--------------|-------------|--------------|-------------|
| A100P15-1   | 1           | A100P100-4   | 2           | A100P350-4TI | 2           |
| A100P20-1   | 1           | A100P100-4TI | 2           | A100P400-4   | 2           |
| A100P25-1   | 1           | A100P125-4   | 2           | A100P400-4TI | 2           |
| A100P30-1   | 1           | A100P125-4TI | 2           | A100P500-4   | 3           |
| A100P35-4   | 2           | A100P150-4   | 2           | A100P500-4TI | 3           |
| A100P40-4   | 2           | A100P150-4TI | 2           | A100P600-4   | 3           |
| A100P50-4   | 2           | A100P200-4   | 2           | A100P600-4TI | 3           |
| A100P50-4TI | 2           | A100P200-4TI | 2           | A100P650-4   | 4           |
| A100P60-4   | 2           | A100P225-4   | 2           | A100P700-4   | 4           |
| A100P60-4TI | 2           | A100P250-4   | 2           | A100P800-4   | 4           |
| A100P70-4TI | 2           | A100P300-4   | 2           | A100P800-4TI | 4           |
| A100P80-4   | 2           | A100P300-4TI | 2           | A100P1000-4  | 5           |
| A100P80-4TI | 2           | A100P350-4   | 2           |              |             |

\* For ampere ratings and styles not listed, call Technical Services at 978-465-4853.

### Dimensions

|                            |        | Fire | Dimensions - Inches (mm) |        |        |       |       |        |        |        |        |
|----------------------------|--------|------|--------------------------|--------|--------|-------|-------|--------|--------|--------|--------|
| Outline Ref. Mounting Type | Fig.   | Α    | в                        | С      | D      | Е     | F     | G      | н      | J      |        |
| A100P15 to 30              | 1      | 1    | 2.63                     | 0.56   | -      | -     | -     | -      | -      | -      | -      |
|                            |        |      | (66.8)                   | (14.2) | -      | -     | -     | -      | -      | -      | -      |
| A100P35 to 60              | 4, 4TI | 2    | 5.00                     | 1.00   | 3.50   | 4.31  | 4.19  | 0.31   | 0.75   | 0.13   | -      |
|                            |        |      | (127)                    | (25.4) | (173)  | (109) | (106) | (7.9)  | (19.1) | (3.3)  | -      |
| A100P65 to 100             | 4, 4TI | 2    | 5.00                     | 1.22   | 3.50   | 4.31  | 4.19  | 0.31   | 1.00   | 0.19   | -      |
|                            |        |      | (127)                    | (31.0) | (173)  | (109) | (106) | (7.9)  | (25.4) | (4.8)  | -      |
| A100P125 to 200            | 4, 4TI | 2    | 5.72                     | 1.50   | 3.47   | 4.78  | 4.16  | 0.41   | 1.00   | 0.25   | -      |
|                            |        |      | (145)                    | (38.1) | (88.1) | (121) | (106) | (10.4) | (25.4) | (6.4)  | -      |
| A100P225 to 400            | 4, 4TI | 2    | 5.72                     | 2.00   | 3.47   | 4.78  | 4.16  | 0.41   | 1.50   | 0.25   | -      |
|                            |        |      | (145)                    | (50.8) | (88.1) | (121) | (106) | (10.4) | (25.4) | (6.4)  | -      |
| A100P500 to 600            | 4, 4TI | 3    | 7.72                     | 2.50   | 3.47   | 5.88  | 5.56  | 0.53   | 2.00   | 0.38   | -      |
|                            |        |      | (196)                    | (63.5) | (88.1) | (149) | (141) | (13.5) | (50.8) | (9.7)  | -      |
| A100P650 to 800            | 4, 4TI | 4    | 7.44                     | 2.88   | 3.94   | 5.94  | -     | 0.63   | 2.00   | 0.38   | -      |
|                            |        |      | (189)                    | (73.2) | (100)  | (151) | -     | (16.0) | (50.8) | (9.7)  | -      |
| A100P1000                  | 4      | 5    | 8.22                     | 3.38   | 4.47   | 6.59  | 5.84  | 0.63   | 2.75   | 0.50   | 1.38   |
|                            |        |      | (209)                    | (85.9) | (114)  | (167) | (148) | (16.0) | (69.9) | (12.7) | (35.1) |








Figure 1





Figure 2

Figure 3



For the most current product performance data visit ep-us.mersen.com and use catalog search.