


HOLE SAWS

Bi-Metal Hole Saws



- Cut through steel, tin, aluminum, fiberglass, wood and plastic.
- Deep 1-5/8" (41.3 mm) cutting depth allows for cutting through 2" x 4" wood studs.
- Extra-tough bi-metal blade – we use the highest grade of tool steel to outlast competitor's blades. That beats premature saw replacement and saves you money.
- Steam oxide finish – no paint to gum up and slow cutting. The saw runs cooler for longer life and better performance.
- Extra-thick backplate minimizes vibration for smoother, easier, less tiring cutting.
- Made in USA

CAT. NO.	UPC NO.	ACTUAL HOLE SIZE		HOLE DIA.			COPPER PIPE SIZE	USE WITH QUICK CHANGE ARBOR NO.	USE WITH STD. ARBOR NO.	WEIGHT	
		INCH	MM	CONDUIT	PG	ISO				LBS.	G
825-9/16	19131	9/16	14.3				1/8"	02800*	37157, 37155, or 38522	.1	46
825-5/8	19132	5/8	15.9		Pg-9		1/4"			.1	46
825-11/16	19133	11/16	17.5			ISO-16	3/8"			.1	46
825-3/4	19134	3/4	19.0		Pg-11		1/2"			.1	46
825-13/16	19135	13/16	20.6		Pg-13	ISO-20	1/2"			.1	46
825-7/8	19136	7/8	22.2	1/2"	Pg-16		5/8"			.1	46
825-15/16	19137	15/16	23.8							.1	46
825-1	19138	1	25.4			ISO-25	3/4"			.1	46
825-1-1/16	19140	1-1/16	27.0							.1	46
825-1-1/8	19141	1-1/8	28.6	3/4"	Pg-21		3/4"			.1	46
825-1-3/16	19143	1-3/16	30.2					02801*	37156 or 37154	.2	91
825-1-1/4	19144	1-1/4	31.7				1"			.2	91
825-1-5/16	19145	1-5/16	33.3			ISO-32				.2	91
825-1-3/8	19146	1-3/8	35.0	1"						.1	46
825-1-7/16	19147	1-7/16	36.5		Pg-29					.2	91
825-1-1/2	19148	1-1/2	38.1				1-1/4"			.2	91
825-1-9/16	19149	1-9/16	39.7							.2	91
825-1-5/8	19150	1-5/8	41.3			ISO-40				.2	91
825-1-11/16	19151	1-11/16	42.9							.3	137
825-1-3/4	19152	1-3/4	44.4	1-1/4"			1-1/2"			.2	91
825-1-13/16	19153	1-13/16	46.0					02801*	37156	.2	91
825-1-7/8	19154	1-7/8	47.6		Pg-36					.3	137
825-2	19155	2	50.8	1-1/2"		ISO-50				.2	91
825-2-1/16	19157	2-1/16	52.4							.3	137
825-2-1/8	19158	2-1/8	54.0		Pg-42					.3	137
825-2-1/4	19159	2-1/4	57.2				2"			.3	137
825-2-5/16	19160	2-5/16	58.7							.5	227
825-2-3/8	19161	2-3/8	60.3		Pg-48		2"			.3	137
825-2-1/2	19162	2-1/2	63.5	2"		ISO-63	2"			.3	137
825-2-9/16	19163	2-9/16	65.0							.4	182
825-2-5/8	19164	2-5/8	66.7					02801*	37156	.4	182
825-2-3/4	19165	2-3/4	69.8							.4	182
825-2-7/8	19166	2-7/8	73.0							.4	182
825-3	19167	3	76.2	2-1/2"			2-1/2"			.5	227
825-3-1/8	19168	3-1/8	79.4							.5	227
825-3-1/4	19169	3-1/4	82.5							.6	273
825-3-3/8	19170	3-3/8	85.7							.6	273
825-3-1/2	19171	3-1/2	88.9							.6	273
825-3-5/8	19172	3-5/8	92.1	3"						.6	273
825-3-3/4	19174	3-3/4	95.2							.7	318
825-3-7/8	19175	3-7/8	98.4				3-1/2"	02801*	37156	.7	318
825-4	19176	4	101.6							.7	318
825-4-1/8	19177	4-1/8	104.8	3-1/2"			3-1/2"			.8	363
825-4-1/4	19178	4-1/4	108.0				4"			.8	363
825-4-3/8	19179	4-3/8	111.1							.8	363
825-4-1/2	19180	4-1/2	114.3	4"						.9	409
825-4-3/4	19181	4-3/4	120.6							1.1	499
825-5	19182	5	127.0							1.2	545
825-5-1/2	19183	5-1/2	139.7				5"			1.2	545
825-6	19184	6	152.4							1.4	636
825-68	36169	68	68.0							.4	182
825-74	36170	74	70.0							.5	227

*See page 121 for Quick Change adapter information.

Bi-Metal Hole Saw Kits



835 / 27538



834 / 19913



830 / 19192



889 / 03478

CAT. NO.	UPC NO.	DESCRIPTION	830/ 19192	834/ 19913	835/ 27538	830PG/ 29209	889/ 03478	890/ 03479	891/ 03480
825-3/4	19134	3/4" Hole Saw					✓	✓	✓
825-7/8	19136	7/8" Hole Saw	✓		✓	✓	✓	✓	✓
825-1	19138	1" Hole Saw						✓	
825-1-1/8	19141	1-1/8" Hole Saw	✓		✓	✓	✓	✓	✓
825-1-3/8	19146	1-3/8" Hole Saw	✓		✓			✓	✓
825-1-1/2	19148	1-1/2" Hole Saw					✓	✓	✓
825-1-3/4	19152	1-3/4" Hole Saw	✓		✓		✓	✓	✓
825-2	19155	2" Hole Saw	✓		✓			✓	✓
825-2-1/4	19159	2-1/4" Hole Saw					✓	✓	✓
825-2-1/2	19162	2-1/2" Hole Saw	✓		✓			✓	✓
825-3	19167	3" Hole Saw		✓	✓			✓	
825-3-1/4	19169	3-1/4" Hole Saw						✓	
825-3-5/8	19172	3-5/8" Hole Saw		✓	✓			✓	
825-3-3/4	19174	3-3/4" Hole Saw						✓	
825-4-1/8	19177	4-1/8" Hole Saw		✓	✓			✓	
825-4-1/2	19180	4-1/2" Hole Saw		✓	✓				
825-4-3/4	19181	4-3/4" Hole Saw						✓	
825-5/8	19132	Pg-9 (15.9 mm) Hole Saw				✓			
825-3/4	19134	Pg-11 (19.0 mm) Hole Saw				✓			
825-13/16	19135	Pg-13 (20.6 mm) Hole Saw				✓			
825-1-3/16	19143	30.2 mm Hole Saw				✓			
825-1-1/2	19148	Pg-29 (38.1 mm) Hole Saw				✓			
825-1-7/8	19154	Pg-36 (47.6 mm) Hole Saw				✓			
825-2-3/8	19161	Pg-48 (60.3 mm) Hole Saw				✓			
38522	38522	Arbor w/Pilot Drill (2)							
37157	37157	Arbor w/Pilot Drill			✓				
37155	37155	Arbor w/Pilot Drill			✓	✓	✓	✓	✓
37156	37156	Arbor w/Pilot Drill	✓	✓	✓	✓	✓	✓	✓
38526	38526	Pilot Drill					✓	✓	✓

890 / 03479

891 / 03480

- Several electrician's kits available providing an assortment of the most commonly used Greenlee variable pitch hole saw sizes and arbors.
- High-impact, rugged plastic carrying case.
- Each kit includes three hole saw stops.

CAT. NO.	UPC NO.	DESCRIPTION	WEIGHT	
			LBS.	KG.
830	19192	Hole Saw Kit for 1/2" through 2" Conduit Sizes	2.7	1.2
834	19913	Hole Saw Kit for 2-1/2" through 4" Conduit Sizes	6.2	2.8
835	27538	Hole Saw Kit for 1/2" through 4" Conduit Sizes	7.7	3.5
830Pg	29209	Hole Saw Kit for Pg-9 through Pg-48	2.7	1.2
889	03478	Plumber's Hole Saw Kit - 3/4" through 2-1/4" Conduit Sizes	2.3	1.0
890	03479	Industrial Maintenance Hole Saw Kit - 3/4" through 4-3/4" Conduit Sizes	9.7	4.4
891	03480	Electrician's/Plumber's Hole Saw Kit - 3/4" through 2-1/2" Conduit Sizes	3.5	1.6

KIT CAT./UPC NO.