

Ratcheting Cable Cutters

- High leverage ratchet mechanism for single-handed cutting of copper and aluminum cables, leaving no burrs or sharp edges.
- Patented two-step ratchet mechanism requires fewer strokes per cut (63060 and 63750).
- Quick release opens blades easily in every cutting position. (Allows removal of the cable before completion of cut).
- Precision ratcheting mechanism holds cable tight and allows rapid, straight cuts with minimum effort.
- Hardened steel cutting blades for lasting strength and sharpness.
- Plastic covered handles with hand guards for comfort and firm grip.
- Locking lever keeps handles closed for easy transport; fits in a toolbox or bag.
- One-year warranty.



⚠WARNING: Do NOT use to cut steel or ACSR.

Cat No	MCM Maximum Cable Capacity			Length	Weight (lbs.)
	Copper	Aluminum	Communication Cable		
63060	Maximum: 400 kcmil (MCM) (185 mm ²)	Maximum: 600 kcmil (MCM) (300 mm ²)	Maximum: 1-1/8" (28 mm)	10-1/4" (260 mm)	1.32 lbs. (600 g)
63600	Maximum: 600 kcmil (MCM) (300 mm ²)	Maximum: 600 kcmil (MCM) (300 mm ²)	Maximum: 1-3/4" (44 mm)	9" (229 mm)	2.12 lbs. (962 g)
63750	Maximum: 1000 kcmil (MCM) (500 mm ²) Frequent Use: 750 kcmil (MCM) (400 mm ²)	Maximum: 1000 kcmil (MCM) (500 mm ²) Frequent Use: 750 kcmil (MCM) (400 mm ²)	Maximum: 2-1/16" (52 mm)	12-1/8" (308 mm)	1.76 lbs. (800 g)

Ratcheting Cutter – Heavy-Duty



- Ratchet-action design provides maximum leverage with minimum effort for heavy-duty use.
- Cuts steel and ACSR.
- Forged, heat-treated, shear-type blades, plus 24" (609 mm) long steel handles with heavy vinyl grips for comfort and slip-resistance.
- Blade-advance knob for fast rotation of the blade to engage the cable or other material being cut, plus a quick-release mechanism allows for removal of the cable or rod before completion of the cut, if desired.
- Not designed for cutting EHS Guy Strand or reinforcement rod.

Cat. No.	Overall Length	Soft Cable-Cutting Maximum Capacity	Communications Cable-Cutting Maximum Capacity	Weight (lbs.)
63700	36" (914 mm)	2-1/4" (57 mm) diameter	1-1/4" (32 mm) dia. ACSR, ACAR 7/16" (11 mm) dia. common guy strand 5/8" (16 mm) dia. steel wire rope 1/2" (13 mm) dia. steel rod (C.R.S. SOFT) 750 MCM (1-3/8" dia.) (35 mm) copper or aluminum	14.00

All dimensions are in inches and (millimeters).


⚠WARNING: Always wear approved eye protection.

⚠WARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



Cable Cutters

Features:



High-Leverage Cable Cutters

Additional Features:

- High-leverage design for exceptional cutting capability.
- Precision, one-hand shearing action.
- Cable-gripping shear-type jaws.
- Perfect for working in confined spaces.
- Can be carried in most tool pouches.



63050

⚠WARNING: Do NOT use to cut steel or ACSR.

Cat. No.	Overall Length	Handle Color	Maximum Cable Cutting Capacity	Weight (lbs.)
63050	9-1/2" (241 mm)	red	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications wire	.90
Journeyman Series – Dual-material handles				
J63050	9-3/4" (248 mm)	red and black	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications wire	.98

Multi-Cable Cutter KLEIN-KURVE®

- Hardened steel precision-ground cutting blades for long life.
- Copper curved cutter cleanly cuts round copper cable without compression or frayed ends.
- Anvil cutter for solid and stranded copper wire up to 12 AWG and stainless steel up to .032" (.81 mm) diameter.
- Mild steel cutter for conductors up to .080" (2 mm) diameter.
- Curved cutter for solid and stranded copper wire up to 8 AWG, multi-conductor cable up to 1/2" (13 mm) diameter and coaxial cable RG-6 Quad, RG-59, and RG-62.
- Double-dipped grips for comfort.
- Coil spring provides fast self-opening action.
- Holes for looping and bending wire.
- Handy closure lock for convenient storage.



63020

Cat. No.	Overall Length	Screw Shearing	Handle Color	Weight (lbs.)
63020	7" (177 mm)	6-32 & 8-32	red	.44

All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

