

## FEATURES & SPECIFICATIONS

### INTENDED USE

For use with housings L7X, L7XR, and LC6. The adjustable gimbal designed for PAR38 lamps provides flexibility and versatility for accent lighting. Ideal for hospitality, retail, residential and apartment interior spaces, such as slope ceilings, grazing textured surfaces, and highlighting artwork or other architectural features.

### CONSTRUCTION

Durable powder-coated steel finishing trim.

Directional accent lighting gimbal ring available in matte white and black, oil rubbed bronze, brush nickel and clear diffuse finishes.

35° vertical tilt standard.

180° horizontal rotation.

### INSTALLATION

Socket to trim interface.

Trim retention is achieved by utilizing two side-mounted torsion springs on the trim and two receiving brackets in the can, ensure a consistently tight fit with the ceiling.

### LISTINGS

cETL<sub>US</sub> listed to U.S. and Canadian safety standards.

Damp location listed.

### WARRANTY

1-year limited warranty. Complete warranty terms located at

[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

6" Finishing Trim

# 6G2

**GIMBAL**  
Narrow Flange



Matte black



Brushed nickel



Oil-rubbed bronze



Clear diffuse


### Specifications

Height: 5-3/4" (14.5) with Par Lamp

Lamp opening: 4-3/4" (12.1)

Diameter: 7-3/4" (19.6)

All dimensions are inches (centimeters) unless otherwise indicated.



### ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

**Example: 6G2MW PAR38 TOR**

6G2		TOR	
Series	Finish	Lamp	Mounting method
<b>6G2</b>	<b>MW</b>	Matte white	<b>PAR38</b>
	<b>ORB</b>	Oil rubbed bronze	
	<b>BN</b>	Brushed nickel	
	<b>MB</b>	Matte black	
	<b>A</b>	Clear diffuse	
			<b>TOR</b> Torsion springs

### Housing Compatibility: Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR38 <i>short or long neck</i>	L7X, L7XR, LC6
	LED	20 PAR38	

## 6G2 6" Gimbal Trim

---

For PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.