

AA Battery Operated Wireless Interconnect Talking Smoke & Carbon Monoxide Alarm



with Wink App Compatibility

Part Number 900-0225CA Model KN-COSM-B-RF-CA 10-Year Limited Warranty

Wireless Interconnect

Combined Smoke & Carbon Monoxide Alarm

Voice Warning

Hush®/Test/Reset Button



Features and Benefits

- Interconnects wirelessly Offers the safety benefits of an interconnected system without having to run new wiring. When one alarm sounds, they all sound, warning you to a potential threat anywhere in your home
- Wink compatible This product is compatible with the Wink Hub and the Wink App* and will send notifications to your smartphone, tablet or PC (Wink Hub required). Please see Wink Hub documentation for instructions. The Wink Hub is required to send notifications to smart devices, but this alarm can operate wirelessly, with or without the Hub.
- Combined Smoke & Carbon Monoxide Alarm A single unit can be installed where previously, two were needed. Reduces installation time and protects against both fire and carbon monoxide dangers.
- Voice Warning Announces the hazard type detected (in English and French). Alarm announces "FIRE!" when a smoke or fire hazard is detected and announces "WARNING! CARBON MONOXIDE!" when a CO hazard is detected. Also announces "LOW BATTERY" when it is time to replace the batteries.
- End of Life Notification Ten (10) years after unit is first powered, this alarm will beep two times every 30 seconds to indicate it is time to replace the alarm.
- Alarm Memory: The green LED will flash every second in alarm. When the alarm condition goes away, the originating alarm unit will flash the green LED every 16 seconds until the Hush®/Test/Reset button is pressed, thus resetting the alarm.

- Multi-function One Button Design includes:
 - Test Feature Tests the alarm circuitry and triggers the voice announcement
 - Hush® Feature Temporarily silences nuisance alarms for approximately 8 minutes (will announce "HUSH MODE ACTIVATED," or "HUSH MODE CANCELLED.").
 - **Reset Feature** Resets the carbon monoxide alarm
 - Peak Level Memory If alarm has detected a CO level of 100ppm or higher since it was last reset, the voice alarm will announce "CAUTION, CARBON MONOXIDE PREVIOUSLY DETECTED"

Alarm Warnings

- Fire: The red LED will flash and be accompanied by three long alarm beeps followed by a verbal warning message "FIRE!". The alarm pattern will repeat until smoke is eliminated.
- Carbon Monoxide: Four short alarm beeps followed by a verbal warning "WARNING! CARBON MONOXIDE!" This continues until the unit is reset or the CO is eliminated.
- Low Battery: One chirp followed by warning "LOW BATTERY." The red LED light will flash. This pattern will continue every minute for at least seven days. Under battery power, the "LOW BATTERY" voice only occurs once every 15 minutes.
- Voice Hush Indication: "HUSH MODE ACTIVATED" and "HUSH MODE CANCELLED" voice announcement.







Architectural and Engineering Specifications

The combination smoke and carbon monoxide alarm shall be Kidde model KN-COSM-B-RF-CA (P/N 900-0225CA) or approved equal. It shall be powered by three AA batteries. The temperature operating range shall be between 4.4°C (40°F) to 37.8°C (100°F) and the humidity operating range shall be 10%–95% relative humidity, non-condensing.

The unit shall incorporate an ionization smoke sensor with nominal sensitivity of 0.66 ± 0.12 %/ft. The CO sensor shall be of a fuel cell design and shall meet the sensitivity requirements of CAN/CSA 6.19-01 (R2011) - Residential carbon monoxide alarming devices.

The alarm can be installed on the surface of any wall or ceiling following the UL/NFPA/Manufacturer's recommended placement guidelines.

The alarm shall include a test button that will electronically simulate the presence of smoke and CO and cause the unit to go into both modes of alarm. This sequence tests the unit's electronics to ensure proper operation.

The CO sensor will not alarm to levels of CO below 30 ppm and will alarm in the following time range when exposed to the corresponding levels of CO:

70 ppm CO Concentration 60 – 240 minutes 150 ppm CO Concentration 10 – 50 minutes 400 ppm CO Concentration 4 – 15 minutes

The combination alarm shall have two methods of warning for danger: a piezoelectric horn that is rated at 85 decibels at 10 feet and a voice warning that identifies the danger. For a CO incident, the horn will sound in four (4) short beeps followed by the verbal warning message "Warning Carbon Monoxide!". This continues until the unit is reset or the CO is eliminated. In a Smoke incident, the horn will sound three (3) long alarm beeps followed by the verbal warning message "FIRE!" This pattern is repeated until the smoke is eliminated. The red LED light will flash while in alarm/voice mode. The smoke alarm takes precedence when both smoke and CO are present.

The unit shall incorporate a green and a red LED. The green LED will flash every 30 seconds in standby mode, every second to indicate alarm memory, and every 2 seconds to indicate the Hush® mode is active. A red LED will flash in unison with the alarm sounder pattern.


The unit shall include the Hush® feature that silences the unit for approximately 9 minutes if a nuisance alarm condition occurs. The Green LED on the alarm will flash every 2 seconds while in Hush® and will automatically reset itself. It also provides voice annunciation of "HUSH MODE ACTIVATED" when Hush® is activated and "HUSH MODE CANCELLED" when the Hush cycle ends.


The unit shall also indicate a low battery warning utilizing each of the following methods: the red LED will flash and the unit will "chirp" once, followed by the warning message "Low Battery!" every 60 seconds for the first hour. After the first hour, the red LED will continue to flash every minute accompanied by only the "chirp" sound. The voice message "Low battery" will sound once every fifteen minutes during the chirp-only cycle. This will continue for at least seven (7) days.

The unit shall at a minimum meet the requirements of CAN/CSA 6.19-01 and CAN/ULC-S531. It shall also include a 10-year manufacturer's limited warranty.

Technical Specifications

Power Source:	Three (3) AA batteries		
Sensors:	Smoke: Ionization, CO: Electrochemical		
Audio Alarm:	85 dB at 10 ft		
Temperature Range:	4.4°C (40°F) to 37.8°C (100°F)		
Humidity Range:	10%-95% relative humidity, non-condensing		
Unit Size:	15cm in length x 15cm in width x 4.4cm depth		
Unit Weight:	0.2 kg		
Interconnects:	Up to 24 devices wirelessly (of which 12 can be smoke alarms)		
Warranty:	10-year limited		





Ordering Information

UPC: 0-47871-26333-2

Part Number	I2 of 5	Pack Quantity	Case Dimensions (w x d x h centimeters)	Case Weight	Case/ Skid
900-0225CA	100-47871-26333-9	6 units	20 cm x 37 cm x 28 cm	5.70 kg	36



Kidde Canada Inc. P.O. Box 40, Apsley, ON K0L 1A0 1-800-880-6788 www.kiddecanada.com

Distr	ıbute	d by: