


## E-Z-Ground® Grounding Connectors

One-piece construction for cable-to-cable, cable-to-rod, “T” and “X” connections.

### Cable-to-Cable or Cable-to-Rod Connectors

- Suitable for direct burial or in concrete
- Replaces exothermic welds
- Made from high-conductivity wrought copper
- Conforms to IEEE 837 standard
- UL467



**DB**

| CAT. NO.      | CABLE TO CABLE RANGE |          |            |          | GROUND ROD | ROD TO CABLE |            |          |
|---------------|----------------------|----------|------------|----------|------------|--------------|------------|----------|
|               | MAIN                 | DIE CODE | BRANCH     | DIE CODE |            | DIE CODE     | CABLE      | DIE CODE |
| GG21-21       | #2 or #1             | 45       | #2 or #1   | 45       | —          | —            | —          | —        |
| GG10-10       | 1/0                  | 54       | 1/0        | 54       | —          | —            | —          | —        |
| GG2030-21     | 2/0 or 3/0           | 60       | #2         | 45       | —          | —            | —          | —        |
| GG2030-10     | 2/0 or 3/0           | 60       | 1/0        | 54       | —          | —            | —          | —        |
| GG2030-2030   | 2/0 or 3/0           | 60       | 2/0 or 3/0 | 50       | —          | —            | —          | —        |
| GG40250-21    | 4/0 or 250           | 71       | #2         | 45       | 1/2"       | 71           | #2 or #1   | 45       |
|               |                      |          | #1         | 50       | 5/8"       | 80H          | #2 or #1   | 50       |
| GG40250-10    | 4/0 or 250           | 71       | 1/0        | 54       | 1/2"       | 71           | 1/0        | 65       |
|               |                      |          |            |          | 5/8"       | 80H          |            |          |
| GG40250-2030  | 4/0 or 250           | 71       | 2/0 or 3/0 | 60       | 1/2"       | 71           | 2/0 or 3/0 | 60       |
|               |                      |          |            |          | 5/8"       | 80H          | 2/0 or 3/0 | 60       |
| GG40250-40250 | 4/0 or 250           | 71       | 4/0 or 250 | 71       | 1/2"       | 71           | 4/0 or 250 | 71       |
|               |                      |          |            |          | 5/8"       | 80H          | 4/0 or 250 | 71       |
| GG350-350     | 350 kcmil            | 80H      | 350        | 80H      | —          | —            | —          | —        |
| GG500-40250   | 500 kcmil            | 87       | 4/0 or 250 | 71       | 5/8"       | 80H          | 500        | 87       |
|               |                      |          |            |          | 3/4"       | 87H          | 500        | 87       |
| GG500-500     | 500 kcmil            | 87       | 500        | 87       | 3/4"       | 87           | 500        | 87       |
| GG500-350     | 500 kcmil            | 87H      | 350        | 80       | 5/8"       | 87H          | 350        | 80H      |
|               |                      |          |            |          | 3/4"       |              |            |          |
| GG500-2030    | 500 kcmil            | 87H      | 2/0 or 3/0 | 60       | 5/8"       | 87H          | 2/0 or 3/0 | 60       |
|               |                      |          |            |          | 3/4"       |              |            |          |

Tooling: pp. F-80–F-100.

Die Selector Chart: p. F-101–F-104.