

System

R1 Cable Ties

R2 Cable Accessories

Stainless Steel Cable Ties & Accessories

Wiring Duct

Abrasion Protection

Cable Management

> D1. Terminals

D2. Power **Connectors**

Grounding Connectors

> Labeling Systems

F2. Lahels

Pre-Printed Write-On Markers

E4. Permanent Identification

> E5. Industrial Safety Solutions

F. Keystone Cabling Systems

Part Number Index

Cable Management

Panduit® offers a complete line of cable management products and accessories to route and secure cable. These products are an essential part of a clean, professional installation, which help improve quality and increase system performance.





- Maintains bend radius control and cable performance while bundling and securing cable to prevent snags and stress from over bending
- Allows for easier moves, adds, and changes while reducing stress on cable
- Organizes cable in a variety of applications where depth is critical or space is limited

Panduit solutions provide the options necessary to handle the most demanding installations while providing the flexibility to facilitate system upgrades now and in the future.





R1 Cable Ties

R2 Cable Accessories

Stainless Steel Cable Ties & Accessories

> Wiring Duct

C2. **Abrasion** Protection

C3. Cable Management

D1. Terminals

D2. Power Connectors

Grounding Connectors

E1. Labeling Systems

F2. Lahels

E3. **Pre-Printed** Write-On Markers

E4. Permanent Identification

> E5. Industrial Safety Solutions

F. Keystone Cabling Systems

G. Part Number Index

J-Pro[™] Cable Support System



- Patented design provides complete horizontal and vertical 1" (25.4mm) bend radius control that helps prevent degradation of cable performance
- UL 2043 and CAN/ULC S102.2 listed and suitable for use in air handling spaces
- Pre-riveted assemblies allow for attachment to walls, ceilings, beams, threaded rods, drop wires and underfloor supports to meet requirements of a variety of applications
- Wide cable support base prevents pinch points that could cause damage to cables
- Cable tie channel allows user to easily install 3/4" Tak-Ty® Cable Ties to retain cable bundle
- Durable non-metallic J Hook materials provide the ability to manage and support a large number of cables
- Standard product is black. For color options see



JP2W-L20



JP2WP2B-L20



JP2CMB-L20



JP2DW-L20





Part Number*	Part Description	Max. Bundle Capacity		Max. Cable Capacity			Ctal
		ln.	mm	Cat. 6A (0.30")	Cat. 6 (0.24")	Cat. 5e (0.23")	Std Pkg Qty
Wall Mount							
JP75W-L20	J Hook for wall mount applications. One 1/4" (M6) mounting hole for user supplied screw.	0.75	19.0	5	8	10	50
JP131W-L20		1.31	33.3	15	25	29	50
JP2W-L20		2.00	50.8	30	46	55	50
JP4W-X20		4.00	101.6	115	180	200	10
Wall Mount with B	racket						
JP75WP2B-L20	J Hook for powder actuated installation on walls. One 5/32" (M4) mounting hole for user	0.75	19.0	5	8	10	50
JP131WP2B-L20		1.31	33.3	15	25	29	50
JP2WP2B-L20		2.00	50.8	30	46	55	50
JP4WP2B-X20	supplied fasteners.	4.00	101.6	115	180	200	10
Ceiling Mount							
JP75CMB-L20	J Hook with ceiling mount bracket that has one 3/16" (M5), 1/4" (M6), and 3/8" (M10) mounting hole.	0.75	19.0	5	8	10	50
JP131CMB-L20		1.31	33.3	15	25	29	50
JP2CMB-L20		2.00	50.8	30	46	55	50
JP4CMB-X20		4.00	101.6	115	180	200	10
Drop Wire and Th	readed Rod Clip	·					
JP75DW-L20	J Hook with clip for use with #12 wire, threaded rod up to 1/4" (6.4mm) in diameter, or 1/8" – 1/4" (3.2mm – 6.4mm) thick flanges.	0.75	19.0	5	8	10	50
JP131DW-L20		1.31	33.3	15	25	29	50
JP2DW-L20		2.00	50.8	30	46	55	50
JP4DW-L20		4.00	101.6	115	180	200	10
Screw-On Beam C	lamps			,			
JP75SBC50-L20	J Hook with screw-on beam clamp for use with flanges up to 1/2" (12.7mm) thick.	0.75	19.0	5	8	10	50
JP131SBC50-L20		1.31	33.3	15	25	29	50
JP2SBC50-L20		2.00	50.8	30	46	55	50
JP4SBC50-X20		4.00	101.6	115	180	200	10
JP75SBC50RB-L20	J Hook with screw-on beam clamp for use with flanges up to 1/2" (12.7mm) thick. Rotates	0.75	19.0	5	8	10	50
JP131SBC50RBL20		1.31	33.3	15	25	29	50
JP2SBC50RB-L20		2.00	50.8	30	46	55	50

^{*}Suitable for use in air handling spaces in accordance with Sec. 300-22(c) and (d) of the National Electrical Code. JP4 family of parts suitable for use in single unit configurations. Listed in accordance with CAN/ULC S102.2 when mounted as single units or in pairs. Minimum spacing of 4' (1220mm) required between mount points. (Flame spread rating = 0, Smoke developed classification = 30)

4.00 101.6

200

10

180

115

JP4SBC50RB-X20

360 degrees.