



E-Z-Ground® Grounding Connectors

Hex compression intimately bonds cable directly to ground rod.

Pigtail Connectors

- Figure-8 connectors
- Conforms to IEEE 837 standard
- UL467 Listed



MEETS
IEEE
837 REQUIREMENTS

DB **UL** **SP**

CAT. NO.	CABLE RANGE	GROUND ROD	DIE CODE FOR TBM14M, 13100A OR TBM15I
GR12-306	One Cable: 3/0 to #6 AWG	1/2"	87H
	Two Cables: #2 to #6 AWG		
GR58-406	One Cable: 4/0 to #6 AWG	5/8"	87H
	Two Cables: #2 to #6 AWG		
GR34-4010	One Cable: 4/0 to 1/0 AWG	3/4"	99H

Tooling: pp. F-80-F-100.

Die Selector Chart: pp. F-101-F-104.

When connecting cable to ground rod for direct burial or in concrete, the connector shall be wrought copper with minimum conductivity of 99% I.A.C.S., such as Thomas & Betts series GR12-306. Hex compression with die code embossing shall be used.

Ground Plates



MEETS
IEEE
837 REQUIREMENTS

DB **UL** **SP**

CAT. NO.	FIG.	CABLE RANGE	H	DIES
GP2250-2	1	#2-250 kcmil	3 3/8"	15G86R
GP2250-4	2	#2-250 kcmil	4 1/2"	15G86R
GP250500-2	1	250-500 kcmil	3 3/8"	15G126R
GP250500-4	2	250-500 kcmil	4 1/2"	15G126R

