



Core & Coil (71A) MH ~LT~ 175W

CORE & COIL HID MH BAL 150W M102/142 120/277/347V C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

| General Information | | | | |
|------------------------------------|----------------|--|--|--|
| ANSI Code | M102-M142 | | | |
| Lamp Type | 150 MH | | | |
| Number of Lamps | 1 piece/unit | | | |
| Circuit Type | HX-HPF | | | |
| Ballast Type | Magnetic HID | | | |
| Base Model | 71A54A2 | | | |
| Core Size | 3 X 4 (2 coil) | | | |
| Suitable For Outdoor Use | Yes | | | |
| Ignitor Catalog Number | LI533-H4 | | | |
| Ignitor Temperature Rating | 105°C | | | |
| Capacitor Value | 16 MFD | | | |
| Capacitor Catalog Number | 7C160M30RA | | | |
| Capacitor Requirements | 280V | | | |
| Capacitor Temperature Rating | 105°C | | | |
| Capacitor Diameter/Oval Dimensions | 1.65 in | | | |
| Capacitor Height | 2.75 in | | | |
| Automatic Restart | No | | | |
| | | | | |

| Operating and Electrical | | | | | | |
|-------------------------------------|-----------------------------|--|--|--|--|--|
| Input Voltage | 120/277/347 V | | | | | |
| Input Frequency | 60 Hz | | | | | |
| Input Current (Open Circuit) | 3.65/1.58/1.25 A | | | | | |
| Input Current (Starting) | 0.95/0.42/0.65 A | | | | | |
| Input Current (Short Circuit) | 1.2-1.9/0.5-0.8/0.45-0.75 A | | | | | |
| Secondary Short Circuit Current | 2.05-2.55 A | | | | | |
| Constant Wattage Deviation | 12% | | | | | |
| Ballast Factor (Nom) | 1 | | | | | |
| Power Factor (Nom) | 0.90 | | | | | |
| Open Circuit Voltage | 265 V | | | | | |
| Input Current (Nom) | 1.6/0.7/0.55 A A | | | | | |
| Input Power (Nom) | 185 W | | | | | |
| Rated Lamp Power | 150 W | | | | | |
| | | | | | | |
| Wiring | | | | | | |
| Wire Striplength | 0.5 mm | | | | | |
| Wire Length by Color | 12" | | | | | |
| Wire Type | Stranded | | | | | |
| Remote Wiring Configuration Allowed | Yes | | | | | |


Datasheet, 2019, March 22 data subject to change

Core & Coil (71A) MH ~LT~ 175W

| Max Ballast-Lamp Distance Remote | 10' | | | |
|-----------------------------------|------------------------------------|--|--|--|
| Wiring | | | | |
| Recommended Fuse Value | 10/4/3 A | | | |
| | | | | |
| Approval and Application | | | | |
| Open Circuit Voltage Test (Volts) | 235-290 V | | | |
| Approval Marks | ULR CSA certificate RoHS Compliant | | | |
| Temperature Marking | E/E/E | | | |
| UL Recognized | Yes | | | |
| Hipot Test (1 Minute) | 2000 V | | | |
| Hipot Test (2 Seconds) | 2500 V | | | |
| UL Insulation Class | H(180°C) | | | |
| UL Temperature Code | 1029E | | | |
| | | | | |

| Product Data | |
|---------------------------------|--------------------------------------|
| Order product name | CORE & COIL HID MH BAL 150W M102/142 |
| | 120/277/347V C&C |
| EAN/UPC - Product | 781087056462 |
| Order code | 913700572509 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 4 |
| Material Nr. (12NC) | 913700572509 |
| Net Weight (Piece) | 3.380 kg |

Dimensional drawing



MH BAL 150W M102/142 120/277/347V C&C

| Product | C1 | C2 | A1 | A2 | B1 | B2 |
|-----------------------------|---------|---------|--------|--------|--------|--------|
| CORE & COIL HID MH BAL 150W | 3.87 in | 2.25 in | 3.9 in | 3.5 in | 2.8 in | 2.4 in |
| M102/142 120/277/347V C&C | | | | | | |

