



LED/CFL Dimmers

Create the right mood

COOPER Wiring Devices



Dimming & energy savings with elegant styling and superior performance

Our dimmable LED/CFL dimmers work great with a variety of light sources and are offered in three styles to fit any decor. With an easily adjustable dimming range, you can fine tune the performance to match a variety of dimmable LED and CFL lamps as well as traditional incandescent lamps.

Residential Grade Decorator Slide Dimmers

FEATURES

- Preset feature allows user to return to previous light level when turning lights ON
- Integrated full-slide control for easy, precise operation
- Can be wired as single-pole or 3-way
- Device can be wired into either 3-way location (load side or line side)
- Neutral is not required for installation of device
- Replaces a standard switch and offers dimming capabilities
- Radio Frequency Interference filtering is standard on all models
- Electrostatic discharge protection
- Precise color matching
- Compatible with any decorator wallplate or screwless wallplate
- Compatible with many dimmable CFL and LED lamps

ASPIRE, DEVINE & SKYE Dimmers, Back & Side Wire



| Style | Rating/Load Compatibility | Description | Available Colors | Catalog No. |
|--------------------|--|----------------------------------|------------------|-------------|
| ASPIRE | 600W/VA Incandescent 300W/VA Dimmable LED/CFL | Single-Pole & 3-Way, with Preset | AW, DS, SG, WS | □ 9573-__ |
| DEVINE (Decorator) | 600W/VA Incandescent 300W/VA Dimmable LED/CFL | Single-Pole & 3-Way, with Preset | A, BK, LA, V, W | □ DLC03P-__ |
| SKYE (Slide) | 600W/VA Incandescent 300W/VA Dimmable LED/CFL | Single-Pole & 3-Way, with Preset | A, BK, LA, V, W | □ SLC03P-__ |

Color Ordering Information:

For ordering devices, include Cat. No. followed by the color code: A (Almond), AW (Alpine White), BK (Black), DS (Desert Sand), LA (Light Almond), SG (Silver Granite), V (Ivory), W (White), WS (White Satin)

TESTING & CODE COMPLIANCE


- cULus Listed to UL 1472, file no. E47967
- NOM Certified

MATERIAL CHARACTERISTICS


- Environmental: Flammability meets UL 94 requirements, V2 rated
- Temperature Rating: 0°C to 40°C (32°F to 104°F)



9573



DLC03P



SLC03P

Cooper Wiring Devices
United States
 203 Cooper Circle
 Peachtree City, GA 30269
 P: 866-853-4293 F: 800-329-3055

www.cooperwiringdevices.com

Canada
 5925 McLaughlin Road
 Mississauga, Ontario, L5R 1B8
 P: 800-267-1042 F: 800-761-5748

Mexico
 Carr. Tlalnepantla – Cuautitlan Km 17.8 s/n
 Col. Villa Jardin esq.
 Cerrada 8 de Mayo
 Cuautitlan, Mexico CP 54800
 P: +525558999190 F: +525526207116

Cooper Wiring Devices is a valuable trademark of Cooper Industries in the U.S. and other countries. You are not permitted to use the Cooper Trademarks without the prior written consent of Cooper Industries. ©2012 Cooper Industries, Ltd.