

# MS132-12

ABB contact for Canada [Print to Pdf..](#)

## General Information

<b>Extended Product Type:</b>	MS132-12
<b>Product ID:</b>	1SAM35000R1012
<b>EAN:</b>	4013614400124
<b>Catalog Description:</b>	MS132-12 Manual Motor Starter
<b>Long Description:</b>	<p>The MS132-12 manual motor starter is a compact 45 mm width devices with a rated operational current of <math>I_e = 12.0</math> A. This device is used to manually switch on and off motors and to protect them reliably and without the need for a fuse from short-circuits, overload and phase failures. The manual motor starter offers a rated service short-circuit breaking capacity <math>I_{cs} = 100</math> kA at 400 VAC and the trip class 10. Further features are the build-in disconnect function, temperature compensation, trip-free mechanism and a rotary handle with a clear switch position indication. The manual motor starter is suitable for three- and single-phase applications. The handle is lockable to protect against unauthorized changes. Auxiliary contacts, signalling contacts, undervoltage releases, shunt trips, 3-phase bus bars, power in-feed blocks are available as accessory.</p>



## Categories

Products » Low Voltage Products and Systems » Circuit Breakers » Manual Motor Starters

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters

## Accessories [Show accessory images](#)

## Ordering

<b>EAN:</b>	4013614400124
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85362010

## Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	92.0 mm
<b>Package Level 1 Length:</b>	102.0 mm
<b>Package Level 1 Height:</b>	50.0 mm
<b>Package Level 1 Gross Weight:</b>	0.325 kg
<b>Package Level 2 Units:</b>	40 piece
<b>Package Level 2 Width:</b>	280.0 mm
<b>Package Level 2 Length:</b>	395.0 mm

<b>Package Level 2 Height:</b>	210.0 mm
<b>Package Level 2 Gross Weight:</b>	13.386 kg
<b>Package Level 2 EAN:</b>	4013614409028

---

## Dimensions

---

<b>Product Net Width:</b>	45.0 mm
<b>Product Net Height:</b>	97.8 mm
<b>Product Net Depth:</b>	86.6 mm
<b>Product Net Weight:</b>	0.310 kg

---

## Technical

---

<b>Rated Service Short-Circuit Breaking Capacity (<math>I_{cs}</math>):</b>	(230V AC) 100.0 kA (250V DC) 3 poles in series 10.0 kA (400V AC) 100.0 kA (440V AC) 20.0 kA (500V AC) 20.0 kA (690V AC) 3.0 kA
<b>Rated Ultimate Short-Circuit Breaking Capacity (<math>I_{cu}</math>):</b>	(230V AC) 100.0 kA (400V AC) 100.0 kA (440V AC) 20.0 kA (500V AC) 20.0 kA (690V AC) 3.0 kA
<b>Rated Instantaneous Short-Circuit Current Setting (<math>I_i</math>):</b>	180.0 A
<b>Setting Range:</b>	8.00 ... 12.0 A
<b>Rated Operational Power AC-3 (<math>P_e</math>):</b>	(400V) Three Phase 5.50 kW
<b>Rated Operational Voltage:</b>	Main Circuit 690 V AC Main Circuit 250 V DC
<b>Rated Operational Current (<math>I_e</math>):</b>	12 A
<b>Rated Operational Current AC-3 (<math>I_e</math>):</b>	12.00 A
<b>Rated Operational Current DC-5 (<math>I_e</math>):</b>	12.000 A
<b>Rated Frequency (f):</b>	Main Circuit 50 Hz Main Circuit 60 Hz
<b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>	Main Circuit 6 kV
<b>Rated Insulation Voltage (<math>U_i</math>):</b>	690 V
<b>Power Loss:</b>	Per Pole 1.0 ... 2.3 W
<b>Number of Poles:</b>	3
<b>Conventional Free-air Thermal Current (<math>I_{th}</math>):</b>	Main Circuit 12.00 A
<b>Degree of Protection:</b>	IP20
<b>Pollution Degree:</b>	3
<b>Electrical Durability:</b>	50000 cycle
<b>Mechanical Durability:</b>	100000 cycle
<b>Connecting Capacity-Main Circuit:</b>	Flexible with Ferrule 1/2x 0.75 ... 6 mm <sup>2</sup> Flexible with Insulated Ferrule 1/2x 0.75 ... 6 mm <sup>2</sup> Flexible 1/2x 1 ... 2.5 mm <sup>2</sup> Flexible 1/2x 2.5 ... 6 mm <sup>2</sup> Rigid 1/2x 1 ... 2.5 mm <sup>2</sup> Rigid 1/2x 2.5 ... 6 mm <sup>2</sup>
<b>Tightening Torque:</b>	Main Circuit 2 N·m

<b>Wire Stripping Length:</b>	Main Circuit 10 mm
<b>Recommended Screw Driver:</b>	M4
<b>Mounting Position:</b>	Position 1 to 6
<b>Actuator Type:</b>	Rotary Handle
<b>Contact Position Indication:</b>	ON / OFF / TRIP
<b>Mounting on DIN Rail:</b>	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
<b>Standards:</b>	IEC/EN 60947-1 IEC/EN 60947-2 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1

## Environmental

<b>Ambient Air Temperature:</b>	Around the Enclosure 0 ... +40 °C Operation -25 ... +70 °C Operation Compensated -25 ... +60 °C Storage -50 ... +80 °C
<b>Ambient Air Temperature Compensation:</b>	Yes
<b>Maximum Operating Altitude Permissible:</b>	2000 m
<b>Resistance to Shock acc. to IEC 60068-2-27:</b>	11 ms Pulse 250 m/s <sup>2</sup>
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	5g / 3 ... 150 Hz
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V AC
<b>Horse Power Rating UL/CSA:</b>	220 ... 240V AC Three Phase 3.00 Hp 440 ... 480V AC Three Phase 7.50 Hp 550 ... 600V AC Three Phase 10.00 Hp
<b>Ampere Rating UL/CSA:</b>	12.00 A
<b>General Use Rating UL/CSA:</b>	600V AC 12.00 A
<b>Connecting Capacity-Main Circuit UL/CSA:</b>	Flexible 1/2x 16 ... 8 AWG Stranded 1/2x 16 ... 8 AWG
<b>Tightening Torque UL/CSA:</b>	Main Circuit 18 in·lb

## Certificates and Declarations (Document Number)

<b>ABS Certificate:</b>	1SAA963001-0101
<b>ATEX Certificate:</b>	1SAA963000-3901
<b>BV Certificate:</b>	1SAA963001-0201
<b>CB Certificate:</b>	1SAA963002-2001
<b>CCC Certificate:</b>	1SAA963001-3802
<b>cUL Certificate:</b>	UL_E137861 UL_E345003
<b>Declaration of Conformity - CE:</b>	1SAD938508-0125
<b>DNV Certificate:</b>	1SAA963001-0303
<b>GL Certificate:</b>	1SAA963001-0401
<b>GOST Certificate:</b>	1SAA937000-2703

<b>LR Certificate:</b>	1SAA963001-0501
<b>RINA Certificate:</b>	1SAA963000-0801
<b>RMRS Certificate:</b>	1SAA918000-0703
<b>RoHS Information:</b>	1SAA963002-4405
<b>UL Certificate:</b>	UL_E137861 UL_E345003

---

## Classifications

---

<b>Object Classification Code:</b>	F
<b>E-nummer:</b>	3112131

---