





Conduit and Cable



Features

- CK Series attaches conduit (EMT, Rigid, ENT and Aluminum) to drop wire, rods or flanges
- Application "A" (vertical flange), supports 25 lb. static load limit
- Application "B" (horizontal flange), supports 100 lb. static load limit
- Application "C" (vertical drop wire), supports 50 lb. static load limit



Features

FROM DROP WIRE

- One-piece construction
- Can be used in vertical or horizontal (0.433-0.535 outer diameter)
- No load rating for positioning only
- No installation tools required





FIG. 1

Cat. No.	Fig. No.	Description	Qty. Per Box
Conduit Hangers from Flange, Wire or Rod			
SSF-CK1/2	1	Conduit hangers for flange wire or rod	100
SSF-CK3/4	1	Conduit hangers for flange wire or rod	
SSF-CK1	2	Conduit hangers for flange wire or rod	

Cat. No.	Fig. No.	Description	Qty. Per Box
Flexible Conduit Hangers from Drop Wire			
SSF-CK535	1	Flexible conduit hanger from drop wire, #8-#12 wire, 0.433-0.535 O.D. cable	100

Conduit Size	#10 & #12 Wire	#8 & #9 Wire	3/16 in. Plain Rod	1/4 in. Plain & Threaded Rod	3/8 in. Plain & Threaded Rod
Wire/Rod					
1/2 EMT	CK1/2	CK1/2	CK1/2	CK1/2	CK3/4
1/2 Rigid	CK1/2	CK1/2	CK1/2	CK3/4	CK3/4
3/4 EMT	CK3/4	CK3/4	CK3/4	CK3/4	CK1
3/4 Rigid	CK3/4	CK3/4	CK3/4	CK1	CK1
1 EMT	—	CK1	CK1	CK1	CK1
1 Rigid	—	CK1	CK1	CK1	—

Conduit Size	1/8 in. Flange	3/16 in. - 1/4 in. Flange	5/16 in. - 3/8 in. Flange	7/16 in. - 1/2 in. Flange
Flange				
1/2 EMT	CK1/2	CK1/2	CK3/4	CK3/4
1/2 Rigid	CK1/2	CK3/4	CK3/4	CK1
3/4 EMT	CK3/4	CK3/4	CK1	CK1
3/4 Rigid	CK3/4	CK1	CK1	CK1
1 EMT	CK1	CK1	CK1	CK1
1 Rigid	CK1	CK1	—	—