

# Boxes and Covers

. . .

## **Device Boxes – Available Models**

#### **Technical Specifications**

			Gangable							Non-Gangable												
	Depth	1 1/2	2	2	2	2 1/4					2 1/2	2 1/2	2 1/2	3	3	3		2 1/2				2 1/2
	Cu. in.	8.0	10.0	10.0	12.0	10.0	12.5	12.5	14.5	12.5	12.5	16.0	18.0	15.0	18.0	18.0	11.0	12.5	14.5	15.0	18.5	25.0
	Series # BC/CI	1100	1102		3102		525				4304			1004	1018		777		2304			4204
	Basic Model		$\checkmark$	$\checkmark$				$\checkmark$						$\checkmark$								
	В							✓														
its It	К							$\checkmark$														
lui Sou	KSSX											$\checkmark$										$\checkmark$
Conduit Knockouts	KSS1X-1											$\checkmark$										
ŬĔ	LE							✓														
<u> </u>	SB		$\checkmark$					$\checkmark$														
	SSX				✓							✓										
	L	$\checkmark$	✓	√		✓	✓	✓		✓				$\checkmark$								
	LB							✓						√								
	LD					✓																
S	LH	$\checkmark$										$\checkmark$	$\checkmark$	$\checkmark$		$\checkmark$					$\checkmark$	
Nonmetallic Sheathed Cable Clamps (Loomex, NMD90)	LHT							✓						· ·								
ar	LHTQ								✓			$\checkmark$			$\checkmark$				$\checkmark$			
U O	LLE	$\checkmark$																$\checkmark$		$\checkmark$		
ble 0)	LHTQ-2/LLE-2	-																$\checkmark$		-		
D9 D9	LHTQ-3/LLE-3																	$\checkmark$				
Σg	LHTQ-4/LLE-4																	$\checkmark$				
, Ne	LMS							~											✓			
eat	LN							•										✓	•			
Sh	LRB																$\checkmark$	-				
<u>°</u>	LRE	$\checkmark$															-					
	LRW							✓														
Jet	LSSX							•			✓	✓				✓		✓				✓
E	LSS2X										-	-				-		$\checkmark$				
Ž	LSS3X																	✓				
	LSSX-1															~		•				
	LSS1X-1															•		$\checkmark$				
	LSS2X-1																	$\checkmark$				
	LX																	$\checkmark$			$\checkmark$	
	LA							✓		$\checkmark$												
	LBA							· √														
о б	LHA							· √				$\checkmark$	$\checkmark$	$\checkmark$							√	
la S	LLEA																	✓				
ం ్	LLEA-2																	· •				
Armoured Cable Clamps (BX, AC90)	LMSA							✓														
) s	LSBA							· √														
ou	LSSAX				✓						<ul> <li>✓</li> </ul>	$\checkmark$						✓		✓		✓
Arr Iar	LSSAA LSSA-2X										-							• √				
O O	LSSA-2X LSSA-3X																	▼ √				
	LSSA-3X LSSAX-1															$\checkmark$		-				✓
												$\checkmark$				v						v
	LSSA1X-1											V										



## **Boxes and Covers**



### **Device Boxes**

### Armoured and Nonmetallic Sheathed Cable Clamps







BC2304-LHTQ

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.



#### BC2304-LHTQ-2

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs One screw mounting.

#### BC2304-LHTQ-3

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs

#### BC2304-LHTQ-4

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs.

BC3104-LHTQ Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs.

One screw mounting

Cat No	Dimensions	Volume	Gangable		Pryouts			
Cat. No.	H x W x D (in.)	(Cu. in.)	Yes or No	One screw mounting	Pos. tabs	Prov. for external nailing	ends	
BC1018-LHTQ	3 x 2 x 3	18.0	yes	yes	yes	yes	4	
BC1304-LHTQ	3 x 2 x 2-1/2	14.5	yes	yes	yes	yes	4	
BC1304-LHATQ	3 x 2 x 2-1/2	14.5	yes	yes	yes	yes	4	
BC2004-LHTQ	3-3/4 x 2-3/16 x 2-3/4	20.5	no	yes	yes	yes	4	
BC2304-LHTQ	3 x 2 x 2-1/2	14.5	no	yes	yes	yes	4	
BC2304-LHTQ-2	3 x 3-3/4 x 2-1/2	27.0	no	yes	yes	yes	8	
BC2304-LHTQ-3	3 x 5-1/2 x 2-1/2	39.5	no	no	yes	yes	12	
BC2304-LHTQ-4	3 x 7-3/8 x 2-1/2	52.0	no	no	yes	yes	16	
BC3104-LHTQ	3 x 2 x 2-1/2	16.0	yes	yes	yes	yes	4	





# Boxes and Covers



## **Device Boxes**

### Armoured and Nonmetallic Sheathed Cable Clamps

CI775-L	BC775-LD	BC777-LRB	CI525-L
Flush ears.	"Swing-arm" rework brackets. Max. wall thickness: 3/4 in.	Pivoting ends for rework installation. Max. wall thickness: 1-1/8 in. * Non-Gangable	"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.
BC1104-LB	BC1104-LHT	CI1104-LMS	BC1104-L
	Positioning tabs. Provision for external nailing. Two embossed mounting slots for internal screw installation.	Mounting strap with prongs. Recessed 1/2 in.	Flush ears.
BC1104-LRB	BC1104-LRW	BC1104-LSSX	BC1304-LHTQ
Flat sides for rework applications.	Rework bracket for closed wall applications. Max. wall thickness: 1 in.		One screw mounting. Provision for external nailing. Positioning tabs for 1/2 in. and 3/4 in. drywall.



Cat. No.	Volume	Fea	tures	Pryouts	Knockouts	
Cat. No.	(Cu. in.)	Ears	Bracket	ends	1/2 in. bottom	
2-1/4 in. Deep — Gangable — 3 in. x 2 in Fe	or use with nonme	etallic sheathed cable (	only			
C1775-L	10.0	flush	-	4	1	
BC775-LD	10.0	flush	rework	4	1	
BC777-LRB*	11.0	-	rework	4	1	
2-1/2 in. Deep — Gangable — 3 in. x 2 in.						
CI525-L	12.5	flush	rework	4	-	
BC1104-L	12.5	flush	-	4	-	
BC1104-LB	12.5	-	"B"	4	-	
BC1104-LHT	12.5	-	P. Tabs	4	-	
CI1104-LMS	12.5	-	"MS"	4	-	
BC1104-LRB	12.5	flush	-	4	-	
BC1104-LRW	12.5	flush	rework	4	-	
BC1104-LSSX	12.5	-	"SSX"	4	-	
BC1304-LHTQ	14.5	-	P. Tabs	4	-	



