



Note: Pattern for bottoms. Left hand entry is shown. For right-hand entry, unit is manufactured symmetrically with hub openings, knockouts for line connectors on right side.

BDC Series

Multiple Position with Blank Compartment
200 A per Position 200 A (Main Lugs)
600 V Max., Stud Type

Product Specifications

- Conductor Range: Line: Single 1/2 in. studs to accommodate compression lugs (supplied by utility), Load: 6 AWG-250 kcmil
- Aluminum tunnel type connectors for load sides
- For underground service only
- Factory prebussed from main lugs to each position
- Supplied with screw type sealing rings
- Internal locking system for covers
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces



Approved for copper or aluminum

For use in All Provinces

Cat. No.		Meter Position	Dimensions (in.)			Weight Each	
Left-Hand Entry	Right-Hand Entry		H	W	D	lb.	kg
4 JAW							
BDC2-V	BDC2-VH	2 position		26-1/4		30	13.6
BDC3-V	BDC3-VH	3 position	15-5/8	35	5-1/4	42	19.0
BDC4-V	BDC4-VH	4 position		43-3/4		54	24.5



Approved for copper or aluminum

For use in Quebec

Cat. No.		Meter Position	Dimensions (in.)			Weight Each	
Left-Hand Entry	Right-Hand Entry		H	W	D	lb.	kg
4 JAW							
BDC2-VIL	BDC2-VHIL	2 position	15-5/8	26-1/4	5-1/4	30	13.6
BDC3-VIL	BDC3-VHIL	3 position		35		42	19.0
BDC4-VIL	BDC4-VHIL	4 position		43-3/4		54	24.5

Locking system inside meter.



Approved for copper or aluminum

For use in British Columbia

Cat. No.		Meter Position	Dimensions (in.)			Weight Each		
Left-Hand Entry	Right-Hand Entry		H	W	D	lb.	kg	
4 JAW								
BDC2-VAILBC	BDC2-VAHILBC	2 position	20-3/4	26-1/4	5-1/4	30	13.6	
BDC3-VAILBC	BDC3-VAHILBC	3 position		35		42	19.0	
BDC4-VAILBC	BDC4-VAHILBC	4 position						

Locking system inside meter, comes with tunnel type connector on line side.