


TYPE SP

VINYLINK™

Splice, Polyvinylchloride Insulated

600 Volts Max., 105° C Max.

The Type SP VINYLINK™ is a PVC insulated seamless butt splice. Type SP VINYLINK™ is designed to accommodate a broad range of 600 volt cables.




B-47



Features & Benefits

- Manufactured from seamless electrolytic copper tubing
 - ◇ Provides maximum conductivity and tensile strength, in a high quality design with NO seams to split
- Funnel entry
 - ◇ Provides easy wire insertion
- Electro-tin plated
 - ◇ Provides durable long lasting resistance to corrosion



- Expanded insulation support
 - ◇ Lower inventory requirements
- Red wire range of 22-16
 - ◇ Lower inventory requirements
- Vinyl insulator
 - ◇ Economical means of providing high dielectric values and cable insulation support

| Catalog Number | Wire Range | Color Code | Bulk Catalog Number | Dimensions (Inches) | | Installation Tooling | Wire Strip Length |
|----------------|------------|------------|---------------------|---------------------|----------------|--|-------------------|
| | | | | L Max. | Max Insul. Dia | | |
| SP16 | 22 - 16 | Red | BS16 | 1.00 | 0.15 | Non-Ratchet: Y10-22 Ratchet: MRE1022NV MR8G-98 MR15 MR8-89-1 | 1/4" |
| SP14 | 16 - 14 | Blue | BS14 | 1.00 | 0.18 | Non-Ratchet: Y10-22 Ratchet: MRE1022NV MR8G-98 MR15 MR8-89-1 | 1/4" |
| SP10 | 12 - 10 | Yellow | BS10 | 1.23 | 0.26 | Non-Ratchet: Y10-22 Ratchet: MRE1022NV MR8G-98 MR15 MR8-89-1 | 21/64" |