# 400, 800, 2300 & 2300D SERIES<sup>™</sup> RACEWAYS Two-Piece, Single- and Dual-Channel, Low Profile




Two-piece, single- and dual-channel, low profile raceway. Easy-toinstall and ideal for power or communication installations.

CODE REFERENCE

cULus Listed Raceway: File E90378 Guide RJTX. Complies with flammability requirements of UL-5A.

Fittings: File E90377 Guide RJYT. Meets Article 388 of NEC. UL Listed for up to 600V. Meets Section 12-1600 of CEC.

#### 400, 800, 2300 & 2300D Series Raceways System Layout



#### **KEY**

- A. 406, 806, 2306 Cover Clip
- B. 411, 811, 2311, 2311DFO Flat Elbow Fitting
- **c.** 810A2, 2310A, 2310DFO Entrance End Fitting **D.** 415, 815, 2315 Tee
- E. 417, 817, 2317, 2317DFO Internal Elbow F. 418, 818, 2318, 2318DFO External Elbow
- G. 2337A, 2338A Round Device Boxes
- H. 2344, 2347, 2348 Sure-Snap Device Boxes

#### **COLOR OPTIONS**



400, 800, 2300 Series Raceway Part Numbers with a "-WH" suffix have a white finish. Part Numbers without a suffix have an ivory finish. 400, 800, 2300 Series Raceways are paintable using latex paint.


Custom color options are also available. Consult the factory for more information.

124

# 400, 800, 2300 & 2300D SERIES<sup>™</sup> RACEWAYS Ordering Information

400/800/2300/2300D Series Raceway Device Box Ordering Information


### 2347, 2347-2 Device Box



2347 one-gang, 2347-2 two-gang. For standard switches and devices. 2347 Base has rectangular KO. 2347-2 Base has rectangular KO to enable extension from existing flush wall box and 1/2" and 1" concentric KOs. Accepts industry standard faceplates for switch and communication devices.

CAT. NO.	L	W	GANG
2347	4 3/4" [121mm]	3" [76mm]	1
2347-WH	4 3/4" [121mm]	3" [76mm]	1
2347-2	4 3/4" [121mm]		2
2347-2-WH	4 3/4" [121mm]		2


### 2348, 2348-2, 2348-3 Deep Device Box




2348 one-gang, 2348-2 two-gang, 2348-3 three-gang. For deeper switches and devices. 2348 Base has rectangular KO. 2348-2 and 2348-3 Bases have rectangular KO to enable extension from existing flush wall box and 1/2" and 1" concentric KOs. Accepts industry standard faceplates for switch and communication devices.


CAT. NO.	L	W	GANG
2348	4 3/4" [121mm]	3" [76mm]	1
2348-WH	4 3/4" [121mm]	3" [76mm]	1
2348-2	4 3/4" [121mm]		2
2348-2-WH	4 3/4" [121mm]		2
2348-3	4 3/4" [121mm]	7" [178mm]	3
2348-3-WH	4 3/4" [121mm]	7" [178mm]	3

### 2348S/51 Shallow Device Box/Extension Box




For shallow switches and receptacles. Base has rectangular KO. Also available in white (2348S/51-WH).






For deeper switches and devices, and has magnetic backing. Base has rectangular KO. Also available 1 3/4" in white (2348AMP-WH).

### 2348D Device Box




For use with 2300D Series Divided Raceway. For mounting standard switches, receptacles, and industry standard faceplates for communication devices. Also available in white (2348D-WH).

### 2344D Extra Deep Device Box



For use with 2300D Series Divided Raceway when additional depth is required. For mounting standard switches, receptacles and industry standard faceplates for communication devices. Also available in white (2344D-WH).

#### 2344SD-2A Two-Gang Deep Divided Device Box



Divided two-gang box for use with 2300D Series Divided Raceway. Provides the ability to have both power and low voltage at a single point of use. Utilizes 5507 Series™ faceplates, as well as Wiremold Open System communication modules, Ortronics® TracJack, Series II, and Pass & Seymour® Activate Series inserts. For faceplate options, see 5507 Series™ Faceplates. Also available in white (2344SD-2A-WH).

NOTE: CM-EPLA End Plates are required when using Wiremold CM2 communication modules and Pass & Seymour® Activate inserts. S2-EPL End Plates are required when using Ortronics® Series II inserts. To mount TracJack modules, use 55074TJ or 55076TJ Faceplates.

# WIREMOLD

# **L**legrand<sup>®</sup>

# 400, 800, 2300, 2300D Series Raceway Systems

# 400, 800, 2300, 2300D Surface Nonmetallic Raceway Systems



For Low Voltage and Power Applications

The Wiremold Company, is a family of single compartment raceways for communication or power applications ideal for use in classrooms, office, and hotel applications or anywhere a small low profile raceway is needed. The 2300D Nonmetallic Divided Raceway is for use when power and low voltage cabling is required in the same raceway.



400, 800, 2300, and 2300D

#### Features & Benefits

- Single and dual compartment low profile raceway design. Provides functionality and flexibility with aesthetics for single or dual service applications.
- Over-the-raceway box for 2300 and 2300D. Boxes mount over continuous run of raceway base eliminating the need to cut raceway when locating devices.
- Quick Fit<sup>™</sup> integral faceplate. Provides flush look and ease of installation. Eliminates the need for additional commercial faceplates.
- Durable, textured PVC ivory or white finish. Blends with walls and ceilings. Consult factory for special colors.
- Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.
- Accommodates communication and/or power wiring. Can be used for communications, computer lines, surveillance systems, fire alarms, outlets, and more.

- Lightweight and easy to handle. Saves time and labor costs. Standard 5' [1.525m] lengths can be easily installed by one person. Special lengths up to 10' [3.050m] are available.
- FiberReady<sup>™</sup> divided fittings. For use with 2300 and 2300D. Full capacity, aesthetically pleasing fittings provide 2<sup>™</sup> [51mm] bend radius.
- Snap-on cover. Provides security with access to wiring for changes or additions.
- Easy to cut. Use a hacksaw or shears to cut raceway which speeds installation.
- Choice of raceway sizes with full line of fittings and accessories. Facilitates easy installation of wiring for whatever the job requires: communication devices, receptacles, switches, temperature controls, etc.
- **Ratings:** UL 600V (UL5A), CSA 300V (CSA 22.2 No. 62-93).



### Sure-Snap<sup>®</sup> Device Boxes

- Interchangeable covers and bases. Provides installation flexibility.
- **Large knockout.** Accommodates many cable types and quantities.
- **Cover removes easily.** One twist of a screwdriver removes the cover for fast changes.
- **No screws to assemble.** The secure snap assembly requires fewer tools and parts, which means a shorter installation time.



Sure-Snap Device Boxes are available in a variety of sizes and depths.

	Sure-S	nap 400	)/800/2	2300	Device	Box	(es (F	or N	lon-Di	vided I	Raceway	ys)
Catalog No	o./Item	em Description/Specifications			Ca	talog N	o./Item	า	Description/Specifications			
2348S/51*	<b>B</b> <b>B</b> <b>Cang(s)</b> 1						2344-2" Extra depth permits installation of cable assemblies that require groater bonds or storage					ire rage. able ng Il box e size
2347* 2347-2*	B	switche	Box – For s s, receptacle ks, connection	es, and	ORT		Cat #	Gang	(s)	A	В	с
		blocks,	coaxial, and	other	P&S		2344	1	[1	4 3/4" 21mm]	3" [76mm]	2 3/4" [70mm]
A C c c c c c c c c c c c c c c c c c c					2344-2	2	[1	4.3/4" 21mm]	4 7/8" [124mm]	2 3/4" [70mm]		
size concentric KOs. • Accepts NEMA Faceplates				-	2348 AMP* Magnetic-Backed Deep				eep ORT			
Cat # 2347 2347-2	Gang(s)   1   2	A 4 3/4" [121mm] 4 3/4" [121mm]	<b>B</b> 3" [76mm] 4 7/8" [124mm]	C 1 3/8" [35mm] 1 3/8" [35mm]		23	48-2 AN		/	for surfac Activate ( and other	t) – Recomr e mounting Connectivity devices. ns same as	nended of the inserts OPEN
2348* 2348-2* 2348-3* B B B B B B B B B B B B B						¥ S		с Д		NEMA Fac	eplates	
		devices	. Two- and t	hree-	P&S	_	Cat	#	Gang(s)	A	В	С
А		KO to e	ase has recta enable extens	sion from	OPEN		2348 AM	IP	1	4 3/4" [121mm]	3" [76mm]	1 3/8" [35mm]
existing single-gang flush wall box and 1/2" and 1" trade size concentric KOs. • Accepts NEMA Faceplates						2348-2 A	MP	2	4.3/4" [121mm]	4 7/8" [124mm]	1 3/8" [35mm]	
Cat #	Gang(s)	Α	В	c		NOT				have a recta hite finish.	angular knocl	out on the base.
2348	1	4 3/4" [121mm]	3" [76mm]	1 3/4 [35mm			, 100					
2348-2	2	4 3/4" [121mm]	4 7/8" [124mm]	1 3/4 [44mm]								
2348-3	3	4 3/4" [121mm]	6 1/2" [165mm]	1 3/4 [44mm]								

1