

One Circuit Trac System

TRAC SECTION, JOINERS & FEEDS T Series

Project: Fixture Type: Location: Contact/Phone:

PRODUCT DESCRIPTION

Low-Profile, single-circuit trac sections for surface or pendant mounting. I-beam cross section provides added strength and rigidity in pendant suspended applications. Compatible with a full range of feed, connector and mounting accessories, as listed on back of this page, to complete virtually any installation requirement. Accepts all Trac-Master and Trac-Lites trac fixtures.

PRODUCT SPECIFICATIONS

Construction Extruded aluminum "I" beam channel • One-piece thermoplastic insulator • Injection molded polycarbonate dead-end with set screw • Standard lengths may be cut-to-length by installer.

Electrical Two 12 gauge solid copper conductors • Rated 20 amps at 120 volts • Aluminum channel used as system ground • One-piece insulator insures consistent conductor spacing for reliable electrical contact • Insulating bushings supplied at mounting hole locations to prevent shorts to ground.


Labels UL listed, CSA certified.


PRODUCT INSTALLATION

Debossed polarity line provides visual cue to proper trac, trac connector and fixture alignment • Supplied with toggle bolts for surface mounting • Integral raceway in top of channel accommodates pendant mounting hardware and wire routing to electrical feed • Insulator stays same length as extrusion to simplify field-cutting of trac • Connectors and feeds simply push into trac sections.

Specifications subject to change without notice.

DIMENSIONS





ORDERING INFORMATION

Example: T 8FT WH

Series Length Finish	
T Trac-Master 1-Circuit Track Sections 2FT 2-foot track section; actual length 19-7/8" 4FT 4-foot track section; actual length 43-7/8" 6FT 6-foot track section; actual length 67-7/8" 8FT 8-foot track section; actual length 91-7/8" 12FT 12-foot track section; actual length 139-7/8" WH White	JM

One Circuit Trac System

TRAC SECTION, JOINERS & FEEDS **T Series**

Electrical Feeds Examples: T21 BL. T34 RP WH

Examples: 121 BL, 104 KI 111				
T21	T21 RP	T29	T34	T34 RP
BL, SL, WH	BL, SL, WH	BL, SL, WH	BL, SL, WH	BL, SL, WH
End Feed Connector and Outlet Box Cover	End Feed Connector and Outlet Box Cover	Floating Electrical Feed	Conduit End Feed	Conduit End Feed
For outlet box feed. Includes: outlet box cover, fixture strap and ground screw.	Same as T21 except designed for use in opposite polarity orientation compared to standard feed connectors.	Permits mounting any point of trac under outlet box. Includes floating connector, outlet box cover plus extra trac dead end.	For surface wiring. Use standard 1/2" connector.	Same as T34 except designed for use in opposite polarity orientation compared to standard feed connectors.
4" 4 1/16"		⊢ 4 5/8" —	3"	1 1/4"


Т36	T36 RP	T38	T38 RP
BL, SL, WH	BL, SL, WH	BL, SL, WH	BL, SL, WH
T-Bar End Feed	T-Bar End Feed	Live End Feed Connector	Live End Feed Connector
Wiring compartment contains standard 1/2" KO's. Feeds surface trac from above, when T-bar is directly above trac.	Same as T36 except designed for use in opposite polarity orientation compared to standard feed connectors.	Feed trac from above with flexible conduit, BX, etc., or end feed in pendant systems. Accepts standard 1/2" connector.	Same as T38 except designed for use in opposite polarity orientation compared to standard feed connectors.
4 1/8"			1/8"

T22	T122		
BL, SL, WH	BL, SL, WH		
Cord and Plug End Feed	Cord and Plug End Feed		
Comes with 15' two-wire white cord. Includes surface wire retainers and in-line switch. Max cap. 7 amps. Not UL Listed.	Same as T122 but with matching color 3-wire grounded cord and plug. No switch. Not UL Listed.		
3 1/8"			

Outrigger System

T47
BL, WH
Outrigger Bracket (non-electrified)
For mounting trac out from wall. Use two for 2'.

4' or 6' trac sections, three for 8' trac sections and four for 12' trac sections. Order trac and connectors separately. For portable electrical feed, use **T22** or **T122** Cord & Plug Connector. For permanent wiring, use **T38** end feed connector.



One Circuit Trac System

TRAC SECTION, JOINERS & FEEDS **T Series**

Trac Joiners & Dead End

BL, SL, WH

Accordion Adjustable


Joiner

Can flex to 90° angle to left, right, up or

down. Joins two trac sections.

	,
T24N ‡	T24F ‡
BL, SL, WH	BL, SL, WH
Adjustable Connector	Adjustable Connector
Joins two trac sections to make a 90° angle or straight run. Straight and right angle covers supplied. For outlet box feed, No. 127 cover plate required.	Same as T24 but with integral ground connection. For outlet box feed, No. T27 cover plate required.
4	4 (01)

Examples: T20 BL, T25 RP WH





T23

BL, SL, WH

Miniature Straight

Connector

Joins two trac sections end to end.

•
4 1/8"
1 3/8"

T25 ‡	T25 RP ‡	T25 F ‡	T26 ‡	T26 F ‡
BL, SL, WH	BL, SL, WH	BL, SL, WH	BL, SL, WH	BL, SL, WH
"T" Connector	"T" Connector	"T" Connector	"X" Connector	"X" Connector
Joins three trac sections. For outlet box feed, No. T27 cover plate required.	Same as T25 except designed for use in opposite polarity orientation compared to standard feed connectors.	Same as T25 but with integral ground connection. For outlet box feed, No. T27 cover plate required.	Joins four trac sections at 90° angles. For outlet box feed, T27 cover plate required.	Same as T26 but with integral ground connection. For outlet box feed, No. T27 cover plate required.
4 1/8"			4	1/8"

T27	T28	T35	T49
BL, SL, WH	BL, SL, WH	BL, SL, WH	BL, SL, WH
Outlet Box Cover	Trac Dead End	T-Bar Adjustable Joiner Feed	Trac Continuation Kit
Use with Nos. T24/T25/T26 for outlet box electrical feed. Includes: nipple, locknut and ground screw.	For use with field-cut trac sections.	Joins two trac sections to make 90° angle or straight run. Wiring compartment contains standard 1/2″ KO's. Feeds from above when T-bar is directly above trac.	Permits trac to continue a run around obstructions. Includes one T34 Conduit Feed and one T34 RP Conduit Feed. Fits standard 1/2" conduit.
1/2" - 4" sq		4 1/8" 4 1/8"	3"

T24N, T25 and T26 may not be used as feed connectors in Canada due to special grounding requirements - T24F, T25F & T26F are approved for use as feed connectors in Canada (may also be used in U.S.).

One Circuit Trac System

TRAC SECTION, JOINERS & FEEDS **T Series**

Pendant Stems	Examples: T90 12IN BL, T93 BL
Pengant Stems	EXAMPLES: 190 1211 BL, 193 BL

Examples. 170 1211 Bi, 170 Bi			
Т90	T91	T9091M	
12IN, 18IN, 24IN, 36IN, 48IN	12IN, 18IN, 24IN, 36IN, 48IN	12IN, 18IN, 24IN, 36IN, 48IN	
BL, SL, WH	BL, SL, WH	BL, SL, WH	
T-Bar Pendant Stem Kit	Rigid Ceiling Pendant Stem Kit	Pendant Stem Mechanical Support Kit	
Compatible with 15/16" flush T-Bar ceilings. Use two for 2', 4', 6' of trac or three for 8' of trac. Includes canopy, T-Bar mounting plate, stem and trac attachment hardware. For electrical feed, order T93 wireway cover.	Attaches directly to junction box in rigid ceilings. Use two for 2', 4', 6' of trac or three for 8' of trac. Includes canopy, J-Box mounting strap, stem and trac attachment hardware. For electrical feed, order T93 wireway cover.	For mechanical support only (no feed). Suspends Trac from T-bar or rigid ceilings. Use two for 2', 4', 6' of trac or three for 8' of trac or four for 12' of trac (support is required every 4 feet). Includes Mini-Canopy, pendant stem, 15/16" T-bar clip, drywall anchor and Trac mounting hardware.	
4 3/4" 1/2" diameter		2-1/4" 1/2" diameter	

T92	T92 L	Т93	T94	
BL, SL, WH		BL, SL, WH	BL, SL, WH	
Straight Structural Bridge	Corner Structural Bridge	Wireway Cover	Sloped Ceiling Adapter	
For use with T24 Straight Connector. Permits mounting Pendant Stem Kits (T90, T91) at center of Trac Joiner.	For use with T24 Right Angle Connector. Permits mounting Pendant Stem Kits (T90, T91) at center of Right Angle Connector.	For Pendant Stem Kits T90 and T91 . Conceals electrical feed wires from stem to connector. One cover required for each trac feed.	Allows T90 or T91 pendant to hang straight down from sloped ceilings. Can be used to feed electrical wires to Trac at up to 60° angle.	
C. C		10 1/8"		

Т96	T56	
BL, SL, WH	BL, SL, WH	
Pendant Stem Threaded Coupling	Solid Rod Pendant Mounting Kit	
Enables multiple pendant stems to be joined for higher ceiling applications.	Attaches solid 5/16" threaded rod to Trac. Includes: plastic cap, mounting bracket and hardware. Rod not supplied.	
	99 440	

One Circuit Trac System

TRAC SECTION, JOINERS & FEEDS **T Series**

Cable Suspension

Examples: T595 48IN BL, T598 144IN WH

T595	T597	T596	T598
48IN, 144IN	48IN, 144IN	48IN, 144IN	48IN, 144IN
BL, WH	BL, WH	BL, WH	BL, WH
T-Bar Ceiling Cable Suspension Kit	Rigid Ceiling Cable Suspension Kit	T-Bar Ceiling Cable Suspension/Feed Kit	Rigid Ceiling Cable Suspension/Feed Kit
Mechanical-only cable suspension kit for 1-circuit or 2-circuit trac. Compatible with 15/16" flush T-Bar ceilings. Adjustable 48" or 144" stainless steel cable length. Includes mini-canopy, T-bar clip and cable hardware. Trac requires support every 4'.	Mechanical-only cable suspension kit for 1-circuit or 2-circuit trac. Attaches directly to junction box in rigid ceilings. Adjustable 48" or 144" stainless steel cable length. Includes mini-canopy, toggle bolt and cable hardware. Trac requires support every 4'.	Cable suspension kit with adjustable 48" or 144" electrical feed cable for 1-circuit trac. Compatible with 15/16" flush T-Bar ceilings. Includes canopy, T-bar clip, mounting plate, cable hardware and flexible electrical feed cable. Trac feed connector not included (order separately). Trac requires support every 4'.	Cable suspension kit with adjustable 48" or 144" electrical feed cable for 1-circuit trac. Attaches directly to junction box in rigid ceilings. Includes canopy, J-box mounting strap, cable hardware and flexible electrical feed cable. Trac feed connector not included (order separately). Trac requires support every 4'.

Note: Cable suspension is recommended for pattern installations only, or those installations that are supplemented with additional rigid mounting points (stems, threaded rod, etc.).

Accessories Example: T31N BL

		·		
T37F	T37D	T37F916	T37D916	
15/16" T-Bar Attachment Clip	15/16" T-Bar Attachment Clip	9/16" T-Bar Attachment Clip	9/16" T-Bar Attachment Clip	
To attach to inverted tee ceilings using flush tiles. Use two for 2' or 4' trac and three for 6' or 8' trac.	Same as T37F with spacer for ceilings using drop tiles.	To attach to inverted tee ceilings using flush or drop tiles. Use two for 2' or 4' trac and three for 6' or 8' trac.	Same as T37F916 with spacer for ceilings using drop tiles.	


T31N	Т32	Т33	Т39
BL, SL, WH	BL, SL, WH	BL, SL, WH	
Pendant Adapter	Plant or Utility Hook	Outlet Adapter	Trac Wireway Cover
Adapts corded, swag or chain-hung fixture to trac. Includes loop hook for chain installation and strain relief for direct cord suspension. Chain installation accepts cord diameters up to 0.270" and supports up to 15 lbs. Strain relief installation accepts cord diameters of 0.170" to 0.255", type SVT 18/3, and supports up to 5 lbs. May also be specified with GTYPE, HTYPE or LTYPE Alternate Mounting Adapters (i.e. T31N HTYPE WH). 5A max. UL Listed.	Supports up to 25 lbs. Not UL Listed.	Provides electrical receptacle. Not UL Listed.	4' black thermoplastic extrusion, covers wire carried in trac wireway. Use one for 4' trac, two for 8' and three for 12' trac. Can be field cut.
1357	11/4"]	2"	46 1/2"


Note: GTYPE, HTYPE and LTYPE available in BL or WH finishes only.


One Circuit Trac System

TRAC SECTION, JOINERS & FEEDS T Series


Example Trac Configurations & Recommended Components (Top Plan View)







- 1 Standard "L" Connector T24N
- 2 Standard "T" Connector **T25**
- (3) Reverse Polarity "T" Connector T25 RP
- 4 Standard "X" Connector T26
- 5 Standard End Feed Connector **T38** (or similar End Feed)
- (6) Reverse Polarity End Feed Connector T38 RP (or similar Reverse Polarity End Feed)



(Each run controlled by separate feeds)