


TYPE SP

VINYLINK™

Splice, Polyvinylchloride Insulated

600 Volts Max., 105° C Max.

The Type SP VINYLINK™ is a PVC insulated seamless butt splice. Type SP VINYLINK™ is designed to accommodate a broad range of 600 volt cables.




B-47



Features & Benefits

- Manufactured from seamless electrolytic copper tubing
 - ◇ Provides maximum conductivity and tensile strength, in a high quality design with NO seams to split
- Funnel entry
 - ◇ Provides easy wire insertion
- Electro-tin plated
 - ◇ Provides durable long lasting resistance to corrosion



- Expanded insulation support
 - ◇ Lower inventory requirements
- Red wire range of 22-16
 - ◇ Lower inventory requirements
- Vinyl insulator
 - ◇ Economical means of providing high dielectric values and cable insulation support

| Catalog Number | Wire Range | Color Code | Bulk Catalog Number | Dimensions (Inches) | | Installation Tooling | Wire Strip Length |
|----------------|------------|------------|---------------------|---------------------|----------------|--|-------------------|
| | | | | L Max. | Max Insul. Dia | | |
| SP16 | 22 - 16 | Red | BS16 | 1.00 | 0.15 | Non-Ratchet: Y10-22 Ratchet: MRE1022NV MR8G-98 MR15 MR8-89-1 | 1/4" |
| SP14 | 16 - 14 | Blue | BS14 | 1.00 | 0.18 | Non-Ratchet: Y10-22 Ratchet: MRE1022NV MR8G-98 MR15 MR8-89-1 | 1/4" |
| SP10 | 12 - 10 | Yellow | BS10 | 1.23 | 0.26 | Non-Ratchet: Y10-22 Ratchet: MRE1022NV MR8G-98 MR15 MR8-89-1 | 21/64" |

SMALL TERMINAL KITS

B-92

PACKAGED KITS OF VARIOUS TYPES OF SMALL TERMINALS

For Use On Copper Conductor

Small Terminal Kits are packaged in reusable plastic cases with secure compartments for each type of connector. Clearly marked on the inside front cover with part numbers and descriptions, the kits contain some of the most common terminals needed on everyday installations.



Features & Benefits

- Quality terminals of various types packaged together for convenience
- Color-coded barrels
- Reusable, refillable container
- Clearly marked with part numbers and descriptions on inside cover

Catalog Number: STKIT08

Contains:

| Kit | Catalog Number | Quantity | Description |
|---------|----------------|----------|--|
| STKIT08 | SP14 | 20 | #16 - #14 AWG splice; vinyl insulation |
| | QP14M25X03D | 10 | #16 - #14 AWG male disconnect; .250 tab size; vinyl insulation |
| | QP14F25X03 | 10 | #16 - #14 AWG female disconnect; .250 tab size; vinyl insulation |
| | TP14-10 | 20 | #16 - #14 AWG ring terminal; 8 - 10 stud size; vinyl insulation |
| | TP14-10F | 20 | #16 - #14 AWG fork terminal; 8 - 10 stud size; vinyl insulation |
| | SP10 | 10 | #12 - #10 AWG splice; vinyl insulation |
| | TP10-10 | 20 | #12 - #10 AWG ring terminal; 8 - 10 stud size; vinyl insulation |
| | TP10-10F | 20 | #12 - #10 AWG fork terminal; 8 - 10 stud size; vinyl insulation |

Catalog Number: STKIT15

Contains:

| Kit | Catalog Number | Quantity | Description |
|---------|----------------|----------|---|
| STKIT15 | QP18M18X02D | 20 | #22 - #18 AWG male disconnect; .187 tab; vinyl insulation |
| | QP18M25X03D | 20 | #22 - #18 AWG male disconnect; .250 tab; vinyl insulation |
| | QP18F18X02D | 20 | #22 - #18 AWG female disconnect; .187 tab; vinyl insulation |
| | QP18F25X03D | 20 | #22 - #18 AWG female disconnect; .250 tab; vinyl insulation |
| | BULM18P | 20 | #22 - #18 AWG male bullet disconnect; vinyl insulation |
| | BULF18P | 20 | #22 - #18 AWG female bullet disconnect; vinyl insulation |
| | SP18 | 20 | #22 - #18 AWG splice; vinyl insulation |
| | QP14M18X02D | 20 | #16 - #14 AWG male disconnect; .187 tab; vinyl insulation |
| | QP14M25X03D | 20 | #16 - #14 AWG male disconnect; .250 tab; vinyl insulation |
| | QP14F18X02D | 20 | #16 - #14 AWG female disconnect; .187 tab; vinyl insulation |
| | QP14F25X03D | 20 | #16 - #14 AWG female disconnect; .250 tab; vinyl insulation |
| | BULM14P | 20 | #16 - #14 AWG male bullet disconnect; vinyl insulation |
| | BULF14P | 20 | #16 - #14 AWG female bullet disconnect; vinyl insulation |
| | SP14 | 20 | #16 - #14 AWG splice; vinyl insulation |
| | SP10 | 20 | #12 - #10 AWG splice; vinyl insulation |