


YDS4W

by Burndy
Catalog ID: YDS4W

Prop 65 Notice

CU Full tension splice, ANSI C119.4 Class 1A(Normal Tension),2-1/2 IN L.

Features: YDS-W Is Designed To Develop Full Rated Breaking Strength Of Hard Drawn And Medium Hard Drawn Solid Copper Conductor, Made Of Pure Copper Tubing, Installed With Standard Tooling, Die Index: 162 Element A, Conductor Type: Solid Copper, Tools, Die Set Catalog Number, And (number Of Crimps): MD7, MD6 Tool, W162 Die, (4), Y35, Y750 Tool, U162 Die, (1), Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1



Product Details

General

Application	For Solid Copper Conductors
Connector Type	Splice
Die Index	162
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810820940

Dimensions

Dimension - B Length inch	1.15 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.55 in
Dimension - Outside Diameter inch	0.38 in

Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Size	6 AWG - 3 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)