



YDS4C

by Burndy
Catalog ID: YDS4C

Prop 65 Notice

CU Full tension splice, Index: 162.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 162 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W162 Die, (4), Y35, Y750 Tool, U162 Die, (1), Y45 Tool, U162 Die With PT-6515 Adapter, (1), Y46 Tool, U162 Die With PUADP-1 Adapter, (1), Conductor Type: Stranded Copper

Product Details

General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	162
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS - C
UPC	781810821060

Dimensions

Dimension - B Length fraction	1-3/20 in
Dimension - B Length inch	1.15 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.55 in
Dimension - Outside Diameter inch	0.40 in

Conductor Related

Conductor - Copper Str Size	4 AWG
-----------------------------	-------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)