

DISTRIBUTION WIRE CONNECTOR 6 CABLES 3 PCS.  
ACCESSORY FOR: 3VA5 125



Model	
Product brand name	SETRON
Product designation	accessories

Connections according IEC	
Connectable conductor cross-section	
<ul style="list-style-type: none"> <li>• for copper cable / solid / minimum</li> </ul>	1.5 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for copper cable / solid / maximum</li> </ul>	16 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for copper cable / finely stranded / minimum</li> </ul>	1.5 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for copper cable / finely stranded / maximum</li> </ul>	25 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for copper cable / stranded / minimum</li> </ul>	1.5 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for copper cable / stranded / maximum</li> </ul>	35 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for aluminum cable / solid / minimum</li> </ul>	4 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for aluminum cable / solid / maximum</li> </ul>	16 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for aluminum cable / stranded / minimum</li> </ul>	4 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for aluminum cable / stranded / maximum</li> </ul>	35 mm <sup>2</sup>
Wire stripping length	12 / 24 / 38,5 mm
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> <li>• solid</li> </ul>	<= 10 mm <sup>2</sup> : 6.2 Nm, > 10 mm <sup>2</sup> : 7 Nm

- stranded
- finely stranded






<= 10 mm<sup>2</sup>: 6.2 Nm, > 10 mm<sup>2</sup>: 7 Nm

<= 10 mm<sup>2</sup>: 6.2 Nm, > 10 mm<sup>2</sup>: 7 Nm

## Connections according UL

Wire stripping length	0.5 / 0.9 / 1.5 in
Connectable conductor cross-section	
<ul style="list-style-type: none"> <li>• for copper cable / solid / minimum</li> <li>• for copper cable / solid / maximum</li> <li>• for copper cable / stranded / minimum</li> <li>• for copper cable / stranded / maximum</li> <li>• for copper cable / finely stranded / minimum</li> <li>• for copper cable / finely stranded / maximum</li> <li>• for aluminum cable / solid / minimum</li> <li>• for aluminum cable / solid / maximum</li> <li>• for aluminum cable / stranded / minimum</li> <li>• for aluminum cable / stranded / maximum</li> </ul>	14 AWG 10 AWG 14 AWG 2 AWG 14 AWG 2 AWG 12 AWG 10 AWG 12 AWG 2 AWG
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> <li>• solid</li> <li>• stranded</li> <li>• finely stranded</li> </ul>	<= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in <= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in <= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in

## Certificates

General Product Approval	EMC	Declaration of Conformity	other
			
			<a href="#">Miscellaneous</a>

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JF60>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JF60>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)







[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9133-0JF60](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JF60)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



**last modified:**

11/20/2017