

L2WMG

LED LINKABLE WRAPAROUND

Stanpro's L2WMG is a LED linkable wrap and is available in 24" and 48". Comes standard with 2 connectors ideal for surface and row mount. Perfectly suited for a variety of commercial and residential applications, such as utility rooms, corridors, hallways, restrooms, and where a decorative fixture with efficient lighting is required.

FEATURES AND SPECIFICATIONS

• Construction

Housing

Steel white powder coating

Mounting options

Surface mount, wall and ceiling

Lens

Frosted polycarbonate lens

• Installation

Ceiling row mount up to 8 units for the 4 ft wrap, and up to 15 units for the 2 ft wrap is possible.

(Connectors included). (see connectors image below)

• Electrical

– Comes standard with 2 connectors to allow easy and rapid connections:

- linkable connector

- 12" linkable cable connector

– Available in 4 000 K only with long-life LEDs that provide 80+ CRI

– Suitable in -25°C to +55°C ambient conditions

– Comes standard with 120-277 V driver

– Suitable for damp location

• Compliances

– Meets requirements of ICES-005

– ETL



OVERVIEW

Light source	LED
Watts (W)	27 - 47
Lumen output (lm)	2878 - 5043
Efficiency (lm/W)	106
Color temperature (K)	4 000
CRI	>80
Weight (lbs)	2.65, 4.63



Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.

QUICK SHIP AND TECHNICAL SPECIFICATION TABLE

Part number	DLC unique ID	Watts (W)	Volts (VAC)	Color temp. (K) ²	Lumen output (lm) ³	Efficiency (lm/W)	CRI	Life L70 (hrs) ⁴	Tested hours LM-80 (hrs) ⁴	Dimming (Yes/No)	Power factor	THD (%)	Case qty (master)
24"													
L2WMG-24-1	PLA98WZM07YZ	27	120-277	4 000	2 878	106	84	> 54 000	9 000	No	0.90	10	12
48"													
L2WMG-48-1	PL6A37IC1S7D	47	120-277	4 000	5 043	106	84	> 36 000	6 000	No	0.93	15	6

¹ **QUICK SHIP:** Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.



² Typical color temperature range: +/- 5 %.

³ Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

⁴ Life hours are derived from IESNA LM-80-08 testing report and projected per IESNA TM-21-11 extrapolations.

ACCESSORIES (order separately)

Part number	Type
HAR1001	Linkable connector no cable
WIR223	12in connector
WIR151-4FT	4ft connector
WIR151-6FT	6ft connector
WIR151-8FT	8ft connector

DIMENSIONS
24 po

48 po


Included connectors



Fixture with linkable connector




Fixture with 12" linkable cable connector

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions.
All products are subject to change or may be discontinued any time without notice.

PHOTOMETRIC DATA¹

L2WMG-24-1 • 2 858.5 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	797.1	27.9%
0-40	1 291.6	45.2%
0-60	2 243.6	78.5%
60-90	588.2	20.6%
70-100	258.7	9%
90-120	13.8	0.5%
0-90	2 831.9	99.1%
90-180	26.6	0.9%
0-180	2 858.5	100%


Illuminance at a distance

Center beam fc	Beam width
1.7'	362 fc
3.3'	96.1 fc
5.0'	41.9 fc
6.7'	23.3 fc
8.3'	15.2 fc
10.0'	10.5 fc

Vert. spread: 105.2°
Horiz. spread: 108.0°

L2WMG-48-1 • 4 946.4 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 366.9	27.6%
0-40	2 212.0	44.7%
0-60	3 834.6	77.5%
60-90	1 067.9	21.6%
70-100	513.6	10.4%
90-120	32.9	0.7%
0-90	4 902.5	99.1%
90-180	43.9	0.9%
0-180	4 946.4	100%

Illuminance at a distance

Center beam fc	Beam width
1.7'	622 fc
3.3'	165 fc
5.0'	71.9 fc
6.7'	40.0 fc
8.3'	26.1 fc
10.0'	18.0 fc

Vert. spread: 108.5°
Horiz. spread: 99.6°

¹ Complete IES files available on our website.