

Part No.: CH1000F

14-2 Unshielded Audio Cable Non-Plenum

ETL listed for guaranteed performance
Made in the USA

Applications


This document establishes the specifications for a two conductor cable used in audio and power limited circuit applications.

Construction Details

Number of Conductors: 2/C
Conductor: 14 AWG 105/34 Bare Copper
Insulation Material: Polyvinyl Chloride
Nominal Insulation Thickness: 0.012 in.
Nominal Insulation Diameter: 0.097 in.
Color Code: Black, Red
Jacket Material: Polyvinyl Chloride
Nominal Jacket Thickness: 0.018 in.
Nominal Diameter: 0.230 in.
Surface Print: 3122598 HI-STRAND AUDIO
CABLE CSA C(ETL) FT4 4 COND
14AWG 105 STRAND 75°C CL3R
(ETL)US MADE IN USA...SUITABLE
FOR OUTDOOR USE...OXYGEN
FREE COPPER + Sequential
Footage Marking

Electricals

Suggested Working Voltage: 150 Volts, rms.



Technical Details

Temperature Rating
Operation -20°C to +75°C
Nominal Weight: 38 lbs. / 1,000 Feet

Standards

NEC Article 725
UL Subject 13, Type CL3R FT4

Codes & Listings

(ETL)US
C(ETL)

Preparation for Shipment

The cable shall be packaged to preclude the inducement of damage due to handling and transportation, and shall be in accordance with the best commercial practices available. Shipping containers shall be constructed as to eliminate any possible damage to the cables due to shipment.

Warranty Info

All warranty information can be viewed at www.remee.com. This product is RoHS compliant and is directive 2002/95/EC. It is the sole responsibility of the user to have the most current specification. Specifications are subject to change without notice.